

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008090

Luminaire Tested: S122DIP-B485D330UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008090
REPORT IS A COMBINATION OF REPORTS P984193 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D330UB2750-4F0-XX-W2A-D_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3277.0 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008090

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008090

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	97	92	87	83	89	85	81	78	72	69	67	60	58	56	50	48	47
2	88	79	72	67	81	73	67	62	62	58	54	52	49	46	43	40	38
3	80	69	61	55	73	64	57	51	54	49	45	46	41	38	37	34	32
4	73	61	52	46	67	56	49	43	48	42	38	40	36	32	33	30	27
5	66	54	45	39	61	50	42	37	43	37	32	36	31	28	30	26	23
6	61	48	40	34	56	45	37	32	38	32	28	32	28	24	27	23	20
7	56	44	35	29	52	41	33	28	35	29	24	29	25	21	24	21	18
8	52	39	31	26	48	37	29	24	32	26	22	27	22	19	22	19	16
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	14
10	45	33	25	21	42	31	24	19	27	21	17	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8122	8122	8122
5°	8159	7775	7733
10°	8105	7506	7397
15°	7990	7228	7054
20°	7846	6935	6728
25°	7703	6655	6432
30°	7505	6371	6139
35°	7302	6097	5924
40°	7090	5859	5711
45°	6886	5643	5524
50°	6669	5445	5341
55°	6440	5234	5153
60°	6160	5015	4957
65°	5869	4763	4730
70°	5539	4492	4486
75°	5119	4221	4257
80°	4455	3940	4018
85°	3786	3674	3812

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6886 cd/sqm

TEST NUMBER: P1008090

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.6	1.5
10°-20°	139.5	4.3
20°-30°	211.4	6.5
30°-40°	257.4	7.9
40°-50°	277.0	8.5
50°-60°	269.0	8.2
60°-70°	234.9	7.2
70°-80°	180.8	5.5
80°-90°	121.9	3.7
90°-100°	98.4	3.0
100°-110°	116.3	3.5
110°-120°	186.9	5.7
120°-130°	265.6	8.1
130°-140°	267.7	8.2
140°-150°	241.6	7.4
150°-160°	193.0	5.9
160°-170°	124.3	3.8
170°-180°	42.8	1.3
0°-30°	399.6	12.2
0°-40°	657.0	20.0
0°-60°	1202.9	36.7
0°-90°	1740.5	53.1
90°-120°	401.5	12.3
90°-150°	1176.4	35.9
90°-180°	1536.0	46.9
0°-180°	3277.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	513	513	513	513	513	
5°	515	512	508	512	512	49
15°	491	492	492	499	498	138
25°	446	451	458	467	469	205
35°	384	397	411	428	433	240
45°	315	335	361	384	392	243
55°	242	268	307	334	344	216
65°	165	202	245	276	286	164
75°	92	133	181	213	222	97
85°	27	73	120	152	162	28
90°	8	54	105	136	146	6
95°	27	51	98	128	137	30
105°	103	134	84	113	123	110
115°	190	204	245	117	102	187
125°	266	270	300	323	330	238
135°	328	333	344	362	368	254
145°	380	379	385	392	394	238
155°	418	415	419	421	418	193
165°	440	439	440	442	440	124
175°	451	448	449	451	448	43
180°	450	450	450	450	450	

TEST NUMBER: P1008090

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	513.1	513.1	513.1	513.1	513.1
2.5°	516.9	514.6	509.4	513.1	511.7
5°	514.6	512.4	507.9	512.4	511.7
7.5°	510.9	509.4	505.7	510.9	510.2
10°	506.5	505.0	502.7	508.7	507.9
12.5°	499.0	499.8	498.3	504.2	503.5
15°	490.8	492.3	492.3	499.0	498.3
17.5°	480.4	483.4	485.6	492.3	492.3
20°	470.0	473.7	476.7	484.9	484.9
22.5°	458.9	463.3	467.8	476.0	477.5
25°	446.2	451.4	458.1	467.0	469.3
27.5°	431.3	439.5	447.0	458.1	459.6
30°	416.5	426.1	435.8	447.7	449.9
32.5°	400.1	411.3	423.2	437.3	441.8
35°	384.5	397.1	411.3	427.6	432.8
37.5°	367.4	381.5	399.4	417.2	422.4
40°	350.3	366.6	386.7	406.1	412.8
42.5°	333.9	350.3	374.1	395.6	402.3
45°	315.3	335.4	361.4	384.5	391.9
47.5°	297.5	319.0	348.8	372.6	380.8
50°	278.9	301.9	335.4	360.7	368.9
52.5°	261.0	285.6	321.3	347.3	356.2
55°	241.7	268.5	307.1	333.9	343.6
57.5°	223.1	252.9	291.5	320.5	330.2
60°	203.0	235.0	277.4	305.7	316.1
62.5°	185.2	218.6	261.0	291.5	301.2
65°	165.1	201.5	245.4	275.9	285.6
67.5°	147.3	185.2	229.8	260.3	270.7
70°	127.9	166.6	212.7	244.7	253.6
72.5°	110.1	150.2	197.1	228.3	239.5
75°	91.5	133.1	180.7	212.7	222.4
77.5°	73.6	116.8	165.1	197.1	207.5
80°	55.8	101.1	149.5	180.7	191.1
82.5°	40.9	85.5	134.6	165.8	175.5
85°	26.8	72.9	120.5	151.7	162.1
87.5°	16.4	61.0	108.6	139.1	148.7
90°	7.7	54.5	104.7	136.0	145.6
92.5°	14.8	52.9	99.3	129.0	138.2
95°	27.0	51.3	98.2	128.1	136.7
97.5°	43.3	48.6	96.9	125.4	134.7
100°	62.8	45.7	92.9	123.0	131.9
102.5°	83.6	107.4	88.4	118.7	127.9
105°	102.6	134.0	83.8	113.4	122.9
107.5°	125.7	151.7	79.3	108.1	117.6
110°	147.1	168.8	111.2	102.5	112.0

TEST NUMBER: P1008090

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	168.0	185.7	214.4	98.0	107.1
115°	190.1	203.8	245.3	117.0	101.8
117.5°	208.5	221.0	257.7	233.5	155.7
120°	230.0	237.8	273.5	298.2	262.5
122.5°	248.2	254.2	288.2	310.2	317.3
125°	266.0	270.2	300.2	322.6	330.3
127.5°	282.9	286.7	311.7	333.5	340.6
130°	298.9	303.3	322.6	343.9	349.6
132.5°	315.1	318.6	333.4	353.4	359.1
135°	328.0	333.2	343.6	362.5	367.7
137.5°	342.3	346.2	353.3	370.6	374.9
140°	356.3	358.2	363.3	378.1	380.9
142.5°	368.0	369.6	373.8	385.3	387.4
145°	379.7	379.4	384.9	391.7	393.8
147.5°	390.4	389.5	395.0	397.3	398.3
150°	400.8	398.6	403.8	405.7	404.1
152.5°	409.6	407.0	411.9	413.9	411.6
155°	418.1	415.2	419.1	421.0	418.4
157.5°	424.9	422.3	425.2	427.5	424.9
160°	430.8	428.8	430.8	432.7	430.5
162.5°	436.0	434.0	435.7	437.9	435.0
165°	440.5	438.6	439.6	441.8	439.6
167.5°	444.1	442.2	443.1	445.4	442.5
170°	447.0	445.1	445.7	448.0	445.1
172.5°	449.0	447.0	447.7	450.0	447.0
175°	450.6	448.3	449.0	451.3	448.0
177.5°	451.3	449.0	449.3	451.6	448.7
180°	449.6	449.6	449.6	449.6	449.6

(END OF REPORT)