

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001510

Luminaire Tested: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001510
REPORT IS A COMBINATION OF REPORTS P996129 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6759.6 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001510

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001510

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37
2	86	79	73	68	78	72	67	62	58	54	51	46	43	41	34	32	31
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26
4	72	61	54	48	65	56	49	44	45	41	37	36	32	30	27	25	23
5	66	55	47	41	59	50	43	38	41	35	32	32	28	26	24	22	20
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	18	18	16	14
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7841	7841	7841
5°	7848	7615	7625
10°	7781	7404	7353
15°	7669	7153	7045
20°	7527	6880	6726
25°	7367	6594	6384
30°	7173	6283	6008
35°	6973	5965	5644
40°	6763	5623	5258
45°	6545	5280	4896
50°	6302	4947	4495
55°	6038	4558	4098
60°	5770	4133	3683
65°	5461	3693	3217
70°	5104	3164	2717
75°	4573	2550	2176
80°	3899	1844	1530
85°	3027	1028	824

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6545 cd/sqm

TEST NUMBER: P1001510

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	1.3
10°-20°	255.3	3.8
20°-30°	375.8	5.6
30°-40°	436.8	6.5
40°-50°	436.8	6.5
50°-60°	382.0	5.7
60°-70°	283.6	4.2
70°-80°	160.9	2.4
80°-90°	48.3	0.7
90°-100°	436.6	6.5
100°-110°	888.0	13.1
110°-120°	791.5	11.7
120°-130°	664.8	9.8
130°-140°	554.8	8.2
140°-150°	423.7	6.3
150°-160°	297.8	4.4
160°-170°	175.2	2.6
170°-180°	57.0	0.8
0°-30°	721.7	10.7
0°-40°	1158.6	17.1
0°-60°	1977.4	29.3
0°-90°	2470.3	36.5
90°-120°	2116.0	31.3
90°-150°	3759.4	55.6
90°-180°	4289.0	63.5
0°-180°	6759.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	962	962	962	962	962	
5°	961	958	949	958	956	91
15°	914	912	900	904	902	258
25°	828	823	812	813	810	381
35°	713	707	696	691	687	446
45°	582	576	564	556	553	448
55°	440	438	427	418	413	394
65°	298	294	287	279	275	295
75°	159	155	151	148	147	168
85°	42	42	40	40	39	45
90°	1	9	21	23	24	5
95°	38	120	941	466	282	42
105°	135	196	758	1631	1625	144
115°	238	298	676	1298	1560	236
125°	331	394	672	1104	1245	295
135°	394	469	666	980	1113	304
145°	454	520	663	827	909	285
155°	516	557	644	730	761	238
165°	562	580	618	654	664	159
175°	587	588	592	600	598	56
180°	588	588	588	588	588	

TEST NUMBER: P1001510

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	961.5	961.5	961.5	961.5	961.5
2.5°	964.6	962.3	953.8	961.5	960.8
5°	960.8	957.7	949.2	957.7	956.2
7.5°	953.8	950.8	941.5	948.4	947.7
10°	943.8	940.7	930.7	936.9	935.4
12.5°	930.7	927.6	916.9	923.8	921.5
15°	914.5	911.5	899.9	904.5	902.2
17.5°	896.1	892.2	881.4	884.5	883.0
20°	875.3	871.4	859.8	862.2	860.6
22.5°	852.9	847.5	836.0	840.6	837.5
25°	828.3	822.9	812.1	812.8	809.8
27.5°	800.5	795.1	785.1	783.6	779.7
30°	772.8	766.6	756.6	753.5	749.7
32.5°	743.5	738.1	727.3	723.5	719.6
35°	712.7	707.3	696.5	691.1	687.3
37.5°	680.3	675.7	664.1	658.8	653.4
40°	648.7	642.6	631.0	623.3	619.5
42.5°	614.8	611.8	598.7	589.4	587.1
45°	581.7	576.3	564.0	555.5	553.2
47.5°	547.0	543.2	531.6	522.4	516.2
50°	511.6	508.5	497.7	486.9	482.3
52.5°	476.9	473.1	461.5	452.3	446.1
55°	439.9	437.6	426.8	417.6	413.0
57.5°	405.3	403.0	392.2	382.9	378.3
60°	369.1	365.2	355.2	348.3	344.4
62.5°	333.6	330.5	319.7	313.6	309.7
65°	298.2	294.3	286.6	278.9	275.1
67.5°	262.0	258.9	251.2	243.5	242.7
70°	228.8	223.4	217.3	211.1	208.8
72.5°	193.4	188.0	183.4	178.7	176.4
75°	158.7	154.9	151.0	147.9	147.2
77.5°	124.8	123.3	119.4	118.7	116.3
80°	94.8	92.5	90.9	89.4	88.6
82.5°	65.5	64.7	64.7	63.9	63.2
85°	41.6	41.6	40.1	40.1	39.3
87.5°	20.0	19.3	18.5	18.5	18.5
90°	1.2	9.2	20.8	23.1	24.2
92.5°	16.2	88.9	452.6	149.6	105.1
95°	38.1	120.0	941.1	465.9	281.7
97.5°	63.5	132.8	1006.9	951.4	676.7
100°	87.8	150.1	928.4	1316.4	1058.9
102.5°	110.9	170.9	830.2	1545.0	1391.4
105°	135.1	195.8	757.5	1631.0	1624.7
107.5°	161.7	221.2	710.1	1605.0	1735.5
110°	188.2	246.5	688.2	1512.7	1737.8

TEST NUMBER: P1001510

CATALOG NUMBER: SA4XXDIP-B575D1205UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.6	271.9	677.8	1399.5	1669.7
115°	237.9	298.5	675.5	1297.9	1560.0
117.5°	263.3	323.4	674.3	1218.2	1452.6
120°	288.7	347.5	674.3	1164.5	1364.9
122.5°	311.8	371.2	673.2	1129.3	1295.6
125°	331.4	393.8	672.0	1104.4	1244.8
127.5°	349.9	414.6	669.7	1080.8	1212.4
130°	364.9	434.8	668.6	1052.5	1184.7
132.5°	379.9	452.1	667.4	1019.0	1153.5
135°	393.8	468.8	666.3	980.4	1113.1
137.5°	407.6	483.2	666.3	938.8	1065.8
140°	422.6	496.6	665.1	898.4	1013.8
142.5°	438.8	508.6	665.1	860.8	958.4
145°	453.8	519.6	662.8	826.8	908.8
147.5°	471.1	530.0	659.3	798.5	862.6
150°	487.3	539.8	655.9	772.5	824.5
152.5°	502.3	549.0	650.1	750.6	789.8
155°	516.2	557.2	644.3	729.8	760.9
157.5°	530.0	564.7	638.6	710.2	734.4
160°	542.7	571.0	631.6	690.5	710.1
162.5°	554.3	576.2	624.7	671.4	687.0
165°	562.3	579.7	617.8	654.2	664.0
167.5°	571.6	582.6	610.8	639.2	645.5
170°	577.4	584.8	603.9	624.1	628.2
172.5°	583.1	586.6	597.0	610.8	610.8
175°	586.6	587.7	592.4	600.4	598.1
177.5°	588.9	587.7	588.9	593.0	588.9
180°	587.7	587.7	587.7	587.7	587.7

(END OF REPORT)