

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008094

Luminaire Tested: S122DIP-B485D330UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008094
REPORT IS A COMBINATION OF REPORTS P984197 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D330UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3258.0 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008094

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1008094

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	65	65	60
1	100	96	92	88	93	89	86	83	78	75	73	67	66	64	58	56	55	55	55	50
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46	46	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40	40	40	36
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34	34	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	30	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	26	26	23
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	23	23	21
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21	21	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	19	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12139	12139	12139
5°	12159	11571	11488
10°	12060	11044	10825
15°	11883	10512	10125
20°	11644	9934	9464
25°	11407	9330	8802
30°	11106	8764	8109
35°	10825	8165	7428
40°	10476	7574	6783
45°	10129	6989	6152
50°	9752	6394	5497
55°	9353	5755	4877
60°	8906	5066	4232
65°	8415	4365	3554
70°	7791	3597	2869
75°	6931	2773	2216
80°	5884	1884	1425
85°	4266	878	607

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10129 cd/sqm

TEST NUMBER: P1008094

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.2	2.2
10°-20°	203.1	6.2
20°-30°	298.4	9.2
30°-40°	346.6	10.6
40°-50°	346.2	10.6
50°-60°	301.9	9.3
60°-70°	223.1	6.8
70°-80°	126.3	3.9
80°-90°	34.1	1.0
90°-100°	14.7	0.5
100°-110°	54.8	1.7
110°-120°	145.3	4.5
120°-130°	240.9	7.4
130°-140°	255.9	7.9
140°-150°	237.8	7.3
150°-160°	191.2	5.9
160°-170°	123.2	3.8
170°-180°	42.4	1.3
0°-30°	573.7	17.6
0°-40°	920.3	28.2
0°-60°	1568.3	48.1
0°-90°	1951.8	59.9
90°-120°	214.7	6.6
90°-150°	949.4	29.1
90°-180°	1306.0	40.1
0°-180°	3258.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	767	764	756	762	760	73
15°	730	726	716	719	715	206
25°	661	655	642	644	642	304
35°	570	563	551	546	543	356
45°	464	459	448	440	436	358
55°	351	347	338	329	325	314
65°	237	232	225	218	215	234
75°	124	122	119	114	116	132
85°	30	30	29	26	26	34
90°	0	4	6	8	9	3
95°	21	10	13	14	14	25
105°	98	108	20	23	24	105
115°	185	191	199	50	26	183
125°	262	266	272	275	276	234
135°	324	330	332	336	335	251
145°	376	376	381	384	382	235
155°	414	411	415	417	415	191
165°	436	435	436	438	436	123
175°	446	444	445	447	444	42
180°	446	446	446	446	446	

TEST NUMBER: P1008094

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	766.9	766.9	766.9	766.9	766.9
2.5°	771.3	767.6	759.5	766.9	765.4
5°	766.9	763.9	755.8	761.7	760.2
7.5°	761.7	757.3	749.2	755.1	753.6
10°	753.6	748.4	739.6	745.5	743.3
12.5°	742.5	738.1	729.2	732.9	731.5
15°	730.0	725.6	716.0	718.9	715.2
17.5°	714.5	710.1	700.5	704.2	700.5
20°	697.5	693.1	682.8	685.0	682.1
22.5°	680.6	673.9	664.4	664.4	662.9
25°	660.7	654.8	642.2	643.7	642.2
27.5°	638.6	633.4	623.8	621.6	617.9
30°	616.4	610.5	599.5	597.3	594.3
32.5°	592.8	588.4	576.6	572.2	569.2
35°	570.0	562.6	550.8	546.4	542.7
37.5°	544.2	537.5	525.7	520.6	516.9
40°	517.6	511.7	499.9	493.3	490.3
42.5°	491.8	485.9	474.1	466.7	462.3
45°	463.8	458.6	447.6	439.5	436.5
47.5°	436.5	431.4	419.6	411.4	407.0
50°	407.8	404.1	393.8	383.4	379.7
52.5°	379.7	374.6	365.0	356.9	351.7
55°	351.0	346.6	337.7	328.9	325.2
57.5°	322.2	318.5	309.0	300.1	297.2
60°	293.5	290.5	280.2	272.1	269.9
62.5°	265.4	260.3	252.9	245.5	242.6
65°	236.7	232.3	224.9	218.3	214.6
67.5°	207.2	203.5	196.9	191.7	188.8
70°	179.9	177.0	170.3	165.2	162.2
72.5°	151.9	148.9	145.3	140.1	137.9
75°	123.9	122.4	118.7	114.3	115.8
77.5°	98.8	95.9	94.4	92.2	90.0
80°	73.7	73.0	71.5	69.3	67.8
82.5°	50.1	50.1	49.4	46.5	46.5
85°	30.2	29.5	28.8	26.5	25.8
87.5°	13.3	11.8	10.3	8.1	7.4
90°	0.3	3.9	6.4	8.1	8.7
92.5°	8.1	6.8	7.7	8.4	8.7
95°	21.0	10.3	12.6	14.2	13.9
97.5°	37.7	11.3	16.4	17.4	17.7
100°	57.1	12.9	18.4	21.0	21.6
102.5°	78.3	77.7	19.0	22.6	23.5
105°	98.0	107.7	19.7	23.2	24.5
107.5°	120.9	129.0	20.3	23.9	25.1
110°	142.8	149.6	56.4	24.2	25.5



TEST NUMBER: P1008094

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	163.5	169.3	163.8	24.8	25.8
115°	185.4	190.9	198.9	49.6	26.4
117.5°	204.4	210.8	216.3	170.2	85.8
120°	225.7	230.5	236.3	240.2	196.7
122.5°	243.7	248.9	255.3	257.3	257.6
125°	262.1	266.3	272.4	274.7	275.7
127.5°	278.9	283.4	288.2	291.4	291.8
130°	294.7	299.8	303.4	306.9	306.6
132.5°	310.8	315.0	318.5	321.4	321.1
135°	324.3	329.5	332.4	335.6	335.0
137.5°	338.5	342.4	345.6	348.8	347.9
140°	352.4	355.0	358.5	361.4	359.8
142.5°	364.0	366.2	370.4	373.0	371.4
145°	376.2	375.9	381.4	383.7	382.0
147.5°	386.9	385.9	391.4	393.0	391.7
150°	397.2	394.9	400.1	402.0	400.4
152.5°	405.9	403.3	408.2	410.1	407.8
155°	414.3	411.4	415.3	417.2	414.6
157.5°	421.1	418.5	421.4	423.6	421.1
160°	426.9	424.9	426.9	428.8	426.5
162.5°	432.0	430.1	431.7	434.0	431.0
165°	436.5	434.6	435.6	437.8	435.6
167.5°	440.1	438.1	439.1	441.4	438.5
170°	443.0	441.0	441.7	443.9	441.0
172.5°	444.9	443.0	443.6	445.9	443.0
175°	446.5	444.3	444.9	447.2	443.9
177.5°	447.2	444.9	445.2	447.5	444.6
180°	445.6	445.6	445.6	445.6	445.6

(END OF REPORT)