

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008105

Luminaire Tested: S122DIP-B485D530UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008105
REPORT IS A COMBINATION OF REPORTS P984253 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D530UB2750-4F0-XX-W2A-D_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4078.0 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008105

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008105

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	49	49	49
1	95	90	86	82	86	82	78	75	68	65	62	54	52	50	42	40	39	39	39	39
2	86	78	71	66	78	71	65	61	58	54	51	47	44	41	36	34	32	32	32	32
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	31	29	27	27	27	27
4	71	60	52	45	64	55	48	42	45	40	35	36	32	29	28	25	23	23	23	23
5	65	53	45	39	59	49	41	36	40	34	30	32	28	25	25	22	19	19	19	19
6	60	47	39	33	54	44	36	31	36	30	26	29	25	21	22	19	17	17	17	17
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	20	17	15	15	15	15
8	51	39	31	25	46	36	28	24	30	24	20	24	20	17	19	16	13	13	13	13
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12	12	12	12
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11	11	11	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8122	8122	8122
5°	8159	7775	7733
10°	8105	7506	7397
15°	7990	7228	7054
20°	7846	6935	6728
25°	7703	6655	6432
30°	7505	6371	6139
35°	7302	6097	5924
40°	7090	5859	5711
45°	6886	5643	5524
50°	6669	5445	5341
55°	6440	5234	5153
60°	6160	5015	4957
65°	5869	4763	4730
70°	5539	4492	4486
75°	5119	4221	4257
80°	4455	3940	4018
85°	3786	3674	3812

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6886 cd/sqm

TEST NUMBER: P1008105

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.6	1.2
10°-20°	139.5	3.4
20°-30°	211.4	5.2
30°-40°	257.4	6.3
40°-50°	277.0	6.8
50°-60°	269.0	6.6
60°-70°	234.9	5.8
70°-80°	180.8	4.4
80°-90°	122.4	3.0
90°-100°	107.4	2.6
100°-110°	149.9	3.7
110°-120°	275.9	6.8
120°-130°	413.2	10.1
130°-140°	424.5	10.4
140°-150°	387.4	9.5
150°-160°	310.2	7.6
160°-170°	199.9	4.9
170°-180°	68.8	1.7
0°-30°	399.6	9.8
0°-40°	657.0	16.1
0°-60°	1202.9	29.5
0°-90°	1741.0	42.7
90°-120°	533.1	13.1
90°-150°	1758.2	43.1
90°-180°	2337.0	57.3
0°-180°	4078.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	513	513	513	513	513	
5°	515	512	508	512	512	49
15°	491	492	492	499	498	138
25°	446	451	458	467	469	205
35°	384	397	411	428	433	240
45°	315	335	361	384	392	243
55°	242	268	307	334	344	216
65°	165	202	245	276	286	164
75°	92	133	181	213	222	97
85°	27	73	120	152	162	28
90°	8	57	109	141	151	7
95°	40	58	106	137	145	45
105°	163	200	96	128	138	174
115°	304	321	367	147	118	299
125°	427	434	467	491	499	381
135°	527	535	547	568	573	407
145°	610	610	619	627	628	382
155°	672	667	674	677	672	310
165°	708	705	706	710	706	200
175°	724	721	722	725	720	69
180°	723	723	723	723	723	

TEST NUMBER: P1008105

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	513.1	513.1	513.1	513.1	513.1
2.5°	516.9	514.6	509.4	513.1	511.7
5°	514.6	512.4	507.9	512.4	511.7
7.5°	510.9	509.4	505.7	510.9	510.2
10°	506.5	505.0	502.7	508.7	507.9
12.5°	499.0	499.8	498.3	504.2	503.5
15°	490.8	492.3	492.3	499.0	498.3
17.5°	480.4	483.4	485.6	492.3	492.3
20°	470.0	473.7	476.7	484.9	484.9
22.5°	458.9	463.3	467.8	476.0	477.5
25°	446.2	451.4	458.1	467.0	469.3
27.5°	431.3	439.5	447.0	458.1	459.6
30°	416.5	426.1	435.8	447.7	449.9
32.5°	400.1	411.3	423.2	437.3	441.8
35°	384.5	397.1	411.3	427.6	432.8
37.5°	367.4	381.5	399.4	417.2	422.4
40°	350.3	366.6	386.7	406.1	412.8
42.5°	333.9	350.3	374.1	395.6	402.3
45°	315.3	335.4	361.4	384.5	391.9
47.5°	297.5	319.0	348.8	372.6	380.8
50°	278.9	301.9	335.4	360.7	368.9
52.5°	261.0	285.6	321.3	347.3	356.2
55°	241.7	268.5	307.1	333.9	343.6
57.5°	223.1	252.9	291.5	320.5	330.2
60°	203.0	235.0	277.4	305.7	316.1
62.5°	185.2	218.6	261.0	291.5	301.2
65°	165.1	201.5	245.4	275.9	285.6
67.5°	147.3	185.2	229.8	260.3	270.7
70°	127.9	166.6	212.7	244.7	253.6
72.5°	110.1	150.2	197.1	228.3	239.5
75°	91.5	133.1	180.7	212.7	222.4
77.5°	73.6	116.8	165.1	197.1	207.5
80°	55.8	101.1	149.5	180.7	191.1
82.5°	40.9	85.5	134.6	165.8	175.5
85°	26.8	72.9	120.5	151.7	162.1
87.5°	16.4	61.0	108.6	139.1	148.7
90°	7.9	56.9	108.7	141.0	150.9
92.5°	19.8	57.1	104.1	134.1	143.5
95°	39.9	57.6	105.9	136.8	145.2
97.5°	66.4	55.5	107.0	136.0	145.6
100°	97.8	53.6	104.2	135.9	145.1
102.5°	131.6	155.0	100.1	132.5	142.3
105°	162.7	200.0	95.9	127.7	137.9
107.5°	199.8	230.8	91.7	122.7	133.0
110°	234.7	260.4	145.8	117.3	127.6

TEST NUMBER: P1008105

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	268.1	289.4	314.8	113.2	122.9
115°	303.7	320.8	367.3	147.4	118.0
117.5°	333.7	350.2	390.3	337.8	208.3
120°	368.3	379.1	418.3	445.4	383.0
122.5°	397.5	406.7	444.7	467.9	475.1
125°	426.7	433.5	467.2	490.9	499.2
127.5°	453.8	460.4	488.3	512.1	519.4
130°	479.5	487.0	508.5	532.0	537.5
132.5°	505.6	511.6	528.6	550.4	555.9
135°	526.8	535.1	547.4	568.2	573.0
137.5°	549.8	556.1	565.1	584.4	588.1
140°	572.3	575.8	583.0	599.6	601.4
142.5°	591.1	594.1	600.9	613.9	615.0
145°	610.3	609.8	618.6	626.8	627.9
147.5°	627.5	626.0	634.9	638.2	638.4
150°	644.3	640.6	649.0	652.1	649.5
152.5°	658.4	654.2	662.0	665.2	661.5
155°	672.0	667.3	673.6	676.7	672.5
157.5°	683.0	678.8	683.5	687.1	683.0
160°	692.4	689.2	692.4	695.5	691.9
162.5°	700.7	697.6	700.2	703.9	699.2
165°	708.1	704.9	706.5	710.2	706.5
167.5°	713.8	710.7	712.2	715.9	711.2
170°	718.5	715.4	716.4	720.1	715.4
172.5°	721.7	718.5	719.6	723.2	718.5
175°	724.3	720.6	721.7	725.3	720.1
177.5°	725.3	721.7	722.2	725.8	721.1
180°	722.7	722.7	722.7	722.7	722.7

(END OF REPORT)