

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008106

Luminaire Tested: S122DIP-B485D530UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008106
REPORT IS A COMBINATION OF REPORTS P984254 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D530UB2750-4F0-XX-W2A-D_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4096.0 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008106

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008106

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43		
1	95	90	86	82	86	82	78	75	68	65	62	54	52	50	42	40	39	33		
2	86	78	71	66	78	71	65	61	58	54	51	47	44	41	36	34	32	27		
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	31	29	27	22		
4	71	60	52	45	64	55	48	42	45	40	35	36	32	29	28	25	23	19		
5	65	53	45	39	59	49	41	36	40	34	30	32	28	25	25	22	19	16		
6	60	47	39	33	54	44	36	31	36	30	26	29	25	21	22	19	17	14		
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	20	17	15	12		
8	51	39	31	25	46	36	28	24	30	24	20	24	20	17	19	16	13	11		
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12	10		
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11	9		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8160	8160	8160
5°	8197	7812	7768
10°	8142	7541	7431
15°	8027	7262	7087
20°	7883	6968	6758
25°	7740	6686	6461
30°	7539	6400	6167
35°	7336	6125	5951
40°	7122	5886	5736
45°	6919	5670	5549
50°	6701	5470	5365
55°	6470	5260	5177
60°	6190	5039	4979
65°	5898	4784	4752
70°	5565	4513	4508
75°	5141	4240	4276
80°	4471	3958	4036
85°	3800	3690	3831

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6919 cd/sqm

TEST NUMBER: P1008106

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.9	1.2
10°-20°	140.2	3.4
20°-30°	212.4	5.2
30°-40°	258.6	6.3
40°-50°	278.2	6.8
50°-60°	270.2	6.6
60°-70°	236.0	5.8
70°-80°	181.6	4.4
80°-90°	122.9	3.0
90°-100°	107.9	2.6
100°-110°	150.5	3.7
110°-120°	277.1	6.8
120°-130°	415.0	10.1
130°-140°	426.3	10.4
140°-150°	389.0	9.5
150°-160°	311.5	7.6
160°-170°	200.7	4.9
170°-180°	69.1	1.7
0°-30°	401.4	9.8
0°-40°	660.0	16.1
0°-60°	1208.5	29.5
0°-90°	1749.0	42.7
90°-120°	535.4	13.1
90°-150°	1765.7	43.1
90°-180°	2347.0	57.3
0°-180°	4096.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	516	516	516	516	516	
5°	517	515	510	515	514	49
15°	493	495	495	501	501	139
25°	448	454	460	469	471	206
35°	386	399	413	430	435	241
45°	317	337	363	386	394	245
55°	243	270	309	336	345	217
65°	166	202	246	277	287	165
75°	92	134	182	214	223	97
85°	27	73	121	152	163	28
90°	8	57	109	142	152	7
95°	40	58	106	137	146	45
105°	163	201	96	128	138	175
115°	305	322	369	148	119	300
125°	428	435	469	493	501	382
135°	529	537	550	571	576	409
145°	613	612	621	629	630	383
155°	675	670	676	680	675	311
165°	711	708	710	713	710	201
175°	727	724	725	728	723	69
180°	726	726	726	726	726	

TEST NUMBER: P1008106

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	515.5	515.5	515.5	515.5	515.5
2.5°	519.2	517.0	511.8	515.5	514.0
5°	517.0	514.8	510.3	514.8	514.0
7.5°	513.3	511.8	508.0	513.3	512.5
10°	508.8	507.3	505.0	511.0	510.3
12.5°	501.3	502.1	500.6	506.5	505.8
15°	493.1	494.6	494.6	501.3	500.6
17.5°	482.6	485.6	487.9	494.6	494.6
20°	472.2	475.9	478.9	487.1	487.1
22.5°	461.0	465.5	469.9	478.2	479.6
25°	448.3	453.5	460.2	469.2	471.4
27.5°	433.3	441.5	449.0	460.2	461.7
30°	418.4	428.1	437.8	449.8	452.0
32.5°	401.9	413.2	425.1	439.3	443.8
35°	386.3	399.0	413.2	429.6	434.8
37.5°	369.1	383.3	401.2	419.1	424.4
40°	351.9	368.3	388.5	407.9	414.6
42.5°	335.5	351.9	375.8	397.5	404.2
45°	316.8	336.9	363.1	386.3	393.7
47.5°	298.8	320.5	350.4	374.3	382.5
50°	280.2	303.3	336.9	362.4	370.6
52.5°	262.2	286.9	322.8	348.9	357.9
55°	242.8	269.7	308.6	335.5	345.2
57.5°	224.1	254.0	292.9	322.0	331.7
60°	204.0	236.1	278.7	307.1	317.5
62.5°	186.0	219.7	262.2	292.9	302.6
65°	165.9	202.5	246.5	277.2	286.9
67.5°	147.9	186.0	230.9	261.5	271.9
70°	128.5	167.4	213.7	245.8	254.8
72.5°	110.6	150.9	198.0	229.4	240.6
75°	91.9	133.7	181.5	213.7	223.4
77.5°	74.0	117.3	165.9	198.0	208.4
80°	56.0	101.6	150.2	181.5	192.0
82.5°	41.1	85.9	135.2	166.6	176.3
85°	26.9	73.2	121.0	152.4	162.9
87.5°	16.4	61.3	109.1	139.7	149.4
90°	8.0	57.1	109.1	141.6	151.7
92.5°	19.8	57.3	104.5	134.7	144.2
95°	40.1	57.9	106.4	137.4	145.9
97.5°	66.6	55.8	107.5	136.7	146.2
100°	98.2	53.9	104.6	136.5	145.8
102.5°	132.1	155.7	100.5	133.2	142.9
105°	163.3	200.8	96.3	128.2	138.5
107.5°	200.6	231.8	92.1	123.3	133.6
110°	235.6	261.6	146.4	117.8	128.2

TEST NUMBER: P1008106

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.3	290.6	316.1	113.6	123.4
115°	305.0	322.1	368.8	148.1	118.6
117.5°	335.2	351.7	392.0	339.3	209.2
120°	369.8	380.7	420.0	447.2	384.7
122.5°	399.2	408.4	446.5	469.9	477.1
125°	428.5	435.3	469.2	493.0	501.3
127.5°	455.8	462.3	490.4	514.3	521.6
130°	481.5	489.1	510.6	534.4	539.7
132.5°	507.8	513.8	530.9	552.7	558.2
135°	529.0	537.4	549.6	570.6	575.5
137.5°	552.1	558.4	567.5	586.9	590.6
140°	574.7	578.2	585.5	602.1	604.0
142.5°	593.6	596.6	603.4	616.6	617.7
145°	612.9	612.3	621.3	629.4	630.5
147.5°	630.2	628.6	637.5	640.9	641.1
150°	647.0	643.3	651.7	654.9	652.3
152.5°	661.2	657.0	664.9	668.0	664.3
155°	674.8	670.1	676.4	679.6	675.4
157.5°	685.9	681.7	686.4	690.1	685.9
160°	695.3	692.2	695.3	698.5	694.8
162.5°	703.7	700.6	703.2	706.9	702.1
165°	711.1	707.9	709.5	713.2	709.5
167.5°	716.8	713.7	715.3	718.9	714.2
170°	721.6	718.4	719.5	723.2	718.4
172.5°	724.7	721.6	722.6	726.3	721.6
175°	727.4	723.7	724.7	728.4	723.2
177.5°	728.4	724.7	725.3	728.9	724.2
180°	725.8	725.8	725.8	725.8	725.8

(END OF REPORT)