

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001557

Luminaire Tested: SA4XXDIP-B575D365UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001557
REPORT IS A COMBINATION OF REPORTS P996179 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D365UB35-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3775.0 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001557

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001557

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	101	97	93	89	95	91	88	85	81	78	76	71	69	68	63	61	60
2	92	85	78	73	87	80	74	69	71	67	63	63	59	56	55	53	50
3	84	74	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	44	40	37
5	71	59	50	44	66	56	48	43	50	44	39	44	39	36	39	35	32
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	28
7	61	48	40	34	57	45	38	33	41	35	30	37	32	28	33	28	25
8	56	44	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7920	7920	7920
5°	7927	7692	7702
10°	7860	7479	7426
15°	7747	7225	7116
20°	7603	6951	6794
25°	7441	6660	6449
30°	7246	6347	6069
35°	7043	6026	5701
40°	6832	5680	5310
45°	6611	5333	4946
50°	6367	4997	4541
55°	6100	4605	4140
60°	5828	4175	3721
65°	5516	3730	3249
70°	5156	3196	2744
75°	4619	2575	2199
80°	3936	1862	1546
85°	3056	1038	832

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6611 cd/sqm

TEST NUMBER: P1001557

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	2.4
10°-20°	257.9	6.8
20°-30°	379.6	10.1
30°-40°	441.2	11.7
40°-50°	441.2	11.7
50°-60°	385.9	10.2
60°-70°	286.5	7.6
70°-80°	162.5	4.3
80°-90°	47.6	1.3
90°-100°	30.1	0.8
100°-110°	90.1	2.4
110°-120°	153.1	4.1
120°-130°	201.9	5.3
130°-140°	226.8	6.0
140°-150°	222.9	5.9
150°-160°	187.5	5.0
160°-170°	124.8	3.3
170°-180°	43.7	1.2
0°-30°	729.1	19.3
0°-40°	1170.3	31.0
0°-60°	1997.4	52.9
0°-90°	2494.0	66.1
90°-120°	273.3	7.2
90°-150°	925.1	24.5
90°-180°	1281.0	33.9
0°-180°	3775.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	921	909	914	911	260
25°	837	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	149	149	170
85°	42	42	40	40	40	45
90°	1	5	8	10	11	4
95°	21	25	27	28	28	23
105°	83	84	85	86	87	88
115°	156	156	155	155	154	154
125°	227	227	226	226	225	202
135°	292	295	295	294	293	226
145°	355	357	357	357	356	222
155°	407	407	407	408	407	187
165°	443	442	441	444	442	125
175°	461	459	459	461	459	44
180°	462	462	462	462	462	

TEST NUMBER: P1001557

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	971.3	971.3	971.3	971.3	971.3
2.5°	974.4	972.1	963.5	971.3	970.5
5°	970.5	967.4	958.8	967.4	965.8
7.5°	963.5	960.4	951.1	958.1	957.3
10°	953.4	950.3	940.2	946.4	944.8
12.5°	940.2	937.0	926.1	933.2	930.8
15°	923.8	920.7	909.0	913.7	911.4
17.5°	905.1	901.2	890.3	893.5	891.9
20°	884.1	880.2	868.6	870.9	869.3
22.5°	861.6	856.1	844.4	849.1	846.0
25°	836.6	831.2	820.3	821.1	818.0
27.5°	808.6	803.2	793.1	791.5	787.6
30°	780.6	774.4	764.3	761.2	757.3
32.5°	751.0	745.6	734.7	730.8	726.9
35°	719.9	714.5	703.6	698.1	694.2
37.5°	687.2	682.5	670.9	665.4	660.0
40°	655.3	649.1	637.4	629.6	625.7
42.5°	621.1	618.0	604.7	595.4	593.0
45°	587.6	582.2	569.7	561.1	558.8
47.5°	552.6	548.7	537.0	527.7	521.4
50°	516.8	513.7	502.8	491.9	487.2
52.5°	481.8	477.9	466.2	456.8	450.6
55°	444.4	442.1	431.2	421.8	417.2
57.5°	409.4	407.0	396.1	386.8	382.1
60°	372.8	368.9	358.8	351.8	347.9
62.5°	337.0	333.9	323.0	316.8	312.9
65°	301.2	297.3	289.5	281.7	277.8
67.5°	264.6	261.5	253.7	245.9	245.2
70°	231.1	225.7	219.5	213.2	210.9
72.5°	195.3	189.9	185.2	180.6	178.2
75°	160.3	156.4	152.5	149.4	148.7
77.5°	126.1	124.5	120.6	119.9	117.5
80°	95.7	93.4	91.8	90.3	89.5
82.5°	66.2	65.4	65.4	64.6	63.8
85°	42.0	42.0	40.5	40.5	39.7
87.5°	20.2	19.5	18.7	18.7	18.7
90°	1.1	5.0	7.9	10.0	10.7
92.5°	9.3	13.9	15.7	16.8	17.1
95°	21.4	24.6	27.1	28.2	28.2
97.5°	34.3	37.1	40.0	41.4	41.4
100°	50.0	51.4	54.6	55.3	55.3
102.5°	66.4	66.8	69.6	70.7	71.1
105°	83.2	83.6	85.0	86.1	87.1
107.5°	100.7	101.0	101.4	102.8	102.5
110°	118.5	119.3	118.9	118.2	119.3

TEST NUMBER: P1001557

CATALOG NUMBER: SA4XXDIP-B575D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	137.1	137.1	136.4	136.4	136.4
115°	155.7	155.7	155.0	154.6	154.3
117.5°	173.2	173.2	172.8	171.7	170.7
120°	190.7	192.1	191.0	189.2	190.0
122.5°	208.9	209.2	208.9	207.8	206.0
125°	226.7	226.7	226.4	225.7	225.0
127.5°	242.8	243.9	243.2	242.4	242.1
130°	259.9	261.0	261.0	260.3	258.9
132.5°	277.4	278.2	277.8	277.1	276.7
135°	292.4	294.6	294.6	293.9	292.8
137.5°	309.2	310.3	311.0	309.9	310.3
140°	326.0	326.7	326.7	326.4	326.0
142.5°	341.4	342.1	341.7	341.7	341.7
145°	355.3	356.7	357.1	356.7	355.6
147.5°	369.6	371.3	371.0	370.6	370.3
150°	382.4	383.8	383.8	383.8	383.5
152.5°	394.6	395.3	395.6	396.7	395.6
155°	407.1	407.1	406.7	408.1	406.7
157.5°	417.8	417.1	417.1	418.1	417.1
160°	427.1	426.7	426.3	427.4	425.6
162.5°	435.6	434.6	434.2	436.3	434.6
165°	443.1	442.0	441.3	443.5	442.0
167.5°	449.2	447.8	447.8	449.9	447.8
170°	454.2	452.4	452.8	454.9	452.4
172.5°	457.8	456.3	456.3	458.8	456.3
175°	461.0	459.2	458.8	461.3	458.8
177.5°	462.4	460.6	460.6	463.1	460.3
180°	461.7	461.7	461.7	461.7	461.7

(END OF REPORT)