

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008113

Luminaire Tested: S122DIP-B485D530UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008113
REPORT IS A COMBINATION OF REPORTS P984261 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D530UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3930.0 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008113

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008113

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33
4	74	63	55	49	68	58	52	46	50	44	40	41	37	34	34	31	28
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25
6	63	51	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19
8	54	41	34	28	49	38	32	27	33	28	24	28	24	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11772	11772	11772
5°	11791	11220	11141
10°	11695	10709	10497
15°	11524	10194	9819
20°	11291	9633	9177
25°	11061	9048	8536
30°	10771	8498	7863
35°	10497	7919	7203
40°	10160	7345	6579
45°	9824	6777	5966
50°	9455	6199	5332
55°	9070	5582	4729
60°	8636	4912	4104
65°	8159	4233	3447
70°	7557	3489	2783
75°	6718	2689	2149
80°	5708	1829	1383
85°	4139	851	588

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9824 cd/sqm

TEST NUMBER: P1008113

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.0	1.8
10°-20°	196.9	5.0
20°-30°	289.4	7.4
30°-40°	336.1	8.6
40°-50°	335.7	8.5
50°-60°	292.7	7.4
60°-70°	216.4	5.5
70°-80°	122.4	3.1
80°-90°	33.5	0.9
90°-100°	22.9	0.6
100°-110°	85.4	2.2
110°-120°	226.5	5.8
120°-130°	375.7	9.6
130°-140°	399.0	10.2
140°-150°	370.9	9.4
150°-160°	298.2	7.6
160°-170°	192.1	4.9
170°-180°	66.1	1.7
0°-30°	556.3	14.2
0°-40°	892.4	22.7
0°-60°	1520.9	38.7
0°-90°	1893.2	48.2
90°-120°	334.8	8.5
90°-150°	1480.4	37.7
90°-180°	2037.0	51.8
0°-180°	3930.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	744	744	744	744	744	
5°	744	741	733	739	737	71
15°	708	704	694	697	694	199
25°	641	635	623	624	623	295
35°	553	546	534	530	526	345
45°	450	445	434	426	423	347
55°	340	336	328	319	315	304
65°	230	225	218	212	208	227
75°	120	119	115	111	112	128
85°	29	29	28	26	25	33
90°	0	6	10	13	14	4
95°	33	16	20	22	22	39
105°	153	168	31	36	38	163
115°	289	298	310	77	41	285
125°	409	415	425	428	430	365
135°	506	514	518	523	522	391
145°	587	586	595	598	596	367
155°	646	642	648	650	646	298
165°	681	678	679	683	679	192
175°	696	693	694	697	692	66
180°	695	695	695	695	695	

TEST NUMBER: P1008113

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	743.7	743.7	743.7	743.7	743.7
2.5°	748.0	744.4	736.5	743.7	742.2
5°	743.7	740.8	732.9	738.7	737.2
7.5°	738.7	734.4	726.5	732.2	730.8
10°	730.8	725.8	717.2	722.9	720.8
12.5°	720.1	715.8	707.2	710.8	709.3
15°	707.9	703.6	694.3	697.2	693.6
17.5°	692.9	688.6	679.3	682.9	679.3
20°	676.4	672.2	662.1	664.3	661.4
22.5°	660.0	653.6	644.3	644.3	642.8
25°	640.7	635.0	622.8	624.2	622.8
27.5°	619.2	614.2	604.9	602.8	599.2
30°	597.8	592.1	581.3	579.2	576.3
32.5°	574.9	570.6	559.2	554.9	552.0
35°	552.7	545.6	534.2	529.9	526.3
37.5°	527.7	521.3	509.8	504.8	501.3
40°	502.0	496.3	484.8	478.4	475.5
42.5°	476.9	471.2	459.8	452.6	448.3
45°	449.8	444.8	434.0	426.2	423.3
47.5°	423.3	418.3	406.9	399.0	394.7
50°	395.4	391.9	381.8	371.8	368.3
52.5°	368.3	363.3	354.0	346.1	341.1
55°	340.4	336.1	327.5	318.9	315.3
57.5°	312.5	308.9	299.6	291.0	288.2
60°	284.6	281.7	271.7	263.9	261.7
62.5°	257.4	252.4	245.3	238.1	235.3
65°	229.5	225.2	218.1	211.7	208.1
67.5°	200.9	197.4	190.9	185.9	183.1
70°	174.5	171.6	165.2	160.2	157.3
72.5°	147.3	144.4	140.9	135.9	133.7
75°	120.1	118.7	115.1	110.8	112.3
77.5°	95.8	93.0	91.5	89.4	87.2
80°	71.5	70.8	69.4	67.2	65.8
82.5°	48.6	48.6	47.9	45.0	45.0
85°	29.3	28.6	27.9	25.7	25.0
87.5°	12.9	11.4	10.0	7.9	7.2
90°	0.5	6.0	10.1	12.6	13.6
92.5°	12.6	10.6	12.1	13.1	13.6
95°	32.7	16.1	19.6	22.1	21.6
97.5°	58.8	17.6	25.6	27.1	27.6
100°	89.0	20.1	28.7	32.7	33.7
102.5°	122.2	121.2	29.7	35.2	36.7
105°	152.8	167.9	30.7	36.2	38.2
107.5°	188.5	201.1	31.7	37.2	39.2
110°	222.7	233.3	88.0	37.7	39.7



TEST NUMBER: P1008113

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	254.9	263.9	255.4	38.7	40.2
115°	289.1	297.6	310.2	77.4	41.2
117.5°	318.7	328.8	337.3	265.4	133.7
120°	351.9	359.4	368.5	374.5	306.7
122.5°	380.1	388.1	398.2	401.2	401.7
125°	408.7	415.2	424.8	428.3	429.8
127.5°	434.9	441.9	449.4	454.5	455.0
130°	459.5	467.5	473.1	478.6	478.1
132.5°	484.6	491.2	496.7	501.2	500.7
135°	505.7	513.8	518.3	523.3	522.3
137.5°	527.9	533.9	538.9	543.9	542.4
140°	549.5	553.5	559.0	563.5	561.0
142.5°	567.6	571.1	577.6	581.6	579.1
145°	586.7	586.2	594.7	598.2	595.7
147.5°	603.3	601.8	610.3	612.8	610.8
150°	619.3	615.8	623.9	626.9	624.4
152.5°	632.9	628.9	636.4	639.5	635.9
155°	646.0	641.5	647.5	650.5	646.5
157.5°	656.5	652.5	657.1	660.6	656.5
160°	665.6	662.6	665.6	668.6	665.1
162.5°	673.6	670.6	673.1	676.7	672.1
165°	680.7	677.7	679.2	682.7	679.2
167.5°	686.2	683.2	684.7	688.2	683.7
170°	690.7	687.7	688.7	692.2	687.7
172.5°	693.7	690.7	691.7	695.3	690.7
175°	696.3	692.7	693.7	697.3	692.2
177.5°	697.3	693.7	694.3	697.8	693.2
180°	694.8	694.8	694.8	694.8	694.8

(END OF REPORT)