

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001571

Luminaire Tested: SA4XXDIP-B575D365UB50-4F0-XX-W2A-D

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001571
REPORT IS A COMBINATION OF REPORTS P996193 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D365UB50-4F0-XX-W2A-D
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3684.0 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001571

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-D

Luminous Intensity Polar Plot



TEST NUMBER: P1001571

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63
1	98	93	89	85	91	87	83	80	75	72	69	64	62	60	53	52	51
2	89	81	74	68	82	75	69	64	65	60	56	55	52	49	46	44	42
3	81	71	63	56	75	66	59	53	57	51	47	48	44	41	41	38	35
4	74	62	54	47	68	58	51	45	50	44	40	43	38	35	36	33	30
5	68	55	47	40	63	52	44	38	45	39	34	38	34	30	32	29	26
6	62	50	41	35	58	46	39	33	40	34	29	35	30	26	29	25	22
7	58	45	36	31	53	42	34	29	36	30	26	31	27	23	27	23	20
8	53	41	32	27	49	38	31	26	33	27	23	29	24	20	24	21	18
9	50	37	29	24	46	35	28	23	30	25	20	26	22	18	23	19	16
10	46	34	26	21	43	32	25	20	28	22	18	24	20	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5427	5427	5427
5°	5442	5285	5295
10°	5406	5182	5167
15°	5356	5065	5022
20°	5281	4938	4881
25°	5197	4798	4729
30°	5105	4660	4575
35°	5001	4518	4437
40°	4918	4383	4294
45°	4796	4255	4168
50°	4691	4111	4036
55°	4583	3972	3883
60°	4416	3798	3738
65°	4230	3611	3565
70°	4007	3397	3364
75°	3694	3160	3173
80°	3340	2916	2975
85°	2874	2673	2811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4796 cd/sqm

TEST NUMBER: P1001571

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	1.7
10°-20°	180.7	4.9
20°-30°	273.2	7.4
30°-40°	330.5	9.0
40°-50°	349.4	9.5
50°-60°	328.8	8.9
60°-70°	272.9	7.4
70°-80°	191.5	5.2
80°-90°	108.9	3.0
90°-100°	79.4	2.2
100°-110°	147.5	4.0
110°-120°	222.7	6.0
120°-130°	260.2	7.1
130°-140°	266.8	7.2
140°-150°	243.8	6.6
150°-160°	195.4	5.3
160°-170°	126.0	3.4
170°-180°	43.4	1.2
0°-30°	516.9	14.0
0°-40°	847.4	23.0
0°-60°	1525.6	41.4
0°-90°	2098.9	57.0
90°-120°	449.6	12.2
90°-150°	1220.4	33.1
90°-180°	1585.0	43.0
0°-180°	3684.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	666	666	666	666	666	
5°	666	664	659	665	664	63
15°	639	639	637	644	643	180
25°	584	589	591	599	600	269
35°	511	520	528	538	540	320
45°	426	440	455	467	471	329
55°	334	350	372	387	391	298
65°	231	255	280	299	305	229
75°	128	156	187	208	215	136
85°	40	71	104	127	134	41
90°	13	46	81	105	112	9
95°	28	42	72	95	102	31
105°	110	126	156	178	171	115
115°	197	204	228	245	250	194
125°	273	274	292	307	312	244
135°	336	336	343	355	360	259
145°	387	387	387	392	396	242
155°	424	424	423	424	423	195
165°	447	445	445	448	445	126
175°	457	455	455	458	454	44
180°	457	457	457	457	457	

TEST NUMBER: P1001571

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-D

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	665.5	665.5	665.5	665.5	665.5
2.5°	668.5	666.3	660.3	665.5	664.8
5°	666.3	664.0	658.8	664.8	664.0
7.5°	661.8	660.3	655.8	662.5	661.8
10°	655.8	655.1	651.4	658.1	657.3
12.5°	647.6	647.6	645.4	651.4	651.4
15°	638.7	639.4	637.2	643.9	643.2
17.5°	626.8	629.0	628.2	635.0	634.2
20°	614.1	616.3	617.1	624.5	624.5
22.5°	599.9	602.9	604.4	611.9	613.3
25°	584.3	588.7	591.0	599.2	599.9
27.5°	567.1	573.8	576.8	584.3	585.0
30°	550.0	556.0	561.2	569.4	570.9
32.5°	531.4	538.8	544.8	554.5	556.0
35°	511.2	520.2	527.6	538.1	540.3
37.5°	491.1	501.6	510.5	520.9	523.2
40°	471.7	481.4	491.9	503.0	506.0
42.5°	449.4	460.6	473.2	485.9	488.1
45°	426.3	440.4	454.6	467.3	471.0
47.5°	404.7	418.8	435.2	447.9	452.4
50°	380.8	397.2	413.6	428.5	433.0
52.5°	357.0	373.4	392.7	407.7	412.1
55°	333.9	349.5	371.9	386.8	391.3
57.5°	307.8	327.2	348.8	366.7	370.4
60°	282.5	301.8	326.4	343.6	349.5
62.5°	257.9	279.5	304.1	321.2	327.2
65°	231.0	254.9	280.2	298.8	304.8
67.5°	205.7	231.0	257.9	276.5	282.5
70°	179.6	204.9	233.3	253.4	258.6
72.5°	154.3	180.4	210.9	230.3	236.2
75°	128.2	155.8	187.1	207.9	214.6
77.5°	103.6	132.7	165.4	186.3	193.8
80°	81.2	111.0	143.8	166.2	172.2
82.5°	58.9	90.2	123.0	146.1	152.8
85°	39.5	70.8	104.3	126.7	134.1
87.5°	24.6	55.1	87.9	109.6	116.3
90°	12.9	46.5	81.3	105.0	111.7
92.5°	16.3	41.7	76.5	99.4	105.3
95°	28.5	41.5	72.3	94.6	101.6
97.5°	44.8	74.0	68.6	89.7	96.8
100°	64.3	89.8	71.6	86.0	91.6
102.5°	86.8	107.3	139.7	82.2	88.2
105°	109.6	126.5	155.8	177.5	171.2
107.5°	131.8	145.5	174.0	194.3	200.9
110°	153.7	165.1	193.2	211.0	218.0

TEST NUMBER: P1001571

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-D

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.7	185.8	211.1	227.0	234.4
115°	196.6	204.3	227.8	244.9	250.1
117.5°	216.8	222.5	245.9	261.3	267.2
120°	236.5	240.1	261.4	277.0	282.2
122.5°	255.6	256.3	277.1	292.4	296.9
125°	273.0	273.6	291.6	306.7	311.6
127.5°	290.4	290.0	306.6	319.8	324.6
130°	306.4	306.0	319.0	332.7	337.2
132.5°	321.8	321.8	332.0	345.1	349.2
135°	336.5	336.1	342.7	355.3	360.5
137.5°	350.1	349.3	354.0	365.9	369.3
140°	363.5	363.3	364.8	375.6	379.6
142.5°	374.6	376.0	375.6	384.5	387.5
145°	386.9	387.3	387.3	392.1	395.8
147.5°	396.5	397.8	397.5	398.5	401.9
150°	407.1	407.8	407.4	407.4	407.8
152.5°	415.3	416.3	415.6	416.3	416.0
155°	423.5	423.8	422.8	424.2	423.1
157.5°	430.7	430.7	429.3	431.0	429.3
160°	436.8	435.8	435.4	437.5	435.4
162.5°	442.3	440.9	440.6	442.6	440.2
165°	446.7	445.0	445.0	447.8	444.7
167.5°	450.5	448.8	448.4	451.5	448.1
170°	453.6	451.5	451.9	454.6	451.2
172.5°	455.6	453.6	453.9	456.6	452.9
175°	457.0	454.9	455.3	458.3	454.2
177.5°	458.0	455.6	456.3	459.0	454.9
180°	457.0	457.0	457.0	457.0	457.0

(END OF REPORT)