

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001576

Luminaire Tested: SA4XXDIP-B575D365UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001576
REPORT IS A COMBINATION OF REPORTS P996198 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D365UB50-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3657.5 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001576

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001576

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70
1	101	97	93	89	95	91	88	84	81	78	75	71	69	67	62	61	59
2	92	84	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42
4	77	66	58	51	72	62	55	49	55	50	45	49	44	41	43	40	37
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28
7	60	48	40	34	57	45	38	33	41	35	30	36	31	27	32	28	25
8	56	43	36	30	53	41	34	29	37	31	27	33	28	25	30	26	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7584	7584	7584
5°	7589	7366	7375
10°	7526	7161	7111
15°	7417	6918	6813
20°	7280	6655	6506
25°	7125	6377	6174
30°	6937	6077	5811
35°	6744	5769	5459
40°	6541	5438	5085
45°	6330	5106	4735
50°	6095	4785	4348
55°	5841	4408	3963
60°	5579	3997	3563
65°	5282	3572	3111
70°	4937	3059	2627
75°	4424	2467	2104
80°	3771	1783	1480
85°	2925	992	797

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6330 cd/sqm

TEST NUMBER: P1001576

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	2.4
10°-20°	247.0	6.8
20°-30°	363.4	9.9
30°-40°	422.5	11.6
40°-50°	422.5	11.6
50°-60°	369.5	10.1
60°-70°	274.3	7.5
70°-80°	155.6	4.3
80°-90°	45.2	1.2
90°-100°	129.3	3.5
100°-110°	262.9	7.2
110°-120°	234.3	6.4
120°-130°	196.8	5.4
130°-140°	164.2	4.5
140°-150°	125.4	3.4
150°-160°	88.2	2.4
160°-170°	51.9	1.4
170°-180°	16.9	0.5
0°-30°	698.1	19.1
0°-40°	1120.5	30.6
0°-60°	1912.5	52.3
0°-90°	2387.7	65.3
90°-120°	626.5	17.1
90°-150°	1113.0	30.4
90°-180°	1270.0	34.7
0°-180°	3657.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	930	930	930	930	930	
5°	929	926	918	926	925	88
15°	884	882	870	875	873	249
25°	801	796	785	786	783	369
35°	689	684	674	668	665	431
45°	563	557	546	537	535	434
55°	426	423	413	404	399	381
65°	288	285	277	270	266	285
75°	154	150	146	143	142	163
85°	40	40	39	39	38	43
90°	0	3	6	7	7	3
95°	11	36	279	138	83	12
105°	40	58	224	483	481	43
115°	70	88	200	384	462	70
125°	98	117	199	327	368	87
135°	117	139	197	290	330	90
145°	134	154	196	245	269	84
155°	153	165	191	216	225	70
165°	166	172	183	194	197	47
175°	174	174	175	178	177	16
180°	174	174	174	174	174	

TEST NUMBER: P1001576

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	930.0	930.0	930.0	930.0	930.0
2.5°	933.0	930.7	922.5	930.0	929.2
5°	929.2	926.3	918.1	926.3	924.8
7.5°	922.5	919.6	910.6	917.3	916.6
10°	912.9	909.9	900.2	906.1	904.7
12.5°	900.2	897.2	886.8	893.5	891.2
15°	884.5	881.6	870.4	874.8	872.6
17.5°	866.6	862.9	852.5	855.5	854.0
20°	846.5	842.8	831.6	833.9	832.4
22.5°	824.9	819.7	808.5	813.0	810.0
25°	801.1	795.9	785.4	786.2	783.2
27.5°	774.2	769.0	759.3	757.9	754.1
30°	747.4	741.5	731.8	728.8	725.1
32.5°	719.1	713.9	703.5	699.7	696.0
35°	689.3	684.1	673.6	668.4	664.7
37.5°	658.0	653.5	642.3	637.1	631.9
40°	627.4	621.5	610.3	602.9	599.1
42.5°	594.7	591.7	579.0	570.1	567.8
45°	562.6	557.4	545.5	537.3	535.0
47.5°	529.1	525.4	514.2	505.2	499.3
50°	494.8	491.8	481.4	471.0	466.5
52.5°	461.3	457.5	446.4	437.4	431.5
55°	425.5	423.3	412.8	403.9	399.4
57.5°	392.0	389.7	379.3	370.4	365.9
60°	356.9	353.2	343.5	336.8	333.1
62.5°	322.7	319.7	309.3	303.3	299.6
65°	288.4	284.7	277.2	269.8	266.0
67.5°	253.4	250.4	242.9	235.5	234.7
70°	221.3	216.1	210.1	204.2	201.9
72.5°	187.0	181.8	177.4	172.9	170.6
75°	153.5	149.8	146.1	143.1	142.3
77.5°	120.7	119.2	115.5	114.8	112.5
80°	91.7	89.4	87.9	86.4	85.7
82.5°	63.3	62.6	62.6	61.9	61.1
85°	40.2	40.2	38.7	38.7	38.0
87.5°	19.4	18.6	17.9	17.9	17.9
90°	0.3	2.7	6.2	6.8	7.2
92.5°	4.8	26.4	134.0	44.2	31.1
95°	11.3	35.6	278.6	138.0	83.4
97.5°	18.8	39.4	298.1	281.6	200.3
100°	26.0	44.4	274.9	389.8	313.5
102.5°	32.8	50.6	245.8	457.4	411.9
105°	40.0	58.0	224.3	482.9	481.0
107.5°	47.9	65.4	210.2	475.2	513.8
110°	55.7	73.0	203.7	447.8	514.5



TEST NUMBER: P1001576

CATALOG NUMBER: SA4XXDIP-B575D365UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	63.2	80.5	200.7	414.3	494.3
115°	70.4	88.4	200.0	384.2	461.8
117.5°	77.9	95.7	199.6	360.6	430.1
120°	85.5	102.9	199.6	344.8	404.1
122.5°	92.3	109.9	199.3	334.4	383.6
125°	98.1	116.6	199.0	327.0	368.5
127.5°	103.6	122.7	198.3	320.0	358.9
130°	108.0	128.8	197.9	311.6	350.7
132.5°	112.5	133.8	197.6	301.6	341.5
135°	116.6	138.8	197.3	290.2	329.5
137.5°	120.7	143.0	197.3	278.0	315.5
140°	125.1	147.0	196.9	266.0	300.1
142.5°	129.9	150.6	196.9	254.8	283.7
145°	134.3	153.8	196.2	244.8	269.0
147.5°	139.5	156.9	195.2	236.4	255.4
150°	144.3	159.8	194.2	228.7	244.1
152.5°	148.7	162.6	192.5	222.2	233.8
155°	152.8	165.0	190.8	216.0	225.3
157.5°	156.9	167.1	189.0	210.2	217.4
160°	160.7	169.0	187.0	204.4	210.2
162.5°	164.1	170.6	184.9	198.8	203.4
165°	166.5	171.6	182.9	193.6	196.6
167.5°	169.2	172.4	180.8	189.2	191.1
170°	170.9	173.1	178.8	184.8	186.0
172.5°	172.6	173.6	176.7	180.8	180.8
175°	173.7	174.0	175.4	177.8	177.1
177.5°	174.3	174.0	174.3	175.6	174.3
180°	174.0	174.0	174.0	174.0	174.0

(END OF REPORT)