

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008122

Luminaire Tested: S122DIP-B485D725UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008122
REPORT IS A COMBINATION OF REPORTS P984315 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB2750-4F0-XX-W2A-D_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4763.0 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008122

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008122

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	94	89	85	81	84	80	77	74	65	62	60	50	48	47	37	36	35
2	85	77	71	65	76	70	64	59	56	52	49	43	41	38	32	30	28
3	77	67	60	54	69	61	54	49	49	44	40	38	35	32	28	25	24
4	70	59	51	45	63	54	47	41	43	38	34	34	30	27	25	22	20
5	64	53	44	38	58	48	40	35	39	33	29	30	26	23	22	19	17
6	59	47	39	33	53	43	35	30	35	29	25	27	23	20	20	17	15
7	55	42	34	29	49	38	31	26	31	26	22	24	20	18	18	15	13
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	17	14	12
9	47	35	27	22	42	32	25	20	26	21	17	20	17	14	15	13	11
10	44	32	24	20	39	29	23	18	24	19	15	19	15	12	14	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8078	8078	8078
5°	8113	7733	7689
10°	8059	7464	7356
15°	7946	7188	7014
20°	7802	6896	6690
25°	7660	6618	6395
30°	7461	6336	6104
35°	7260	6063	5891
40°	7049	5826	5678
45°	6849	5612	5493
50°	6631	5415	5310
55°	6403	5205	5125
60°	6127	4986	4929
65°	5837	4736	4704
70°	5509	4467	4462
75°	5091	4198	4232
80°	4431	3916	3996
85°	3757	3653	3791

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6849 cd/sqm

TEST NUMBER: P1008122

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	1.0
10°-20°	138.7	2.9
20°-30°	210.2	4.4
30°-40°	256.0	5.4
40°-50°	275.4	5.8
50°-60°	267.5	5.6
60°-70°	233.6	4.9
70°-80°	179.8	3.8
80°-90°	122.1	2.6
90°-100°	114.7	2.4
100°-110°	178.7	3.8
110°-120°	353.0	7.4
120°-130°	541.4	11.4
130°-140°	560.7	11.8
140°-150°	514.0	10.8
150°-160°	412.0	8.6
160°-170°	265.5	5.6
170°-180°	91.4	1.9
0°-30°	397.3	8.3
0°-40°	653.3	13.7
0°-60°	1196.2	25.1
0°-90°	1731.6	36.4
90°-120°	646.5	13.6
90°-150°	2262.6	47.5
90°-180°	3031.0	63.6
0°-180°	4763.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	510	510	510	510	510	
5°	512	510	505	510	509	49
15°	488	490	490	496	496	137
25°	444	449	456	464	467	204
35°	382	395	409	425	430	239
45°	314	334	359	382	390	242
55°	240	267	305	332	342	215
65°	164	200	244	274	284	163
75°	91	132	180	212	221	96
85°	27	72	120	151	161	28
90°	8	59	112	145	155	8
95°	51	63	112	144	152	58
105°	215	257	106	140	150	230
115°	402	422	473	174	132	396
125°	566	575	612	637	646	505
135°	700	711	724	747	751	541
145°	811	810	822	831	831	507
155°	893	886	895	899	893	411
165°	940	936	938	943	938	266
175°	962	957	959	963	956	92
180°	960	960	960	960	960	

TEST NUMBER: P1008122

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	510.3	510.3	510.3	510.3	510.3
2.5°	514.0	511.7	506.6	510.3	508.8
5°	511.7	509.5	505.1	509.5	508.8
7.5°	508.0	506.6	502.9	508.0	507.3
10°	503.6	502.1	499.9	505.8	505.1
12.5°	496.2	497.0	495.5	501.4	500.7
15°	488.1	489.6	489.6	496.2	495.5
17.5°	477.7	480.7	482.9	489.6	489.6
20°	467.4	471.1	474.0	482.2	482.2
22.5°	456.3	460.7	465.2	473.3	474.8
25°	443.7	448.9	455.5	464.4	466.6
27.5°	428.9	437.1	444.4	455.5	457.0
30°	414.1	423.7	433.4	445.2	447.4
32.5°	397.9	409.0	420.8	434.8	439.3
35°	382.3	394.9	409.0	425.2	430.4
37.5°	365.3	379.4	397.1	414.9	420.0
40°	348.3	364.6	384.5	403.8	410.4
42.5°	332.0	348.3	372.0	393.4	400.1
45°	313.6	333.5	359.4	382.3	389.7
47.5°	295.8	317.3	346.8	370.5	378.6
50°	277.3	300.2	333.5	358.7	366.8
52.5°	259.6	284.0	319.5	345.4	354.2
55°	240.3	267.0	305.4	332.0	341.7
57.5°	221.9	251.4	289.9	318.7	328.3
60°	201.9	233.7	275.8	303.9	314.3
62.5°	184.1	217.4	259.6	289.9	299.5
65°	164.2	200.4	244.0	274.4	284.0
67.5°	146.4	184.1	228.5	258.8	269.2
70°	127.2	165.7	211.5	243.3	252.2
72.5°	109.4	149.4	196.0	227.0	238.1
75°	91.0	132.4	179.7	211.5	221.1
77.5°	73.2	116.1	164.2	196.0	206.3
80°	55.5	100.6	148.6	179.7	190.1
82.5°	40.7	85.0	133.9	164.9	174.5
85°	26.6	72.5	119.8	150.9	161.2
87.5°	16.3	60.6	108.0	138.3	147.9
90°	8.1	58.6	111.5	144.6	154.9
92.5°	24.1	60.5	107.7	137.9	147.5
95°	51.1	62.9	112.1	143.7	151.9
97.5°	86.5	61.3	115.3	144.7	154.3
100°	128.1	60.3	113.6	146.5	155.9
102.5°	173.2	196.2	109.8	144.0	154.2
105°	214.9	257.1	106.0	139.5	150.4
107.5°	264.2	299.3	102.2	135.0	145.9
110°	310.7	340.0	175.6	129.7	140.7

TEST NUMBER: P1008122

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.2	379.5	401.7	126.0	136.2
115°	402.4	422.3	473.0	173.6	131.7
117.5°	442.6	462.4	505.3	428.2	253.6
120°	488.4	501.9	544.0	573.0	487.3
122.5°	527.3	539.3	580.4	604.6	611.9
125°	566.2	575.3	612.1	636.9	645.7
127.5°	602.4	611.3	641.7	667.1	674.5
130°	636.4	646.7	669.9	695.3	700.5
132.5°	671.1	679.4	698.1	721.3	726.6
135°	699.5	710.6	724.3	746.8	751.3
137.5°	730.1	738.4	749.0	770.1	773.2
140°	759.9	764.8	773.9	792.0	792.9
142.5°	784.9	789.1	798.1	812.6	812.8
145°	810.6	809.9	821.7	831.0	831.2
147.5°	833.6	831.5	843.3	847.5	847.0
150°	855.8	850.9	862.0	866.2	862.7
152.5°	874.5	869.0	879.4	883.6	878.7
155°	892.6	886.3	894.7	898.8	893.3
157.5°	907.2	901.6	907.9	912.7	907.2
160°	919.7	915.5	919.7	923.9	919.0
162.5°	930.8	926.6	930.1	935.0	928.7
165°	940.5	936.4	938.4	943.3	938.4
167.5°	948.2	944.0	946.1	950.9	944.7
170°	954.4	950.3	951.6	956.5	950.3
172.5°	958.6	954.4	955.8	960.7	954.4
175°	962.1	957.2	958.6	963.4	956.5
177.5°	963.4	958.6	959.3	964.1	957.9
180°	960.0	960.0	960.0	960.0	960.0

(END OF REPORT)