

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001581

Luminaire Tested: SA4XXDIP-B575D590UB27-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001581
REPORT IS A COMBINATION OF REPORTS P996203 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D590UB27-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4373.0 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001581

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001581

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	97	92	88	84	89	85	81	78	71	69	66	59	57	55	48	46	45
2	88	80	73	68	80	73	68	63	62	58	54	51	48	45	41	39	37
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	36	33	31
4	73	61	53	47	67	57	49	44	48	42	38	40	36	32	32	29	26
5	67	55	46	40	61	50	43	37	43	37	32	36	31	28	29	26	23
6	61	49	40	34	56	45	38	32	38	33	28	32	27	24	26	23	20
7	57	44	36	30	52	41	33	28	35	29	25	29	25	21	24	20	18
8	52	40	32	26	48	37	30	25	32	26	22	27	22	19	22	18	16
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	17	14
10	46	33	26	21	42	31	24	20	27	21	17	22	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5594	5594	5594
5°	5610	5448	5458
10°	5574	5341	5326
15°	5521	5220	5177
20°	5444	5090	5032
25°	5357	4946	4875
30°	5263	4804	4716
35°	5156	4658	4574
40°	5070	4518	4427
45°	4944	4387	4297
50°	4836	4238	4161
55°	4725	4094	4002
60°	4552	3915	3854
65°	4362	3723	3675
70°	4130	3502	3469
75°	3807	3256	3272
80°	3442	3008	3066
85°	2962	2757	2899

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4944 cd/sqm

TEST NUMBER: P1001581

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	1.5
10°-20°	186.2	4.3
20°-30°	281.6	6.4
30°-40°	340.7	7.8
40°-50°	360.2	8.2
50°-60°	339.0	7.8
60°-70°	281.3	6.4
70°-80°	197.4	4.5
80°-90°	112.9	2.6
90°-100°	114.0	2.6
100°-110°	192.1	4.4
110°-120°	275.9	6.3
120°-130°	338.9	7.8
130°-140°	367.9	8.4
140°-150°	355.3	8.1
150°-160°	297.5	6.8
160°-170°	197.9	4.5
170°-180°	69.3	1.6
0°-30°	532.8	12.2
0°-40°	873.5	20.0
0°-60°	1572.7	36.0
0°-90°	2164.2	49.5
90°-120°	581.9	13.3
90°-150°	1644.1	37.6
90°-180°	2209.0	50.5
0°-180°	4373.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	686	686	686	686	686	
5°	687	684	679	685	684	65
15°	658	659	657	664	663	186
25°	602	607	609	618	618	277
35°	527	536	544	555	557	330
45°	439	454	469	482	486	340
55°	344	360	383	399	403	307
65°	238	263	289	308	314	236
75°	132	161	193	214	221	140
85°	41	73	108	131	138	42
90°	14	51	89	114	122	11
95°	44	74	110	132	139	45
105°	139	155	186	206	214	148
115°	252	258	282	298	303	248
125°	363	362	381	394	398	324
135°	466	469	474	485	488	360
145°	564	566	566	570	572	353
155°	646	646	645	648	645	297
165°	703	701	700	704	701	198
175°	731	728	728	732	728	69
180°	732	732	732	732	732	

TEST NUMBER: P1001581

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	686.0	686.0	686.0	686.0	686.0
2.5°	689.1	686.8	680.7	686.0	685.3
5°	686.8	684.5	679.1	685.3	684.5
7.5°	682.2	680.7	676.1	683.0	682.2
10°	676.1	675.3	671.4	678.4	677.6
12.5°	667.6	667.6	665.3	671.4	671.4
15°	658.4	659.2	656.8	663.8	663.0
17.5°	646.1	648.4	647.6	654.5	653.8
20°	633.0	635.3	636.1	643.8	643.8
22.5°	618.4	621.5	623.0	630.7	632.3
25°	602.3	606.9	609.2	617.7	618.4
27.5°	584.6	591.5	594.6	602.3	603.1
30°	567.0	573.1	578.5	586.9	588.5
32.5°	547.8	555.4	561.6	571.6	573.1
35°	527.0	536.2	543.9	554.7	557.0
37.5°	506.3	517.0	526.2	537.0	539.3
40°	486.3	496.3	507.0	518.6	521.6
42.5°	463.3	474.8	487.8	500.9	503.2
45°	439.4	454.0	468.6	481.7	485.5
47.5°	417.2	431.8	448.7	461.7	466.3
50°	392.6	409.5	426.4	441.7	446.4
52.5°	368.0	384.9	404.9	420.2	424.8
55°	344.2	360.3	383.4	398.7	403.3
57.5°	317.3	337.3	359.5	378.0	381.8
60°	291.2	311.1	336.5	354.2	360.3
62.5°	265.8	288.1	313.4	331.1	337.3
65°	238.2	262.7	288.9	308.1	314.2
67.5°	212.0	238.2	265.8	285.0	291.2
70°	185.1	211.3	240.5	261.2	266.6
72.5°	159.0	185.9	217.4	237.4	243.5
75°	132.1	160.6	192.8	214.3	221.3
77.5°	106.8	136.7	170.6	192.1	199.7
80°	83.7	114.5	148.3	171.3	177.5
82.5°	60.7	93.0	126.8	150.6	157.5
85°	40.7	73.0	107.6	130.6	138.3
87.5°	25.4	56.9	90.7	112.9	119.8
90°	14.0	50.9	88.6	114.2	121.5
92.5°	26.2	60.5	96.3	119.6	126.3
95°	44.0	74.4	109.9	132.4	139.3
97.5°	63.6	90.4	126.4	148.7	155.6
100°	87.8	110.0	145.1	166.9	172.3
102.5°	113.9	131.3	165.0	186.7	193.4
105°	138.9	154.9	185.5	206.4	214.3
107.5°	166.7	180.3	207.8	229.3	234.0
110°	194.2	206.1	232.4	249.0	256.8

TEST NUMBER: P1001581

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	222.9	232.1	256.3	273.3	279.4
115°	251.6	258.5	282.0	298.3	303.1
117.5°	279.4	284.0	306.5	320.9	325.3
120°	306.3	310.9	331.5	344.1	351.3
122.5°	335.2	335.8	356.0	369.6	372.2
125°	362.8	362.0	380.7	394.1	397.6
127.5°	388.3	389.2	403.5	416.2	421.0
130°	414.7	415.6	427.9	440.7	443.0
132.5°	442.5	442.8	451.5	463.4	467.5
135°	465.5	468.9	474.3	485.4	488.3
137.5°	492.1	493.1	497.2	507.1	511.5
140°	518.7	519.2	519.9	529.3	532.6
142.5°	542.4	543.5	542.2	550.7	553.7
145°	564.5	565.9	566.5	570.5	572.0
147.5°	587.1	589.2	588.6	588.8	591.3
150°	607.5	609.0	609.0	609.0	608.4
152.5°	626.0	627.1	627.7	629.4	627.7
155°	645.8	645.8	645.3	647.5	645.3
157.5°	662.8	661.7	661.7	663.4	661.7
160°	677.6	677.0	676.4	678.1	675.3
162.5°	691.2	689.5	688.9	692.3	689.5
165°	703.0	701.3	700.2	703.6	701.3
167.5°	712.7	710.4	710.4	713.8	710.4
170°	720.6	717.8	718.3	721.7	717.8
172.5°	726.3	724.0	724.0	728.0	724.0
175°	731.4	728.5	728.0	731.9	728.0
177.5°	733.6	730.8	730.8	734.8	730.2
180°	732.5	732.5	732.5	732.5	732.5

(END OF REPORT)