

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001585

Luminaire Tested: SA4XXDIP-B575D590UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001585
REPORT IS A COMBINATION OF REPORTS P996207 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D590UB27-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4567.2 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001585

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001585

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	72	70	63	62	60	53	52	50
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	41	46	40	36	39	35	31	33	30	27
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7826	7594	7603
10°	7759	7383	7331
15°	7648	7133	7025
20°	7506	6861	6708
25°	7345	6575	6366
30°	7153	6265	5990
35°	6953	5948	5628
40°	6745	5607	5242
45°	6527	5265	4882
50°	6284	4933	4482
55°	6022	4545	4086
60°	5753	4121	3673
65°	5445	3683	3208
70°	5091	3156	2709
75°	4562	2543	2169
80°	3887	1839	1527
85°	3020	1025	822

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6527 cd/sqm

TEST NUMBER: P1001585

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.4	2.0
10°-20°	254.6	5.6
20°-30°	374.7	8.2
30°-40°	435.6	9.5
40°-50°	435.5	9.5
50°-60°	380.9	8.3
60°-70°	282.8	6.2
70°-80°	160.5	3.5
80°-90°	47.1	1.0
90°-100°	214.3	4.7
100°-110°	435.8	9.5
110°-120°	388.4	8.5
120°-130°	326.3	7.1
130°-140°	272.3	6.0
140°-150°	207.9	4.6
150°-160°	146.2	3.2
160°-170°	86.0	1.9
170°-180°	28.0	0.6
0°-30°	719.7	15.8
0°-40°	1155.3	25.3
0°-60°	1971.8	43.2
0°-90°	2462.1	53.9
90°-120°	1038.5	22.7
90°-150°	1845.0	40.4
90°-180°	2105.0	46.1
0°-180°	4567.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	959	959	959	959	959	
5°	958	955	946	955	953	91
15°	912	909	897	902	900	257
25°	826	820	810	810	808	380
35°	711	705	694	689	685	444
45°	580	575	562	554	552	447
55°	439	436	426	416	412	393
65°	297	294	286	278	274	294
75°	158	154	151	148	147	168
85°	42	42	40	40	39	45
90°	1	4	10	11	12	4
95°	19	59	462	229	138	21
105°	66	96	372	800	797	71
115°	117	146	332	637	766	116
125°	163	193	330	542	611	145
135°	193	230	327	481	546	149
145°	223	255	325	406	446	140
155°	253	273	316	358	374	117
165°	276	284	303	321	326	78
175°	288	288	291	295	294	27
180°	288	288	288	288	288	

TEST NUMBER: P1001585

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	958.8	958.8	958.8	958.8	958.8
2.5°	961.9	959.6	951.1	958.8	958.1
5°	958.1	955.0	946.5	955.0	953.4
7.5°	951.1	948.1	938.8	945.8	945.0
10°	941.2	938.1	928.1	934.2	932.7
12.5°	928.1	925.0	914.3	921.2	918.9
15°	912.0	908.9	897.4	902.0	899.7
17.5°	893.5	889.7	878.9	882.0	880.5
20°	872.8	868.9	857.4	859.7	858.2
22.5°	850.5	845.1	833.6	838.2	835.1
25°	825.9	820.5	809.8	810.5	807.5
27.5°	798.2	792.9	782.9	781.3	777.5
30°	770.6	764.4	754.5	751.4	747.5
32.5°	741.4	736.0	725.3	721.4	717.6
35°	710.7	705.3	694.5	689.2	685.3
37.5°	678.4	673.8	662.3	656.9	651.5
40°	646.9	640.8	629.2	621.5	617.7
42.5°	613.1	610.0	597.0	587.7	585.4
45°	580.1	574.7	562.4	553.9	551.6
47.5°	545.5	541.6	530.1	520.9	514.8
50°	510.1	507.1	496.3	485.6	480.9
52.5°	475.6	471.7	460.2	451.0	444.8
55°	438.7	436.4	425.6	416.4	411.8
57.5°	404.1	401.8	391.1	381.8	377.2
60°	368.0	364.2	354.2	347.3	343.4
62.5°	332.7	329.6	318.8	312.7	308.9
65°	297.3	293.5	285.8	278.1	274.3
67.5°	261.2	258.1	250.5	242.8	242.0
70°	228.2	222.8	216.7	210.5	208.2
72.5°	192.8	187.5	182.9	178.2	175.9
75°	158.3	154.4	150.6	147.5	146.7
77.5°	124.5	122.9	119.1	118.3	116.0
80°	94.5	92.2	90.7	89.1	88.4
82.5°	65.3	64.5	64.5	63.8	63.0
85°	41.5	41.5	40.0	40.0	39.2
87.5°	20.0	19.2	18.4	18.4	18.4
90°	0.6	4.5	10.2	11.3	11.9
92.5°	7.9	43.6	222.1	73.4	51.6
95°	18.7	58.9	461.9	228.6	138.3
97.5°	31.2	65.2	494.2	467.0	332.1
100°	43.1	73.6	455.6	646.0	519.7
102.5°	54.4	83.9	407.5	758.2	682.9
105°	66.3	96.0	371.8	800.4	797.4
107.5°	79.3	108.5	348.5	787.7	851.8
110°	92.4	121.0	337.8	742.4	852.9

TEST NUMBER: P1001585

CATALOG NUMBER: SA4XXDIP-B575D590UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	104.8	133.4	332.7	686.8	819.5
115°	116.7	146.4	331.5	637.0	765.6
117.5°	129.2	158.6	331.0	597.9	712.9
120°	141.7	170.6	331.0	571.5	669.8
122.5°	153.0	182.2	330.4	554.2	635.8
125°	162.6	193.2	329.8	542.0	610.9
127.5°	171.7	203.4	328.7	530.4	595.0
130°	179.1	213.4	328.1	516.6	581.4
132.5°	186.4	221.8	327.6	500.1	566.1
135°	193.2	230.0	327.0	481.2	546.3
137.5°	200.0	237.2	327.0	460.8	523.1
140°	207.4	243.7	326.4	440.9	497.6
142.5°	215.3	249.6	326.4	422.5	470.4
145°	222.7	255.0	325.3	405.8	446.0
147.5°	231.2	260.1	323.6	391.9	423.3
150°	239.1	264.9	321.9	379.1	404.6
152.5°	246.5	269.5	319.1	368.4	387.6
155°	253.3	273.4	316.2	358.2	373.5
157.5°	260.1	277.1	313.4	348.5	360.4
160°	266.4	280.2	310.0	338.9	348.5
162.5°	272.0	282.8	306.6	329.6	337.2
165°	276.0	284.5	303.2	321.0	325.9
167.5°	280.5	285.9	299.8	313.6	316.8
170°	283.4	287.0	296.4	306.4	308.3
172.5°	286.2	287.9	293.0	299.8	299.8
175°	287.9	288.5	290.7	294.7	293.6
177.5°	289.0	288.5	289.0	291.0	289.0
180°	288.5	288.5	288.5	288.5	288.5

(END OF REPORT)