

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008123

Luminaire Tested: S122DIP-B485D725UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008123
REPORT IS A COMBINATION OF REPORTS P984316 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB2750-4F0-XX-W2A-D_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4606.0 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008123

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008123

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	44	44	36
1	94	89	85	81	84	80	77	74	65	62	60	50	48	47	37	36	35	35	35	28
2	85	77	71	65	76	70	64	59	56	52	49	43	41	38	32	30	28	28	28	23
3	77	67	60	54	69	61	54	49	49	44	40	38	35	32	28	26	24	24	24	19
4	70	59	51	45	63	54	47	41	43	38	34	34	30	27	25	22	20	20	20	16
5	64	53	44	38	58	48	40	35	39	33	29	30	26	23	22	19	17	17	17	14
6	59	47	39	33	53	43	35	30	35	29	25	27	23	20	20	17	15	15	15	12
7	55	42	34	29	49	38	31	26	31	26	22	24	20	18	18	15	13	13	13	10
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	17	14	12	12	12	9
9	47	35	27	22	42	32	25	20	26	21	17	20	17	14	15	13	11	11	11	8
10	44	32	24	20	39	29	23	18	24	19	15	19	15	12	14	11	10	10	10	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7812	7812	7812
5°	7847	7478	7437
10°	7795	7220	7114
15°	7684	6952	6784
20°	7545	6669	6470
25°	7408	6401	6186
30°	7216	6127	5904
35°	7023	5863	5698
40°	6819	5635	5491
45°	6622	5428	5312
50°	6414	5238	5135
55°	6193	5035	4955
60°	5926	4824	4767
65°	5645	4580	4548
70°	5327	4319	4315
75°	4923	4060	4092
80°	4279	3789	3864
85°	3630	3534	3666

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6622 cd/sqm

TEST NUMBER: P1008123

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.8	1.0
10°-20°	134.2	2.9
20°-30°	203.3	4.4
30°-40°	247.6	5.4
40°-50°	266.4	5.8
50°-60°	258.7	5.6
60°-70°	225.9	4.9
70°-80°	173.9	3.8
80°-90°	118.1	2.6
90°-100°	111.0	2.4
100°-110°	172.8	3.8
110°-120°	341.4	7.4
120°-130°	523.5	11.4
130°-140°	542.2	11.8
140°-150°	497.0	10.8
150°-160°	398.4	8.6
160°-170°	256.7	5.6
170°-180°	88.4	1.9
0°-30°	384.3	8.3
0°-40°	631.8	13.7
0°-60°	1156.9	25.1
0°-90°	1674.7	36.4
90°-120°	625.1	13.6
90°-150°	2187.8	47.5
90°-180°	2931.0	63.6
0°-180°	4606.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	494	494	494	494	494	
5°	495	493	488	493	492	47
15°	472	474	474	480	479	133
25°	429	434	441	449	451	197
35°	370	382	396	411	416	231
45°	303	323	348	370	377	234
55°	232	258	295	321	330	208
65°	159	194	236	265	275	158
75°	88	128	174	204	214	93
85°	26	70	116	146	156	27
90°	8	57	108	140	150	7
95°	49	61	108	139	147	56
105°	208	249	102	135	145	222
115°	389	408	457	168	127	383
125°	548	556	592	616	624	489
135°	676	687	700	722	726	523
145°	784	783	795	804	804	490
155°	863	857	865	869	864	398
165°	910	905	907	912	907	257
175°	930	926	927	932	925	89
180°	928	928	928	928	928	

TEST NUMBER: P1008123

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	493.5	493.5	493.5	493.5	493.5
2.5°	497.1	494.9	489.9	493.5	492.1
5°	494.9	492.8	488.5	492.8	492.1
7.5°	491.3	489.9	486.3	491.3	490.6
10°	487.1	485.6	483.5	489.2	488.5
12.5°	479.9	480.6	479.2	484.9	484.2
15°	472.0	473.5	473.5	479.9	479.2
17.5°	462.0	464.9	467.0	473.5	473.5
20°	452.0	455.6	458.4	466.3	466.3
22.5°	441.3	445.6	449.9	457.7	459.2
25°	429.1	434.1	440.6	449.2	451.3
27.5°	414.8	422.7	429.8	440.6	442.0
30°	400.5	409.8	419.1	430.6	432.7
32.5°	384.8	395.5	407.0	420.5	424.8
35°	369.8	381.9	395.5	411.2	416.3
37.5°	353.3	366.9	384.1	401.2	406.2
40°	336.9	352.6	371.9	390.5	396.9
42.5°	321.1	336.9	359.7	380.5	386.9
45°	303.2	322.6	347.6	369.8	376.9
47.5°	286.1	306.8	335.4	358.3	366.2
50°	268.2	290.4	322.6	346.9	354.7
52.5°	251.0	274.6	309.0	334.0	342.6
55°	232.4	258.2	295.4	321.1	330.4
57.5°	214.6	243.2	280.4	308.3	317.6
60°	195.3	226.0	266.8	294.0	304.0
62.5°	178.1	210.3	251.0	280.4	289.7
65°	158.8	193.8	236.0	265.3	274.6
67.5°	141.6	178.1	221.0	250.3	260.3
70°	123.0	160.2	204.5	235.3	243.9
72.5°	105.9	144.5	189.5	219.6	230.3
75°	88.0	128.0	173.8	204.5	213.8
77.5°	70.8	112.3	158.8	189.5	199.5
80°	53.6	97.3	143.8	173.8	183.8
82.5°	39.3	82.2	129.5	159.5	168.8
85°	25.7	70.1	115.9	145.9	155.9
87.5°	15.7	58.6	104.4	133.7	143.0
90°	7.9	56.7	107.8	139.8	149.7
92.5°	23.2	58.4	104.1	133.4	142.5
95°	49.4	60.8	108.4	139.0	146.9
97.5°	83.6	59.3	111.5	140.0	149.2
100°	123.9	58.4	109.8	141.7	150.9
102.5°	167.5	189.8	106.1	139.3	149.1
105°	207.8	248.6	102.5	134.9	145.4
107.5°	255.5	289.4	98.8	130.5	141.1
110°	300.5	328.9	169.7	125.5	136.1

TEST NUMBER: P1008123

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	343.4	366.9	388.4	121.8	131.7
115°	389.1	408.3	457.3	167.8	127.3
117.5°	427.9	447.2	488.6	414.1	245.2
120°	472.3	485.3	525.9	554.0	471.2
122.5°	509.9	521.4	561.3	584.6	591.8
125°	547.5	556.2	591.9	615.9	624.4
127.5°	582.4	591.1	620.5	645.1	652.2
130°	615.3	625.4	647.8	672.3	677.4
132.5°	648.9	656.9	675.0	697.6	702.6
135°	676.4	687.2	700.4	722.1	726.5
137.5°	706.0	714.0	724.3	744.7	747.7
140°	734.9	739.5	748.3	765.9	766.8
142.5°	759.0	763.0	771.8	785.7	786.0
145°	783.9	783.2	794.6	803.6	803.8
147.5°	806.0	804.0	815.4	819.5	819.0
150°	827.5	822.8	833.6	837.6	834.2
152.5°	845.7	840.3	850.4	854.4	849.7
155°	863.1	857.1	865.1	869.2	863.8
157.5°	877.2	871.8	877.9	882.6	877.2
160°	889.3	885.3	889.3	893.3	888.6
162.5°	900.1	896.0	899.4	904.1	898.0
165°	909.5	905.4	907.4	912.2	907.4
167.5°	916.9	912.8	914.8	919.5	913.5
170°	922.9	918.9	920.2	924.9	918.9
172.5°	926.9	922.9	924.2	928.9	922.9
175°	930.3	925.6	926.9	931.6	924.9
177.5°	931.6	926.9	927.6	932.3	926.3
180°	928.3	928.3	928.3	928.3	928.3

(END OF REPORT)