

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008127

Luminaire Tested: S122DIP-B485D725UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008127
REPORT IS A COMBINATION OF REPORTS P984320 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4773.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008127

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008127

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41		
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35		
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29		
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	25		
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21		
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18		
6	61	50	42	36	56	45	38	33	38	33	29	31	27	24	24	21	19	16		
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14		
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13		
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	12		
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12176	12176	12176
5°	12196	11606	11524
10°	12097	11076	10857
15°	11919	10544	10156
20°	11680	9965	9493
25°	11441	9359	8829
30°	11141	8790	8133
35°	10857	8190	7451
40°	10508	7598	6805
45°	10160	7011	6172
50°	9781	6413	5514
55°	9382	5772	4892
60°	8933	5082	4245
65°	8439	4378	3564
70°	7817	3609	2878
75°	6953	2782	2222
80°	5908	1889	1430
85°	4280	878	609

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10160 cd/sqm

TEST NUMBER: P1008127

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.4	1.5
10°-20°	203.7	4.3
20°-30°	299.3	6.3
30°-40°	347.7	7.3
40°-50°	347.2	7.3
50°-60°	302.8	6.3
60°-70°	223.8	4.7
70°-80°	126.6	2.7
80°-90°	35.1	0.7
90°-100°	31.7	0.7
100°-110°	118.0	2.5
110°-120°	313.0	6.6
120°-130°	519.1	10.9
130°-140°	551.4	11.6
140°-150°	512.4	10.7
150°-160°	412.0	8.6
160°-170°	265.5	5.6
170°-180°	91.4	1.9
0°-30°	575.4	12.1
0°-40°	923.1	19.3
0°-60°	1573.1	33.0
0°-90°	1958.7	41.0
90°-120°	462.7	9.7
90°-150°	2045.5	42.9
90°-180°	2814.0	59.0
0°-180°	4773.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	769	766	758	764	763	73
15°	732	728	718	721	717	206
25°	663	657	644	646	644	305
35°	572	564	552	548	544	357
45°	465	460	449	441	438	359
55°	352	348	339	330	326	315
65°	237	233	226	219	215	235
75°	124	123	119	115	116	133
85°	30	30	29	27	26	34
90°	1	8	14	17	19	4
95°	45	22	27	31	30	53
105°	211	232	42	50	53	226
115°	399	411	429	107	57	393
125°	565	574	587	592	594	504
135°	699	710	716	723	722	540
145°	811	810	822	827	823	507
155°	893	886	895	899	893	411
165°	940	936	938	943	938	266
175°	962	957	959	963	956	92
180°	960	960	960	960	960	

TEST NUMBER: P1008127

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	769.2	769.2	769.2	769.2	769.2
2.5°	773.7	770.0	761.8	769.2	767.7
5°	769.2	766.3	758.1	764.0	762.6
7.5°	764.0	759.6	751.5	757.4	755.9
10°	755.9	750.7	741.8	747.8	745.5
12.5°	744.8	740.4	731.5	735.2	733.7
15°	732.2	727.8	718.2	721.1	717.4
17.5°	716.7	712.3	702.6	706.3	702.6
20°	699.7	695.2	684.9	687.1	684.2
22.5°	682.7	676.0	666.4	666.4	664.9
25°	662.7	656.8	644.2	645.7	644.2
27.5°	640.5	635.3	625.7	623.5	619.8
30°	618.3	612.4	601.3	599.1	596.1
32.5°	594.7	590.2	578.4	574.0	571.0
35°	571.7	564.3	552.5	548.1	544.4
37.5°	545.8	539.2	527.4	522.2	518.5
40°	519.2	513.3	501.5	494.8	491.9
42.5°	493.3	487.4	475.6	468.2	463.7
45°	465.2	460.0	449.0	440.8	437.9
47.5°	437.9	432.7	420.8	412.7	408.3
50°	409.0	405.3	395.0	384.6	380.9
52.5°	380.9	375.7	366.1	358.0	352.8
55°	352.1	347.6	338.7	329.9	326.2
57.5°	323.2	319.5	309.9	301.0	298.1
60°	294.4	291.4	281.1	272.9	270.7
62.5°	266.3	261.1	253.7	246.3	243.3
65°	237.4	233.0	225.6	218.9	215.2
67.5°	207.8	204.1	197.5	192.3	189.3
70°	180.5	177.5	170.9	165.7	162.7
72.5°	152.4	149.4	145.7	140.5	138.3
75°	124.3	122.8	119.1	114.6	116.1
77.5°	99.1	96.2	94.7	92.5	90.2
80°	74.0	73.2	71.7	69.5	68.0
82.5°	50.3	50.3	49.6	46.6	46.6
85°	30.3	29.6	28.8	26.6	25.9
87.5°	13.3	11.8	10.4	8.1	7.4
90°	0.7	8.3	13.9	17.4	18.8
92.5°	17.4	14.6	16.7	18.1	18.8
95°	45.2	22.2	27.1	30.6	29.9
97.5°	81.3	24.3	35.4	37.5	38.2
100°	122.9	27.8	39.6	45.2	46.5
102.5°	168.8	167.4	41.0	48.6	50.7
105°	211.2	232.0	42.4	50.0	52.8
107.5°	260.5	277.9	43.8	51.4	54.2
110°	307.7	322.3	121.6	52.1	54.9

TEST NUMBER: P1008127

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	352.2	364.7	352.9	53.5	55.6
115°	399.4	411.2	428.6	107.0	57.0
117.5°	440.4	454.3	466.1	366.8	184.8
120°	486.2	496.7	509.2	517.5	423.7
122.5°	525.1	536.3	550.1	554.3	555.0
125°	564.7	573.8	587.0	591.8	593.9
127.5°	600.9	610.6	621.0	627.9	628.6
130°	634.9	646.0	653.6	661.3	660.6
132.5°	669.6	678.7	686.3	692.5	691.8
135°	698.8	709.9	716.2	723.1	721.7
137.5°	729.4	737.7	744.6	751.6	749.5
140°	759.2	764.8	772.4	778.7	775.2
142.5°	784.2	789.1	798.1	803.7	800.2
145°	810.6	809.9	821.7	826.6	823.1
147.5°	833.6	831.5	843.3	846.8	844.0
150°	855.8	850.9	862.0	866.2	862.7
152.5°	874.5	869.0	879.4	883.6	878.7
155°	892.6	886.3	894.7	898.8	893.3
157.5°	907.2	901.6	907.9	912.7	907.2
160°	919.7	915.5	919.7	923.9	919.0
162.5°	930.8	926.6	930.1	935.0	928.7
165°	940.5	936.4	938.4	943.3	938.4
167.5°	948.2	944.0	946.1	950.9	944.7
170°	954.4	950.3	951.6	956.5	950.3
172.5°	958.6	954.4	955.8	960.7	954.4
175°	962.1	957.2	958.6	963.4	956.5
177.5°	963.4	958.6	959.3	964.1	957.9
180°	960.0	960.0	960.0	960.0	960.0

(END OF REPORT)