

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008134

Luminaire Tested: S122DIP-B485D925UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008134
REPORT IS A COMBINATION OF REPORTS P984372 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D925UB2750-4F0-XX-W2A-D_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5575.0 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008134

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1008134

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31	31	31
1	93	88	84	80	83	79	76	72	62	60	58	47	45	44	33	32	31	24	24	24
2	84	76	70	65	75	69	63	59	54	50	47	41	38	36	28	27	25	19	19	19
3	76	67	59	53	68	60	54	48	47	43	39	36	32	30	25	23	21	16	16	16
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	22	20	18	14	14	14
5	64	52	44	38	57	47	40	35	37	32	28	28	24	22	20	17	15	12	12	12
6	58	46	38	33	52	42	35	30	33	28	24	25	22	19	18	15	13	10	10	10
7	54	42	34	28	48	38	31	26	30	25	21	23	19	16	16	14	12	9	9	9
8	50	38	30	25	45	34	27	23	27	22	19	21	17	14	15	12	10	8	8	8
9	46	34	27	22	41	31	25	20	25	20	16	19	15	13	13	11	9	7	7	7
10	43	31	24	19	39	28	22	18	23	18	15	17	14	12	12	10	8	6	6	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8052	8052	8052
5°	8089	7708	7665
10°	8035	7442	7332
15°	7921	7166	6992
20°	7777	6876	6670
25°	7636	6597	6376
30°	7440	6315	6085
35°	7240	6043	5873
40°	7027	5809	5661
45°	6827	5595	5476
50°	6612	5398	5294
55°	6384	5190	5108
60°	6108	4972	4913
65°	5819	4722	4689
70°	5491	4454	4447
75°	5074	4184	4219
80°	4415	3905	3984
85°	3743	3641	3779

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6827 cd/sqm

TEST NUMBER: P1008134

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.2	0.9
10°-20°	138.3	2.5
20°-30°	209.6	3.8
30°-40°	255.2	4.6
40°-50°	274.6	4.9
50°-60°	266.6	4.8
60°-70°	232.9	4.2
70°-80°	179.2	3.2
80°-90°	122.2	2.2
90°-100°	123.7	2.2
100°-110°	212.8	3.8
110°-120°	443.8	8.0
120°-130°	692.1	12.4
130°-140°	720.9	12.9
140°-150°	662.9	11.9
150°-160°	531.6	9.5
160°-170°	342.6	6.1
170°-180°	117.9	2.1
0°-30°	396.1	7.1
0°-40°	651.3	11.7
0°-60°	1192.5	21.4
0°-90°	1726.8	31.0
90°-120°	780.2	14.0
90°-150°	2856.0	51.2
90°-180°	3848.0	69.0
0°-180°	5575.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	509	509	509	509	509	
5°	510	508	504	508	507	48
15°	487	488	488	495	494	137
25°	442	448	454	463	465	203
35°	381	394	408	424	429	238
45°	313	332	358	381	388	241
55°	240	266	304	331	341	214
65°	164	200	243	274	283	163
75°	91	132	179	211	220	96
85°	26	72	119	150	161	28
90°	8	61	115	149	160	8
95°	64	69	120	152	160	74
105°	276	324	118	154	165	295
115°	518	542	597	204	148	510
125°	730	742	783	809	818	652
135°	902	917	932	957	961	697
145°	1046	1045	1060	1071	1070	654
155°	1152	1144	1155	1160	1153	531
165°	1214	1208	1211	1217	1211	343
175°	1242	1235	1237	1243	1234	118
180°	1239	1239	1239	1239	1239	

TEST NUMBER: P1008134

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	508.7	508.7	508.7	508.7	508.7
2.5°	512.4	510.2	505.0	508.7	507.2
5°	510.2	508.0	503.5	508.0	507.2
7.5°	506.5	505.0	501.3	506.5	505.7
10°	502.1	500.6	498.4	504.3	503.5
12.5°	494.7	495.4	493.9	499.8	499.1
15°	486.6	488.1	488.1	494.7	493.9
17.5°	476.3	479.2	481.4	488.1	488.1
20°	465.9	469.6	472.6	480.7	480.7
22.5°	454.9	459.3	463.7	471.8	473.3
25°	442.3	447.5	454.1	463.0	465.2
27.5°	427.6	435.7	443.1	454.1	455.6
30°	412.9	422.4	432.0	443.8	446.0
32.5°	396.6	407.7	419.5	433.5	437.9
35°	381.2	393.7	407.7	423.9	429.1
37.5°	364.2	378.2	395.9	413.6	418.8
40°	347.2	363.5	383.4	402.5	409.2
42.5°	331.0	347.2	370.8	392.2	398.8
45°	312.6	332.5	358.3	381.2	388.5
47.5°	294.9	316.3	345.8	369.4	377.5
50°	276.5	299.3	332.5	357.6	365.7
52.5°	258.8	283.1	318.5	344.3	353.1
55°	239.6	266.1	304.5	331.0	340.6
57.5°	221.2	250.7	289.0	317.7	327.3
60°	201.3	233.0	275.0	303.0	313.3
62.5°	183.6	216.7	258.8	289.0	298.6
65°	163.7	199.8	243.3	273.5	283.1
67.5°	146.0	183.6	227.8	258.0	268.4
70°	126.8	165.1	210.9	242.6	251.4
72.5°	109.1	148.9	195.4	226.3	237.4
75°	90.7	132.0	179.1	210.9	220.4
77.5°	73.0	115.7	163.7	195.4	205.7
80°	55.3	100.3	148.2	179.1	189.5
82.5°	40.5	84.8	133.4	164.4	174.0
85°	26.5	72.2	119.4	150.4	160.7
87.5°	16.2	60.5	107.6	137.9	147.4
90°	8.3	60.9	115.2	149.2	159.9
92.5°	29.0	64.5	112.2	142.7	152.5
95°	64.2	69.2	119.8	152.2	160.1
97.5°	110.1	68.3	125.3	155.3	165.0
100°	163.9	68.3	124.8	159.3	169.2
102.5°	222.2	244.8	121.5	157.8	168.6
105°	276.2	324.5	118.1	153.7	165.4
107.5°	339.9	380.0	114.7	149.6	161.3
110°	400.0	433.6	210.7	144.6	156.3

TEST NUMBER: P1008134

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	457.4	485.3	504.1	141.2	152.1
115°	518.3	541.8	597.3	204.4	148.0
117.5°	570.5	594.3	640.6	534.5	307.0
120°	629.7	646.1	691.8	723.1	610.2
122.5°	679.9	694.9	740.2	765.4	773.0
125°	730.3	741.9	782.6	808.7	818.0
127.5°	776.9	788.6	822.0	849.5	856.9
130°	820.8	834.4	859.7	887.3	892.3
132.5°	865.6	876.5	897.4	922.5	927.5
135°	902.5	916.8	932.3	956.8	960.9
137.5°	941.9	952.7	965.3	988.3	990.8
140°	980.5	986.9	998.3	1018.2	1018.1
142.5°	1012.7	1018.3	1030.0	1045.9	1045.2
145°	1046.1	1045.2	1060.4	1071.1	1070.3
147.5°	1075.7	1073.0	1088.2	1093.4	1092.0
150°	1104.4	1098.1	1112.4	1117.8	1113.3
152.5°	1128.6	1121.4	1134.8	1140.2	1134.0
155°	1151.9	1143.8	1154.6	1159.9	1152.8
157.5°	1170.7	1163.5	1171.6	1177.9	1170.7
160°	1186.8	1181.5	1186.8	1192.2	1185.9
162.5°	1201.2	1195.8	1200.3	1206.6	1198.5
165°	1213.7	1208.4	1211.0	1217.3	1211.0
167.5°	1223.6	1218.2	1220.9	1227.2	1219.1
170°	1231.7	1226.3	1228.1	1234.3	1226.3
172.5°	1237.0	1231.7	1233.5	1239.7	1231.7
175°	1241.5	1235.2	1237.0	1243.3	1234.3
177.5°	1243.3	1237.0	1237.9	1244.2	1236.1
180°	1238.8	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)