

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001605

Luminaire Tested: SA4XXDIP-B575D590UB30-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001605
REPORT IS A COMBINATION OF REPORTS P996227 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D590UB30-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4411.0 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001605

CATALOG NUMBER: SA4XXDIP-B575D590UB30-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001605

CATALOG NUMBER: SA4XXDIP-B575D590UB30-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	97	92	88	84	89	85	81	78	71	69	66	59	57	55	48	46	45
2	88	80	73	68	80	73	68	63	62	58	54	51	48	45	41	39	37
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	36	33	31
4	73	61	53	47	67	57	49	44	48	42	38	40	36	32	32	29	26
5	67	55	46	40	61	50	43	37	43	37	32	36	31	28	29	26	23
6	61	49	40	34	56	45	38	32	38	33	28	32	27	24	26	23	20
7	57	44	36	30	52	41	33	28	35	29	25	29	25	21	24	20	18
8	52	40	32	26	48	37	30	25	32	26	22	27	22	19	22	18	16
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	17	14
10	46	33	26	21	42	31	24	20	27	21	17	22	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5642	5642	5642
5°	5658	5495	5505
10°	5621	5387	5372
15°	5568	5266	5221
20°	5490	5133	5075
25°	5403	4988	4917
30°	5307	4845	4756
35°	5200	4698	4613
40°	5114	4557	4465
45°	4986	4424	4334
50°	4877	4274	4196
55°	4765	4129	4037
60°	4591	3949	3887
65°	4399	3754	3706
70°	4165	3531	3498
75°	3841	3285	3299
80°	3475	3032	3092
85°	2991	2780	2924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4986 cd/sqm

TEST NUMBER: P1001605

CATALOG NUMBER: SA4XXDIP-B575D590UB30-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.6	1.5
10°-20°	187.8	4.3
20°-30°	284.0	6.4
30°-40°	343.6	7.8
40°-50°	363.2	8.2
50°-60°	341.9	7.8
60°-70°	283.7	6.4
70°-80°	199.1	4.5
80°-90°	113.8	2.6
90°-100°	115.0	2.6
100°-110°	193.8	4.4
110°-120°	278.3	6.3
120°-130°	341.9	7.8
130°-140°	371.1	8.4
140°-150°	358.4	8.1
150°-160°	300.1	6.8
160°-170°	199.7	4.5
170°-180°	69.9	1.6
0°-30°	537.4	12.2
0°-40°	881.0	20.0
0°-60°	1586.1	36.0
0°-90°	2182.7	49.5
90°-120°	587.0	13.3
90°-150°	1658.5	37.6
90°-180°	2228.0	50.5
0°-180°	4411.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	692	692	692	692	692	
5°	693	690	685	691	690	66
15°	664	665	662	669	669	187
25°	608	612	614	623	624	280
35°	532	541	549	559	562	333
45°	443	458	473	486	490	343
55°	347	363	387	402	407	309
65°	240	265	291	311	317	238
75°	133	162	194	216	223	142
85°	41	74	108	132	140	43
90°	14	51	89	115	122	11
95°	44	75	111	134	140	45
105°	140	156	187	208	216	149
115°	254	261	284	301	306	251
125°	366	365	384	398	401	326
135°	470	473	478	490	493	364
145°	570	571	572	576	577	357
155°	652	652	651	653	651	300
165°	709	708	706	710	708	200
175°	738	735	734	738	734	70
180°	739	739	739	739	739	

TEST NUMBER: P1001605

CATALOG NUMBER: SA4XXDIP-B575D590UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	691.9	691.9	691.9	691.9	691.9
2.5°	695.0	692.7	686.5	691.9	691.1
5°	692.7	690.4	684.9	691.1	690.4
7.5°	688.0	686.5	681.8	688.8	688.0
10°	681.8	681.1	677.2	684.2	683.4
12.5°	673.3	673.3	671.0	677.2	677.2
15°	664.0	664.8	662.5	669.4	668.7
17.5°	651.6	653.9	653.2	660.1	659.4
20°	638.4	640.8	641.5	649.3	649.3
22.5°	623.7	626.8	628.4	636.1	637.7
25°	607.5	612.1	614.4	623.0	623.7
27.5°	589.6	596.6	599.7	607.5	608.2
30°	571.8	578.0	583.4	592.0	593.5
32.5°	552.4	560.2	566.4	576.5	578.0
35°	531.5	540.8	548.6	559.4	561.7
37.5°	510.6	521.4	530.7	541.6	543.9
40°	490.5	500.5	511.4	523.0	526.1
42.5°	467.2	478.8	492.0	505.2	507.5
45°	443.2	457.9	472.6	485.8	489.7
47.5°	420.7	435.4	452.5	465.7	470.3
50°	395.9	413.0	430.0	445.5	450.2
52.5°	371.1	388.2	408.3	423.8	428.5
55°	347.1	363.4	386.6	402.1	406.8
57.5°	320.0	340.1	362.6	381.2	385.1
60°	293.7	313.8	339.4	357.2	363.4
62.5°	268.1	290.6	316.1	333.9	340.1
65°	240.2	265.0	291.3	310.7	316.9
67.5°	213.8	240.2	268.1	287.5	293.7
70°	186.7	213.1	242.5	263.4	268.9
72.5°	160.4	187.5	219.3	239.4	245.6
75°	133.3	161.9	194.5	216.2	223.1
77.5°	107.7	137.9	172.0	193.7	201.5
80°	84.5	115.4	149.5	172.8	179.0
82.5°	61.2	93.8	127.8	151.9	158.8
85°	41.1	73.6	108.5	131.7	139.5
87.5°	25.6	57.3	91.4	113.9	120.9
90°	14.1	51.4	89.3	115.2	122.5
92.5°	26.5	61.0	97.2	120.7	127.4
95°	44.4	75.0	110.8	133.5	140.5
97.5°	64.2	91.2	127.5	150.0	157.0
100°	88.5	111.0	146.3	168.4	173.8
102.5°	114.8	132.5	166.4	188.4	195.1
105°	140.2	156.2	187.1	208.2	216.2
107.5°	168.2	181.8	209.6	231.2	236.1
110°	195.9	207.9	234.5	251.2	259.1

TEST NUMBER: P1001605

CATALOG NUMBER: SA4XXDIP-B575D590UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	224.9	234.2	258.6	275.6	281.8
115°	253.8	260.8	284.4	301.0	305.8
117.5°	281.8	286.5	309.1	323.7	328.2
120°	309.1	313.7	334.5	347.1	354.5
122.5°	338.2	338.8	359.1	372.9	375.5
125°	366.0	365.2	384.0	397.6	401.2
127.5°	391.7	392.7	407.0	419.9	424.7
130°	418.4	419.3	431.7	444.5	446.9
132.5°	446.4	446.7	455.5	467.5	471.6
135°	469.6	473.0	478.5	489.8	492.7
137.5°	496.4	497.5	501.7	511.6	516.1
140°	523.3	523.7	524.4	534.0	537.3
142.5°	547.2	548.3	547.0	555.5	558.6
145°	569.5	571.0	571.5	575.6	576.9
147.5°	592.3	594.4	593.8	594.0	596.6
150°	612.9	614.4	614.4	614.4	613.8
152.5°	631.5	632.7	633.3	635.0	633.3
155°	651.5	651.5	651.0	653.3	651.0
157.5°	668.7	667.5	667.5	669.3	667.5
160°	683.5	683.0	682.4	684.1	681.3
162.5°	697.3	695.6	695.0	698.4	695.6
165°	709.3	707.6	706.4	709.8	707.6
167.5°	719.0	716.7	716.7	720.1	716.7
170°	727.0	724.1	724.7	728.1	724.1
172.5°	732.7	730.4	730.4	734.4	730.4
175°	737.8	735.0	734.4	738.4	734.4
177.5°	740.1	737.3	737.3	741.3	736.7
180°	739.0	739.0	739.0	739.0	739.0

(END OF REPORT)