

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008137

Luminaire Tested: S122DIP-B485D925UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008137
REPORT IS A COMBINATION OF REPORTS P984375 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D925UB2750-4F0-XX-W2A-D_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5592.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008137

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008137

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	93	88	84	80	83	79	76	72	62	60	58	47	45	44	33	32	31
2	84	76	70	65	75	69	63	59	54	50	47	41	38	36	28	27	25
3	76	67	59	53	68	60	54	48	47	43	39	36	32	30	25	23	21
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	22	20	18
5	64	52	44	38	57	47	40	35	37	32	28	28	24	22	20	17	15
6	58	46	38	33	52	42	35	30	33	28	24	25	22	19	18	15	13
7	54	42	34	28	48	38	31	26	30	25	21	23	19	16	16	14	12
8	50	38	30	25	45	34	27	23	27	22	19	21	17	14	15	12	10
9	46	34	27	22	41	31	25	20	25	20	16	19	15	13	13	11	9
10	43	31	24	19	39	28	22	18	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8078	8078	8078
5°	8113	7733	7689
10°	8059	7464	7356
15°	7946	7188	7014
20°	7802	6896	6690
25°	7660	6618	6395
30°	7461	6336	6104
35°	7260	6063	5891
40°	7049	5826	5678
45°	6849	5612	5493
50°	6631	5415	5310
55°	6403	5205	5125
60°	6127	4986	4929
65°	5837	4736	4704
70°	5509	4467	4462
75°	5091	4198	4232
80°	4431	3916	3996
85°	3757	3653	3791

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6849 cd/sqm

TEST NUMBER: P1008137

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	0.9
10°-20°	138.7	2.5
20°-30°	210.2	3.8
30°-40°	256.0	4.6
40°-50°	275.4	4.9
50°-60°	267.5	4.8
60°-70°	233.6	4.2
70°-80°	179.8	3.2
80°-90°	122.6	2.2
90°-100°	124.1	2.2
100°-110°	213.4	3.8
110°-120°	445.2	8.0
120°-130°	694.2	12.4
130°-140°	723.0	12.9
140°-150°	664.9	11.9
150°-160°	533.3	9.5
160°-170°	343.6	6.1
170°-180°	118.3	2.1
0°-30°	397.3	7.1
0°-40°	653.3	11.7
0°-60°	1196.2	21.4
0°-90°	1732.1	31.0
90°-120°	782.6	14.0
90°-150°	2864.7	51.2
90°-180°	3860.0	69.0
0°-180°	5592.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	510	510	510	510	510	
5°	512	510	505	510	509	49
15°	488	490	490	496	496	137
25°	444	449	456	464	467	204
35°	382	395	409	425	430	239
45°	314	334	359	382	390	242
55°	240	267	305	332	342	215
65°	164	200	244	274	284	163
75°	91	132	180	212	221	96
85°	27	72	120	151	161	28
90°	8	61	116	150	160	9
95°	64	70	120	153	161	74
105°	277	325	118	154	166	296
115°	520	543	599	205	148	512
125°	732	744	785	811	820	654
135°	905	920	935	960	964	700
145°	1049	1048	1064	1074	1074	656
155°	1155	1147	1158	1164	1156	532
165°	1217	1212	1215	1221	1215	344
175°	1245	1239	1241	1247	1238	119
180°	1243	1243	1243	1243	1243	

TEST NUMBER: P1008137

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	510.3	510.3	510.3	510.3	510.3
2.5°	514.0	511.7	506.6	510.3	508.8
5°	511.7	509.5	505.1	509.5	508.8
7.5°	508.0	506.6	502.9	508.0	507.3
10°	503.6	502.1	499.9	505.8	505.1
12.5°	496.2	497.0	495.5	501.4	500.7
15°	488.1	489.6	489.6	496.2	495.5
17.5°	477.7	480.7	482.9	489.6	489.6
20°	467.4	471.1	474.0	482.2	482.2
22.5°	456.3	460.7	465.2	473.3	474.8
25°	443.7	448.9	455.5	464.4	466.6
27.5°	428.9	437.1	444.4	455.5	457.0
30°	414.1	423.7	433.4	445.2	447.4
32.5°	397.9	409.0	420.8	434.8	439.3
35°	382.3	394.9	409.0	425.2	430.4
37.5°	365.3	379.4	397.1	414.9	420.0
40°	348.3	364.6	384.5	403.8	410.4
42.5°	332.0	348.3	372.0	393.4	400.1
45°	313.6	333.5	359.4	382.3	389.7
47.5°	295.8	317.3	346.8	370.5	378.6
50°	277.3	300.2	333.5	358.7	366.8
52.5°	259.6	284.0	319.5	345.4	354.2
55°	240.3	267.0	305.4	332.0	341.7
57.5°	221.9	251.4	289.9	318.7	328.3
60°	201.9	233.7	275.8	303.9	314.3
62.5°	184.1	217.4	259.6	289.9	299.5
65°	164.2	200.4	244.0	274.4	284.0
67.5°	146.4	184.1	228.5	258.8	269.2
70°	127.2	165.7	211.5	243.3	252.2
72.5°	109.4	149.4	196.0	227.0	238.1
75°	91.0	132.4	179.7	211.5	221.1
77.5°	73.2	116.1	164.2	196.0	206.3
80°	55.5	100.6	148.6	179.7	190.1
82.5°	40.7	85.0	133.9	164.9	174.5
85°	26.6	72.5	119.8	150.9	161.2
87.5°	16.3	60.6	108.0	138.3	147.9
90°	8.3	61.1	115.6	149.7	160.4
92.5°	29.2	64.8	112.6	143.2	153.0
95°	64.3	69.5	120.1	152.7	160.7
97.5°	110.4	68.5	125.8	155.8	165.6
100°	164.3	68.5	125.2	159.7	169.6
102.5°	222.9	245.5	121.8	158.3	169.1
105°	277.0	325.4	118.4	154.2	165.9
107.5°	340.9	381.0	115.0	150.1	161.8
110°	401.3	434.9	211.3	145.0	156.8

TEST NUMBER: P1008137

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	458.9	486.8	505.6	141.7	152.5
115°	520.0	543.4	599.2	205.1	148.4
117.5°	572.2	596.1	642.5	536.1	308.0
120°	631.6	648.1	693.9	725.3	612.1
122.5°	681.9	697.1	742.4	767.8	775.3
125°	732.5	744.2	784.9	811.1	820.5
127.5°	779.2	791.0	824.5	852.0	859.6
130°	823.3	836.9	862.4	890.0	895.0
132.5°	868.3	879.1	900.1	925.2	930.3
135°	905.2	919.6	935.1	959.7	963.8
137.5°	944.8	955.6	968.3	991.3	993.8
140°	983.4	989.9	1001.3	1021.2	1021.1
142.5°	1015.8	1021.4	1033.1	1049.2	1048.4
145°	1049.3	1048.4	1063.7	1074.4	1073.6
147.5°	1078.9	1076.2	1091.5	1096.7	1095.4
150°	1107.7	1101.4	1115.8	1121.2	1116.7
152.5°	1132.0	1124.8	1138.3	1143.7	1137.4
155°	1155.4	1147.3	1158.1	1163.5	1156.3
157.5°	1174.2	1167.1	1175.1	1181.4	1174.2
160°	1190.4	1185.0	1190.4	1195.8	1189.5
162.5°	1204.8	1199.4	1203.9	1210.2	1202.1
165°	1217.4	1212.0	1214.7	1221.0	1214.7
167.5°	1227.3	1221.9	1224.6	1230.9	1222.8
170°	1235.4	1230.0	1231.8	1238.1	1230.0
172.5°	1240.8	1235.4	1237.2	1243.5	1235.4
175°	1245.3	1239.0	1240.8	1247.1	1238.1
177.5°	1247.1	1240.8	1241.7	1248.0	1239.9
180°	1242.6	1242.6	1242.6	1242.6	1242.6

(END OF REPORT)