

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001615

Luminaire Tested: SA4XXDIP-B575D590UB35-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001615
REPORT IS A COMBINATION OF REPORTS P996237 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D590UB35-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4503.3 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001615

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001615

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	97	92	88	84	89	85	81	78	71	68	66	58	57	55	47	46	44
2	87	80	73	67	80	73	68	63	62	57	54	51	48	45	41	39	37
3	80	70	62	56	73	64	57	52	54	49	45	45	41	38	36	33	31
4	73	61	53	47	66	57	49	44	48	42	38	39	35	32	32	29	26
5	66	54	46	40	61	50	43	37	43	37	32	35	31	27	28	25	23
6	61	49	40	34	56	45	38	32	38	32	28	32	27	24	26	22	20
7	56	44	36	30	52	41	33	28	35	29	25	29	24	21	23	20	17
8	52	40	32	26	48	37	30	25	31	26	22	26	22	19	21	18	16
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	16	14
10	45	33	26	21	42	31	24	20	26	21	17	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5668	5668	5668
5°	5684	5521	5531
10°	5647	5412	5397
15°	5594	5290	5246
20°	5516	5157	5098
25°	5428	5012	4940
30°	5333	4868	4779
35°	5224	4720	4635
40°	5137	4578	4486
45°	5010	4445	4354
50°	4901	4294	4216
55°	4787	4148	4055
60°	4611	3967	3905
65°	4419	3772	3724
70°	4185	3547	3514
75°	3859	3300	3315
80°	3488	3046	3106
85°	3005	2793	2937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5010 cd/sqm

TEST NUMBER: P1001615

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	1.5
10°-20°	188.7	4.2
20°-30°	285.3	6.3
30°-40°	345.2	7.7
40°-50°	364.9	8.1
50°-60°	343.5	7.6
60°-70°	285.0	6.3
70°-80°	200.0	4.4
80°-90°	113.9	2.5
90°-100°	284.1	6.3
100°-110°	491.1	10.9
110°-120°	426.8	9.5
120°-130°	349.3	7.8
130°-140°	283.9	6.3
140°-150°	212.2	4.7
150°-160°	148.1	3.3
160°-170°	87.1	1.9
170°-180°	28.3	0.6
0°-30°	539.9	12.0
0°-40°	885.1	19.7
0°-60°	1593.5	35.4
0°-90°	2192.4	48.7
90°-120°	1202.0	26.7
90°-150°	2047.4	45.5
90°-180°	2311.0	51.3
0°-180°	4503.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	695	695	695	695	695	
5°	696	694	688	694	694	66
15°	667	668	666	673	672	188
25°	610	615	617	626	627	281
35°	534	543	551	562	564	334
45°	445	460	475	488	492	344
55°	349	365	388	404	409	311
65°	241	266	293	312	318	239
75°	134	163	195	217	224	142
85°	41	74	109	132	140	43
90°	13	48	87	111	118	10
95°	29	95	536	320	236	29
105°	74	120	428	882	885	80
115°	123	160	372	699	835	122
125°	168	198	356	586	660	150
135°	197	235	338	507	577	153
145°	226	258	330	416	460	142
155°	257	277	320	363	378	118
165°	280	288	307	325	330	79
175°	292	292	294	298	297	28
180°	292	292	292	292	292	

TEST NUMBER: P1001615

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	695.1	695.1	695.1	695.1	695.1
2.5°	698.2	695.9	689.7	695.1	694.4
5°	695.9	693.6	688.1	694.4	693.6
7.5°	691.2	689.7	685.0	692.0	691.2
10°	685.0	684.2	680.3	687.4	686.6
12.5°	676.5	676.5	674.1	680.3	680.3
15°	667.1	667.9	665.6	672.6	671.8
17.5°	654.7	657.0	656.2	663.2	662.4
20°	641.4	643.8	644.5	652.3	652.3
22.5°	626.6	629.7	631.3	639.1	640.6
25°	610.3	615.0	617.3	625.9	626.6
27.5°	592.4	599.4	602.5	610.3	611.1
30°	574.5	580.7	586.2	594.7	596.3
32.5°	555.0	562.8	569.0	579.1	580.7
35°	534.0	543.3	551.1	562.0	564.4
37.5°	513.0	523.9	533.2	544.1	546.5
40°	492.7	502.9	513.8	525.4	528.6
42.5°	469.4	481.1	494.3	507.5	509.9
45°	445.3	460.1	474.8	488.1	492.0
47.5°	422.7	437.5	454.6	467.8	472.5
50°	397.8	414.9	432.0	447.6	452.3
52.5°	372.9	390.0	410.2	425.8	430.5
55°	348.7	365.1	388.4	404.0	408.7
57.5°	321.5	341.7	364.3	383.0	386.9
60°	295.0	315.3	341.0	358.9	365.1
62.5°	269.3	291.9	317.6	335.5	341.7
65°	241.3	266.2	292.7	312.1	318.4
67.5°	214.8	241.3	269.3	288.8	295.0
70°	187.6	214.1	243.6	264.7	270.1
72.5°	161.1	188.4	220.3	240.5	246.8
75°	133.9	162.7	195.4	217.2	224.2
77.5°	108.2	138.6	172.8	194.6	202.4
80°	84.8	116.0	150.2	173.6	179.8
82.5°	61.5	94.2	128.4	152.6	159.6
85°	41.3	74.0	109.0	132.3	140.1
87.5°	25.7	57.6	91.9	114.4	121.4
90°	13.1	48.2	87.4	111.1	118.0
92.5°	19.7	83.1	297.4	168.6	152.6
95°	29.0	95.4	535.5	320.3	235.8
97.5°	40.9	97.9	564.3	557.1	427.5
100°	52.2	103.4	520.7	734.6	611.9
102.5°	63.7	110.6	468.0	843.4	773.3
105°	74.2	119.9	427.9	881.6	884.7
107.5°	87.4	130.1	400.5	864.7	935.1
110°	99.8	139.6	386.5	814.2	932.3

TEST NUMBER: P1001615

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	111.6	150.0	377.4	753.3	893.8
115°	122.9	160.0	372.4	698.9	834.6
117.5°	135.6	170.0	367.9	654.6	777.4
120°	147.4	179.0	364.0	623.2	729.0
122.5°	158.9	188.5	359.5	601.8	689.9
125°	167.8	198.0	355.9	585.6	660.1
127.5°	177.0	208.4	350.8	569.2	640.1
130°	183.7	217.7	346.3	551.2	621.6
132.5°	191.1	226.4	342.7	530.6	602.2
135°	197.3	234.6	338.2	506.8	577.4
137.5°	204.2	241.0	335.1	482.2	549.3
140°	211.7	247.6	332.2	458.2	519.6
142.5°	218.9	253.6	330.6	436.5	488.1
145°	226.4	258.3	329.5	415.6	459.5
147.5°	235.0	263.4	327.7	397.7	432.7
150°	243.0	268.4	326.0	384.0	409.8
152.5°	249.7	272.9	323.2	373.1	392.6
155°	256.6	277.0	320.3	362.8	378.3
157.5°	263.5	280.6	317.4	353.0	365.1
160°	269.8	283.8	314.0	343.2	353.0
162.5°	275.5	286.4	310.5	333.8	341.5
165°	279.5	288.2	307.1	325.2	330.0
167.5°	284.1	289.6	303.6	317.7	320.9
170°	287.0	290.8	300.2	310.2	312.2
172.5°	289.9	291.6	296.7	303.6	303.6
175°	291.6	292.2	294.5	298.5	297.3
177.5°	292.7	292.2	292.7	294.8	292.7
180°	292.2	292.2	292.2	292.2	292.2

(END OF REPORT)