

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008141

Luminaire Tested: S122DIP-B485D925UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008141
REPORT IS A COMBINATION OF REPORTS P984379 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D925UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5657.0 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008141

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008141

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42			35
1	94	90	86	83	85	82	78	76	66	63	61	51	49	48	37	36	36			29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30			25
3	78	69	62	56	71	63	57	52	51	46	43	39	36	34	29	27	26			21
4	72	61	53	48	64	56	49	44	45	40	36	35	32	29	26	24	22			18
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	23	21	19			16
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17			14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15			12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13			11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12			10
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11			9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12295	12295	12295
5°	12315	11719	11636
10°	12213	11184	10963
15°	12035	10647	10255
20°	11794	10061	9585
25°	11552	9451	8916
30°	11249	8876	8212
35°	10964	8270	7524
40°	10611	7671	6870
45°	10258	7078	6231
50°	9876	6475	5568
55°	9473	5829	4939
60°	9018	5131	4286
65°	8521	4421	3599
70°	7891	3643	2907
75°	7021	2808	2243
80°	5964	1908	1444
85°	4322	887	614

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10258 cd/sqm

TEST NUMBER: P1008141

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.1	1.3
10°-20°	205.7	3.6
20°-30°	302.3	5.3
30°-40°	351.0	6.2
40°-50°	350.6	6.2
50°-60°	305.7	5.4
60°-70°	226.0	4.0
70°-80°	127.9	2.3
80°-90°	35.9	0.6
90°-100°	41.4	0.7
100°-110°	154.2	2.7
110°-120°	409.1	7.2
120°-130°	678.5	12.0
130°-140°	720.7	12.7
140°-150°	669.9	11.8
150°-160°	538.5	9.5
160°-170°	347.0	6.1
170°-180°	119.4	2.1
0°-30°	581.0	10.3
0°-40°	932.1	16.5
0°-60°	1588.4	28.1
0°-90°	1978.2	35.0
90°-120°	604.7	10.7
90°-150°	2673.8	47.3
90°-180°	3679.0	65.0
0°-180°	5657.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	774	766	772	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	363
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	34
90°	1	11	18	23	24	5
95°	59	29	35	40	39	70
105°	276	303	55	65	69	295
115°	522	538	560	140	74	514
125°	738	750	767	774	776	658
135°	913	928	936	945	943	706
145°	1060	1059	1074	1080	1076	663
155°	1167	1159	1170	1175	1168	538
165°	1229	1224	1227	1233	1227	347
175°	1258	1251	1253	1259	1250	120
180°	1255	1255	1255	1255	1255	

TEST NUMBER: P1008141

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	776.7	776.7	776.7	776.7	776.7
2.5°	781.2	777.4	769.2	776.7	775.2
5°	776.7	773.7	765.5	771.5	770.0
7.5°	771.5	767.0	758.8	764.7	763.2
10°	763.2	758.0	749.0	755.0	752.8
12.5°	752.0	747.6	738.6	742.3	740.8
15°	739.3	734.9	725.2	728.1	724.4
17.5°	723.7	719.2	709.5	713.2	709.5
20°	706.5	702.0	691.5	693.8	690.8
22.5°	689.3	682.6	672.9	672.9	671.4
25°	669.1	663.2	650.5	652.0	650.5
27.5°	646.7	641.5	631.8	629.6	625.8
30°	624.3	618.4	607.2	604.9	601.9
32.5°	600.4	596.0	584.0	579.5	576.5
35°	577.3	569.8	557.9	553.4	549.7
37.5°	551.1	544.4	532.5	527.2	523.5
40°	524.3	518.3	506.3	499.6	496.6
42.5°	498.1	492.1	480.2	472.7	468.2
45°	469.7	464.5	453.3	445.1	442.1
47.5°	442.1	436.9	424.9	416.7	412.2
50°	413.0	409.3	398.8	388.3	384.6
52.5°	384.6	379.4	369.7	361.5	356.2
55°	355.5	351.0	342.0	333.1	329.3
57.5°	326.4	322.6	312.9	304.0	301.0
60°	297.2	294.2	283.8	275.6	273.3
62.5°	268.9	263.6	256.2	248.7	245.7
65°	239.7	235.2	227.8	221.1	217.3
67.5°	209.9	206.1	199.4	194.2	191.2
70°	182.2	179.2	172.5	167.3	164.3
72.5°	153.8	150.9	147.1	141.9	139.7
75°	125.5	124.0	120.2	115.8	117.2
77.5°	100.1	97.1	95.6	93.4	91.1
80°	74.7	73.9	72.4	70.2	68.7
82.5°	50.8	50.8	50.0	47.0	47.0
85°	30.6	29.9	29.1	26.9	26.1
87.5°	13.4	11.9	10.5	8.2	7.5
90°	0.9	10.9	18.2	22.7	24.5
92.5°	22.7	19.1	21.8	23.6	24.5
95°	59.0	29.1	35.4	40.0	39.0
97.5°	106.2	31.8	46.3	49.0	49.9
100°	160.7	36.3	51.8	59.0	60.8
102.5°	220.6	218.8	53.6	63.6	66.3
105°	276.0	303.3	55.4	65.4	69.0
107.5°	340.5	363.2	57.2	67.2	70.8
110°	402.2	421.3	158.9	68.1	71.7

TEST NUMBER: P1008141

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	460.4	476.7	461.3	69.9	72.6
115°	522.1	537.5	560.2	139.8	74.5
117.5°	575.7	593.8	609.3	479.4	241.5
120°	635.6	649.2	665.6	676.5	553.9
122.5°	686.4	701.0	719.1	724.6	725.5
125°	738.2	750.0	767.3	773.6	776.3
127.5°	785.4	798.1	811.8	820.8	821.7
130°	829.9	844.4	854.4	864.4	863.5
132.5°	875.3	887.1	897.1	905.3	904.4
135°	913.4	928.0	936.1	945.2	943.4
137.5°	953.4	964.3	973.4	982.5	979.7
140°	992.4	999.7	1009.7	1017.9	1013.3
142.5°	1025.1	1031.5	1043.3	1050.6	1046.0
145°	1059.6	1058.7	1074.2	1080.5	1076.0
147.5°	1089.6	1086.9	1102.3	1106.9	1103.2
150°	1118.7	1112.3	1126.8	1132.3	1127.7
152.5°	1143.2	1135.9	1149.5	1155.0	1148.6
155°	1166.8	1158.6	1169.5	1175.0	1167.7
157.5°	1185.8	1178.6	1186.8	1193.1	1185.8
160°	1202.2	1196.7	1202.2	1207.6	1201.3
162.5°	1216.7	1211.3	1215.8	1222.2	1214.0
165°	1229.4	1224.0	1226.7	1233.1	1226.7
167.5°	1239.4	1234.0	1236.7	1243.1	1234.9
170°	1247.6	1242.1	1244.0	1250.3	1242.1
172.5°	1253.0	1247.6	1249.4	1255.8	1247.6
175°	1257.6	1251.2	1253.0	1259.4	1250.3
177.5°	1259.4	1253.0	1253.9	1260.3	1252.1
180°	1254.9	1254.9	1254.9	1254.9	1254.9

(END OF REPORT)