

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008151

Luminaire Tested: S122DIP-B675D1080UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008151
REPORT IS A COMBINATION OF REPORTS P984434 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D1080UB2750-4F0-XX-W2A-D_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7038.9 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008151

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008151

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42
1	93	89	84	81	84	80	76	73	64	61	59	49	47	46	35	34	33
2	84	77	70	65	76	69	64	59	55	51	48	42	40	37	30	29	27
3	77	67	60	54	69	61	54	49	48	44	40	37	34	31	27	24	23
4	70	59	51	45	63	53	46	41	43	38	34	33	29	26	24	21	19
5	64	52	44	38	57	47	40	35	38	33	29	29	25	22	21	19	16
6	59	47	39	33	53	42	35	30	34	29	25	26	22	19	19	16	14
7	54	42	34	28	49	38	31	26	31	25	22	24	20	17	17	15	13
8	50	38	30	25	45	34	28	23	28	23	19	22	18	15	16	13	11
9	47	35	27	22	42	31	25	20	25	20	17	20	16	13	15	12	10
10	44	32	24	20	39	29	22	18	23	18	15	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11259	11259	11259
5°	11309	10779	10717
10°	11234	10404	10254
15°	11076	10019	9778
20°	10876	9614	9325
25°	10678	9225	8916
30°	10402	8831	8510
35°	10121	8451	8212
40°	9826	8121	7915
45°	9546	7823	7658
50°	9245	7548	7402
55°	8926	7255	7142
60°	8539	6952	6870
65°	8134	6603	6555
70°	7678	6226	6218
75°	7093	5851	5899
80°	6171	5460	5569
85°	5241	5092	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9546 cd/sqm

TEST NUMBER: P1008151

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.4	1.0
10°-20°	193.4	2.7
20°-30°	293.0	4.2
30°-40°	356.8	5.1
40°-50°	383.9	5.5
50°-60°	372.8	5.3
60°-70°	325.6	4.6
70°-80°	250.6	3.6
80°-90°	170.4	2.4
90°-100°	164.4	2.3
100°-110°	265.8	3.8
110°-120°	536.5	7.6
120°-130°	828.3	11.8
130°-140°	859.9	12.2
140°-150°	789.2	11.2
150°-160°	632.7	9.0
160°-170°	407.7	5.8
170°-180°	140.3	2.0
0°-30°	553.8	7.9
0°-40°	910.7	12.9
0°-60°	1667.4	23.7
0°-90°	2414.0	34.3
90°-120°	966.7	13.7
90°-150°	3444.1	48.9
90°-180°	4625.0	65.7
0°-180°	7038.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	711	711	711	711	711	
5°	713	710	704	710	709	68
15°	680	682	682	692	691	192
25°	618	626	635	647	650	284
35°	533	550	570	593	600	333
45°	437	465	501	533	543	337
55°	335	372	426	463	476	300
65°	229	279	340	382	396	227
75°	127	184	250	295	308	134
85°	37	101	167	210	225	39
90°	11	83	157	204	218	11
95°	78	91	160	205	216	89
105°	330	391	154	202	217	352
115°	618	647	720	257	192	608
125°	870	883	936	972	984	776
135°	1074	1091	1111	1144	1150	830
145°	1245	1244	1262	1276	1276	779
155°	1371	1361	1374	1380	1372	632
165°	1444	1438	1441	1449	1441	408
175°	1478	1470	1472	1480	1469	141
180°	1474	1474	1474	1474	1474	

TEST NUMBER: P1008151

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	711.3	711.3	711.3	711.3	711.3
2.5°	716.4	713.3	706.1	711.3	709.2
5°	713.3	710.3	704.1	710.3	709.2
7.5°	708.2	706.1	701.0	708.2	707.2
10°	702.0	699.9	696.8	705.1	704.1
12.5°	691.7	692.7	690.7	698.9	697.9
15°	680.4	682.4	682.4	691.7	690.7
17.5°	665.9	670.0	673.1	682.4	682.4
20°	651.5	656.6	660.8	672.1	672.1
22.5°	636.0	642.2	648.4	659.7	661.8
25°	618.5	625.7	635.0	647.4	650.5
27.5°	597.9	609.2	619.5	635.0	637.1
30°	577.3	590.7	604.1	620.6	623.7
32.5°	554.6	570.1	586.5	606.1	612.3
35°	532.9	550.5	570.1	592.7	600.0
37.5°	509.2	528.8	553.6	578.3	585.5
40°	485.5	508.2	536.0	562.8	572.1
42.5°	462.8	485.5	518.5	548.4	557.7
45°	437.1	464.9	501.0	532.9	543.3
47.5°	412.3	442.2	483.5	516.5	527.8
50°	386.6	418.5	464.9	500.0	511.3
52.5°	361.8	395.8	445.3	481.4	493.8
55°	335.0	372.1	425.7	462.8	476.2
57.5°	309.3	350.5	404.1	444.3	457.7
60°	281.4	325.7	384.5	423.7	438.1
62.5°	256.7	303.1	361.8	404.1	417.5
65°	228.8	279.4	340.2	382.4	395.8
67.5°	204.1	256.7	318.5	360.8	375.2
70°	177.3	230.9	294.8	339.1	351.5
72.5°	152.6	208.2	273.2	316.5	331.9
75°	126.8	184.5	250.5	294.8	308.2
77.5°	102.1	161.8	228.8	273.2	287.6
80°	77.3	140.2	207.2	250.5	264.9
82.5°	56.7	118.5	186.6	229.9	243.3
85°	37.1	101.0	167.0	210.3	224.7
87.5°	22.7	84.5	150.5	192.8	206.2
90°	11.4	82.9	157.4	204.0	218.5
92.5°	36.0	86.3	152.4	194.7	208.2
95°	77.5	90.8	160.1	204.6	216.0
97.5°	132.0	88.8	165.7	207.1	220.5
100°	196.0	88.1	163.9	210.5	224.1
102.5°	265.4	297.3	158.8	207.7	222.2
105°	329.5	391.3	153.8	201.5	217.2
107.5°	405.3	456.6	148.6	195.4	211.0
110°	476.7	519.7	262.0	188.2	203.9

TEST NUMBER: P1008151

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	545.0	580.7	610.0	183.1	197.7
115°	617.5	647.1	720.1	257.1	191.6
117.5°	679.5	709.0	770.5	648.9	379.7
120°	749.9	770.0	830.4	872.1	739.5
122.5°	809.6	827.7	887.2	921.5	931.8
125°	869.5	883.3	936.5	971.9	984.4
127.5°	924.9	938.8	982.7	1019.0	1029.4
130°	977.2	993.2	1026.6	1063.0	1070.3
132.5°	1030.5	1043.3	1070.6	1103.9	1111.0
135°	1074.3	1091.3	1111.2	1143.6	1149.7
137.5°	1121.2	1134.0	1149.9	1180.1	1184.1
140°	1167.1	1174.6	1188.4	1214.5	1215.3
142.5°	1205.5	1211.9	1225.8	1246.8	1246.5
145°	1245.0	1244.0	1262.1	1275.8	1275.5
147.5°	1280.2	1277.0	1295.2	1301.5	1300.3
150°	1314.4	1306.9	1324.0	1330.4	1325.0
152.5°	1343.2	1334.6	1350.6	1357.0	1349.6
155°	1370.9	1361.3	1374.1	1380.5	1372.0
157.5°	1393.3	1384.8	1394.4	1401.8	1393.3
160°	1412.5	1406.1	1412.5	1418.9	1411.4
162.5°	1429.6	1423.2	1428.5	1436.0	1426.4
165°	1444.5	1438.1	1441.3	1448.8	1441.3
167.5°	1456.3	1449.9	1453.1	1460.5	1450.9
170°	1465.9	1459.5	1461.6	1469.1	1459.5
172.5°	1472.3	1465.9	1468.0	1475.5	1465.9
175°	1477.6	1470.1	1472.3	1479.7	1469.1
177.5°	1479.7	1472.3	1473.3	1480.8	1471.2
180°	1474.4	1474.4	1474.4	1474.4	1474.4

(END OF REPORT)