

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001641

Luminaire Tested: SA4XXDIP-B575D810UB27-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001641
REPORT IS A COMBINATION OF REPORTS P996263 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D810UB27-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5057.0 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001641

CATALOG NUMBER: SA4XXDIP-B575D810UB27-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001641

CATALOG NUMBER: SA4XXDIP-B575D810UB27-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	95	91	86	83	87	83	79	76	68	66	63	55	53	51	42	41	40
2	86	79	72	67	79	72	66	62	59	55	52	48	45	42	37	35	33
3	79	69	61	55	71	63	56	51	52	47	43	42	38	35	32	30	28
4	72	61	53	46	65	56	48	43	46	41	36	37	33	30	29	26	24
5	66	54	46	39	60	49	42	37	41	35	31	33	29	26	26	23	20
6	60	48	40	34	55	44	37	32	37	31	27	30	26	22	23	20	18
7	56	43	35	30	51	40	33	28	33	28	24	27	23	20	21	18	16
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	19	16	14
9	48	36	28	23	44	33	26	22	28	22	19	23	18	16	18	15	13
10	45	33	25	21	41	30	24	19	25	20	17	21	17	14	17	14	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5594	5594	5594
5°	5610	5448	5458
10°	5574	5341	5326
15°	5521	5220	5177
20°	5444	5090	5032
25°	5357	4946	4875
30°	5263	4804	4716
35°	5156	4658	4574
40°	5070	4518	4427
45°	4944	4387	4297
50°	4836	4238	4161
55°	4725	4094	4002
60°	4552	3915	3854
65°	4362	3723	3675
70°	4130	3502	3469
75°	3807	3256	3272
80°	3442	3008	3066
85°	2962	2757	2899

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4944 cd/sqm

TEST NUMBER: P1001641

CATALOG NUMBER: SA4XXDIP-B575D810UB27-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	1.3
10°-20°	186.2	3.7
20°-30°	281.6	5.6
30°-40°	340.7	6.7
40°-50°	360.2	7.1
50°-60°	339.0	6.7
60°-70°	281.3	5.6
70°-80°	197.4	3.9
80°-90°	113.4	2.2
90°-100°	130.0	2.6
100°-110°	240.2	4.7
110°-120°	357.6	7.1
120°-130°	446.7	8.8
130°-140°	488.9	9.7
140°-150°	474.2	9.4
150°-160°	397.5	7.9
160°-170°	264.5	5.2
170°-180°	92.6	1.8
0°-30°	532.8	10.5
0°-40°	873.5	17.3
0°-60°	1572.7	31.1
0°-90°	2164.7	42.8
90°-120°	727.8	14.4
90°-150°	2137.6	42.3
90°-180°	2892.0	57.2
0°-180°	5057.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	686	686	686	686	686	
5°	687	684	679	685	684	65
15°	658	659	657	664	663	186
25°	602	607	609	618	618	277
35°	527	536	544	555	557	330
45°	439	454	469	482	486	340
55°	344	360	383	399	403	307
65°	238	263	289	308	314	236
75°	132	161	193	214	221	140
85°	41	73	108	131	138	42
90°	15	54	93	120	127	12
95°	55	88	124	147	154	57
105°	183	199	231	252	261	195
115°	335	342	365	381	385	330
125°	484	483	502	514	518	431
135°	622	626	631	642	645	481
145°	754	756	757	761	762	472
155°	863	863	862	865	862	397
165°	940	937	936	940	937	265
175°	977	974	973	978	973	93
180°	979	979	979	979	979	

TEST NUMBER: P1001641

CATALOG NUMBER: SA4XXDIP-B575D810UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	686.0	686.0	686.0	686.0	686.0
2.5°	689.1	686.8	680.7	686.0	685.3
5°	686.8	684.5	679.1	685.3	684.5
7.5°	682.2	680.7	676.1	683.0	682.2
10°	676.1	675.3	671.4	678.4	677.6
12.5°	667.6	667.6	665.3	671.4	671.4
15°	658.4	659.2	656.8	663.8	663.0
17.5°	646.1	648.4	647.6	654.5	653.8
20°	633.0	635.3	636.1	643.8	643.8
22.5°	618.4	621.5	623.0	630.7	632.3
25°	602.3	606.9	609.2	617.7	618.4
27.5°	584.6	591.5	594.6	602.3	603.1
30°	567.0	573.1	578.5	586.9	588.5
32.5°	547.8	555.4	561.6	571.6	573.1
35°	527.0	536.2	543.9	554.7	557.0
37.5°	506.3	517.0	526.2	537.0	539.3
40°	486.3	496.3	507.0	518.6	521.6
42.5°	463.3	474.8	487.8	500.9	503.2
45°	439.4	454.0	468.6	481.7	485.5
47.5°	417.2	431.8	448.7	461.7	466.3
50°	392.6	409.5	426.4	441.7	446.4
52.5°	368.0	384.9	404.9	420.2	424.8
55°	344.2	360.3	383.4	398.7	403.3
57.5°	317.3	337.3	359.5	378.0	381.8
60°	291.2	311.1	336.5	354.2	360.3
62.5°	265.8	288.1	313.4	331.1	337.3
65°	238.2	262.7	288.9	308.1	314.2
67.5°	212.0	238.2	265.8	285.0	291.2
70°	185.1	211.3	240.5	261.2	266.6
72.5°	159.0	185.9	217.4	237.4	243.5
75°	132.1	160.6	192.8	214.3	221.3
77.5°	106.8	136.7	170.6	192.1	199.7
80°	83.7	114.5	148.3	171.3	177.5
82.5°	60.7	93.0	126.8	150.6	157.5
85°	40.7	73.0	107.6	130.6	138.3
87.5°	25.4	56.9	90.7	112.9	119.8
90°	14.6	53.6	92.8	119.5	127.2
92.5°	31.2	67.9	104.7	128.6	135.4
95°	55.4	87.5	124.3	147.4	154.3
97.5°	81.9	110.2	147.8	170.8	177.7
100°	114.5	137.4	174.2	196.4	201.8
102.5°	149.3	167.0	202.1	224.4	231.3
105°	183.3	199.4	230.9	252.3	260.8
107.5°	220.4	234.2	261.9	284.1	288.7
110°	257.4	269.7	295.9	312.1	320.4

TEST NUMBER: P1001641

CATALOG NUMBER: SA4XXDIP-B575D810UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	296.1	305.3	329.1	346.1	352.2
115°	334.7	341.6	364.6	380.8	385.4
117.5°	371.8	376.4	398.7	412.5	416.4
120°	408.1	413.4	433.4	445.0	452.6
122.5°	446.7	447.4	467.5	480.5	482.1
125°	483.8	483.0	501.5	514.5	517.6
127.5°	517.9	519.3	533.2	545.5	550.2
130°	553.4	554.9	567.2	579.6	581.1
132.5°	590.5	591.2	599.8	611.3	615.1
135°	621.5	626.0	631.4	642.2	644.6
137.5°	657.1	658.7	663.2	672.5	677.1
140°	692.7	693.5	694.2	703.4	706.6
142.5°	724.5	726.0	724.5	733.0	736.0
145°	754.0	756.3	757.0	760.9	761.7
147.5°	784.3	787.3	786.6	786.6	788.8
150°	811.6	813.8	813.8	813.8	813.0
152.5°	836.5	838.0	838.8	841.1	838.8
155°	863.0	863.0	862.3	865.3	862.3
157.5°	885.7	884.2	884.2	886.5	884.2
160°	905.4	904.6	903.9	906.2	902.4
162.5°	923.6	921.3	920.5	925.1	921.3
165°	939.5	937.2	935.7	940.2	937.2
167.5°	952.3	949.3	949.3	953.9	949.3
170°	962.9	959.2	959.9	964.5	959.2
172.5°	970.5	967.5	967.5	972.8	967.5
175°	977.3	973.5	972.8	978.1	972.8
177.5°	980.3	976.6	976.6	981.9	975.8
180°	978.8	978.8	978.8	978.8	978.8

(END OF REPORT)