

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001665

Luminaire Tested: SA4XXDIP-B575D810UB30-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001665
REPORT IS A COMBINATION OF REPORTS P996287 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D810UB30-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5100.0 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001665

CATALOG NUMBER: SA4XXDIP-B575D810UB30-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001665

CATALOG NUMBER: SA4XXDIP-B575D810UB30-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	95	91	86	83	87	83	79	76	68	66	63	55	53	51	42	41	40
2	86	79	72	67	79	72	66	62	59	55	52	48	45	42	37	35	33
3	79	69	61	55	71	63	56	51	52	47	43	42	38	35	32	30	28
4	72	61	53	46	65	56	48	43	46	41	36	37	33	30	29	26	24
5	66	54	46	39	60	49	42	37	41	35	31	33	29	26	26	23	20
6	60	48	40	34	55	44	37	32	37	31	27	30	26	22	23	20	18
7	56	43	35	30	51	40	33	28	33	28	24	27	23	20	21	18	16
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	19	16	14
9	48	36	28	23	44	33	26	22	28	22	19	23	18	16	18	15	13
10	45	33	25	21	41	30	24	19	25	20	17	21	17	14	17	14	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5642	5642	5642
5°	5658	5495	5505
10°	5621	5387	5372
15°	5568	5266	5221
20°	5490	5133	5075
25°	5403	4988	4917
30°	5307	4845	4756
35°	5200	4698	4613
40°	5114	4557	4465
45°	4986	4424	4334
50°	4877	4274	4196
55°	4765	4129	4037
60°	4591	3949	3887
65°	4399	3754	3706
70°	4165	3531	3498
75°	3841	3285	3299
80°	3475	3032	3092
85°	2991	2780	2924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4986 cd/sqm

TEST NUMBER: P1001665

CATALOG NUMBER: SA4XXDIP-B575D810UB30-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.6	1.3
10°-20°	187.8	3.7
20°-30°	284.0	5.6
30°-40°	343.6	6.7
40°-50°	363.2	7.1
50°-60°	341.9	6.7
60°-70°	283.7	5.6
70°-80°	199.1	3.9
80°-90°	114.3	2.2
90°-100°	131.2	2.6
100°-110°	242.2	4.7
110°-120°	360.6	7.1
120°-130°	450.5	8.8
130°-140°	493.0	9.7
140°-150°	478.3	9.4
150°-160°	400.9	7.9
160°-170°	266.7	5.2
170°-180°	93.4	1.8
0°-30°	537.4	10.5
0°-40°	881.0	17.3
0°-60°	1586.1	31.1
0°-90°	2183.2	42.8
90°-120°	734.0	14.4
90°-150°	2155.7	42.3
90°-180°	2917.0	57.2
0°-180°	5100.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	692	692	692	692	692	
5°	693	690	685	691	690	66
15°	664	665	662	669	669	187
25°	608	612	614	623	624	280
35°	532	541	549	559	562	333
45°	443	458	473	486	490	343
55°	347	363	387	402	407	309
65°	240	265	291	311	317	238
75°	133	162	194	216	223	142
85°	41	74	108	132	140	43
90°	15	54	94	121	128	12
95°	56	88	125	149	156	58
105°	185	201	233	254	263	197
115°	338	344	368	384	389	333
125°	488	487	506	519	522	435
135°	627	631	637	648	650	485
145°	760	763	763	767	768	476
155°	870	870	870	873	870	401
165°	947	945	944	948	945	267
175°	986	982	981	986	981	94
180°	987	987	987	987	987	

TEST NUMBER: P1001665

CATALOG NUMBER: SA4XXDIP-B575D810UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	691.9	691.9	691.9	691.9	691.9
2.5°	695.0	692.7	686.5	691.9	691.1
5°	692.7	690.4	684.9	691.1	690.4
7.5°	688.0	686.5	681.8	688.8	688.0
10°	681.8	681.1	677.2	684.2	683.4
12.5°	673.3	673.3	671.0	677.2	677.2
15°	664.0	664.8	662.5	669.4	668.7
17.5°	651.6	653.9	653.2	660.1	659.4
20°	638.4	640.8	641.5	649.3	649.3
22.5°	623.7	626.8	628.4	636.1	637.7
25°	607.5	612.1	614.4	623.0	623.7
27.5°	589.6	596.6	599.7	607.5	608.2
30°	571.8	578.0	583.4	592.0	593.5
32.5°	552.4	560.2	566.4	576.5	578.0
35°	531.5	540.8	548.6	559.4	561.7
37.5°	510.6	521.4	530.7	541.6	543.9
40°	490.5	500.5	511.4	523.0	526.1
42.5°	467.2	478.8	492.0	505.2	507.5
45°	443.2	457.9	472.6	485.8	489.7
47.5°	420.7	435.4	452.5	465.7	470.3
50°	395.9	413.0	430.0	445.5	450.2
52.5°	371.1	388.2	408.3	423.8	428.5
55°	347.1	363.4	386.6	402.1	406.8
57.5°	320.0	340.1	362.6	381.2	385.1
60°	293.7	313.8	339.4	357.2	363.4
62.5°	268.1	290.6	316.1	333.9	340.1
65°	240.2	265.0	291.3	310.7	316.9
67.5°	213.8	240.2	268.1	287.5	293.7
70°	186.7	213.1	242.5	263.4	268.9
72.5°	160.4	187.5	219.3	239.4	245.6
75°	133.3	161.9	194.5	216.2	223.1
77.5°	107.7	137.9	172.0	193.7	201.5
80°	84.5	115.4	149.5	172.8	179.0
82.5°	61.2	93.8	127.8	151.9	158.8
85°	41.1	73.6	108.5	131.7	139.5
87.5°	25.6	57.3	91.4	113.9	120.9
90°	14.7	54.1	93.5	120.6	128.3
92.5°	31.4	68.5	105.7	129.7	136.6
95°	55.9	88.3	125.4	148.6	155.6
97.5°	82.6	111.2	149.0	172.3	179.3
100°	115.4	138.6	175.7	198.1	203.5
102.5°	150.5	168.4	203.9	226.4	233.3
105°	184.9	201.1	232.8	254.5	263.0
107.5°	222.3	236.2	264.1	286.5	291.2
110°	259.7	272.0	298.4	314.7	323.2

TEST NUMBER: P1001665

CATALOG NUMBER: SA4XXDIP-B575D810UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	298.6	307.9	331.9	348.9	355.1
115°	337.5	344.5	367.7	384.1	388.7
117.5°	374.9	379.6	402.0	416.0	419.9
120°	411.6	416.9	437.1	448.8	456.5
122.5°	450.5	451.3	471.4	484.6	486.2
125°	487.9	487.1	505.7	518.9	522.1
127.5°	522.2	523.7	537.7	550.2	554.8
130°	558.1	559.6	572.0	584.4	586.0
132.5°	595.5	596.2	604.8	616.4	620.4
135°	626.8	631.3	636.8	647.7	650.0
137.5°	662.6	664.2	668.8	678.2	682.8
140°	698.5	699.3	700.0	709.4	712.5
142.5°	730.6	732.2	730.6	739.1	742.2
145°	760.4	762.7	763.4	767.3	768.1
147.5°	791.0	794.0	793.2	793.2	795.6
150°	818.4	820.7	820.7	820.7	819.9
152.5°	843.6	845.1	845.9	848.2	845.9
155°	870.3	870.3	869.5	872.6	869.5
157.5°	893.2	891.7	891.7	894.0	891.7
160°	913.1	912.3	911.5	913.8	910.0
162.5°	931.4	929.1	928.3	932.9	929.1
165°	947.4	945.1	943.6	948.2	945.1
167.5°	960.4	957.3	957.3	961.9	957.3
170°	971.1	967.3	968.0	972.6	967.3
172.5°	978.7	975.7	975.7	981.0	975.7
175°	985.6	981.8	981.0	986.4	981.0
177.5°	988.6	984.8	984.8	990.2	984.1
180°	987.1	987.1	987.1	987.1	987.1

(END OF REPORT)