

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008156

Luminaire Tested: S122DIP-B675D1080UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008156
REPORT IS A COMBINATION OF REPORTS P984439 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D1080UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7052.0 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008156

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008156

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	86	83	80	77	67	65	63	53	52	51	40	39	39
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	32	29	28
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16967	16967	16967
5°	16995	16172	16058
10°	16856	15435	15129
15°	16609	14694	14152
20°	16276	13886	13227
25°	15944	13042	12304
30°	15524	12249	11334
35°	15131	11412	10383
40°	14643	10587	9482
45°	14159	9769	8599
50°	13628	8936	7684
55°	13073	8044	6817
60°	12447	7080	5915
65°	11760	6100	4967
70°	10892	5029	4010
75°	9683	3875	3097
80°	8231	2635	1993
85°	5975	1226	849

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14159 cd/sqm

TEST NUMBER: P1008156

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	1.4
10°-20°	283.8	4.0
20°-30°	417.1	5.9
30°-40°	484.5	6.9
40°-50°	483.9	6.9
50°-60°	421.9	6.0
60°-70°	311.9	4.4
70°-80°	176.5	2.5
80°-90°	49.2	0.7
90°-100°	48.6	0.7
100°-110°	181.2	2.6
110°-120°	480.7	6.8
120°-130°	797.2	11.3
130°-140°	846.8	12.0
140°-150°	787.0	11.2
150°-160°	632.7	9.0
160°-170°	407.7	5.8
170°-180°	140.3	2.0
0°-30°	801.8	11.4
0°-40°	1286.3	18.2
0°-60°	2192.1	31.1
0°-90°	2729.6	38.7
90°-120°	710.5	10.1
90°-150°	3141.6	44.5
90°-180°	4322.0	61.3
0°-180°	7052.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1056	1065	1063	102
15°	1020	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	614	610	500
55°	491	484	472	460	454	439
65°	331	325	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	47
90°	1	13	21	27	29	7
95°	69	34	42	47	46	82
105°	324	356	65	77	81	347
115°	613	632	658	164	88	604
125°	867	881	902	909	912	774
135°	1073	1090	1100	1111	1108	829
145°	1245	1244	1262	1270	1264	779
155°	1371	1361	1374	1380	1372	632
165°	1444	1438	1441	1449	1441	408
175°	1478	1470	1472	1480	1469	141
180°	1474	1474	1474	1474	1474	

TEST NUMBER: P1008156

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1071.9	1071.9	1071.9	1071.9	1071.9
2.5°	1078.1	1072.9	1061.6	1071.9	1069.8
5°	1071.9	1067.7	1056.4	1064.7	1062.6
7.5°	1064.7	1058.5	1047.1	1055.4	1053.3
10°	1053.3	1046.1	1033.7	1042.0	1038.9
12.5°	1037.9	1031.7	1019.3	1024.5	1022.4
15°	1020.3	1014.2	1000.8	1004.9	999.7
17.5°	998.7	992.5	979.1	984.3	979.1
20°	975.0	968.8	954.4	957.5	953.3
22.5°	951.3	942.0	928.6	928.6	926.5
25°	923.5	915.2	897.7	899.7	897.7
27.5°	892.5	885.3	871.9	868.8	863.7
30°	861.6	853.4	837.9	834.8	830.7
32.5°	828.6	822.5	806.0	799.8	795.7
35°	796.7	786.4	769.9	763.7	758.6
37.5°	760.6	751.3	734.8	727.6	722.5
40°	723.5	715.3	698.8	689.5	685.4
42.5°	687.4	679.2	662.7	652.4	646.2
45°	648.3	641.1	625.6	614.3	610.1
47.5°	610.1	602.9	586.4	575.1	568.9
50°	569.9	564.8	550.4	535.9	530.8
52.5°	530.8	523.6	510.2	498.8	491.6
55°	490.6	484.4	472.0	459.7	454.5
57.5°	450.4	445.2	431.8	419.5	415.3
60°	410.2	406.1	391.6	380.3	377.2
62.5°	371.0	363.8	353.5	343.2	339.1
65°	330.8	324.7	314.3	305.1	299.9
67.5°	289.6	284.5	275.2	268.0	263.8
70°	251.5	247.4	238.1	230.9	226.7
72.5°	212.3	208.2	203.0	195.8	192.7
75°	173.1	171.1	165.9	159.7	161.8
77.5°	138.1	134.0	131.9	128.8	125.7
80°	103.1	102.0	100.0	96.9	94.8
82.5°	70.1	70.1	69.1	64.9	64.9
85°	42.3	41.2	40.2	37.1	36.1
87.5°	18.6	16.5	14.4	11.3	10.3
90°	1.1	12.8	21.3	26.7	28.8
92.5°	26.7	22.4	25.6	27.7	28.8
95°	69.3	34.1	41.6	46.9	45.9
97.5°	124.8	37.3	54.4	57.6	58.7
100°	188.8	42.7	60.8	69.3	71.5
102.5°	259.2	257.1	62.9	74.7	77.9
105°	324.3	356.3	65.1	76.8	81.1
107.5°	400.1	426.7	67.2	78.9	83.2
110°	472.6	495.0	186.7	80.0	84.3

TEST NUMBER: P1008156

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	540.9	560.1	542.0	82.1	85.3
115°	613.4	631.6	658.2	164.3	87.5
117.5°	676.4	697.7	715.9	563.3	283.8
120°	746.8	762.8	782.0	794.8	650.8
122.5°	806.5	823.6	844.9	851.4	852.4
125°	867.4	881.2	901.5	909.0	912.2
127.5°	922.8	937.8	953.8	964.4	965.5
130°	975.1	992.2	1003.9	1015.6	1014.6
132.5°	1028.4	1042.3	1054.1	1063.7	1062.6
135°	1073.3	1090.3	1099.9	1110.6	1108.5
137.5°	1120.2	1133.0	1143.7	1154.3	1151.1
140°	1166.1	1174.6	1186.3	1195.9	1190.6
142.5°	1204.5	1211.9	1225.8	1234.4	1229.0
145°	1245.0	1244.0	1262.1	1269.6	1264.2
147.5°	1280.2	1277.0	1295.2	1300.5	1296.2
150°	1314.4	1306.9	1324.0	1330.4	1325.0
152.5°	1343.2	1334.6	1350.6	1357.0	1349.6
155°	1370.9	1361.3	1374.1	1380.5	1372.0
157.5°	1393.3	1384.8	1394.4	1401.8	1393.3
160°	1412.5	1406.1	1412.5	1418.9	1411.4
162.5°	1429.6	1423.2	1428.5	1436.0	1426.4
165°	1444.5	1438.1	1441.3	1448.8	1441.3
167.5°	1456.3	1449.9	1453.1	1460.5	1450.9
170°	1465.9	1459.5	1461.6	1469.1	1459.5
172.5°	1472.3	1465.9	1468.0	1475.5	1465.9
175°	1477.6	1470.1	1472.3	1479.7	1469.1
177.5°	1479.7	1472.3	1473.3	1480.8	1471.2
180°	1474.4	1474.4	1474.4	1474.4	1474.4

(END OF REPORT)