

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008158

Luminaire Tested: S122DIP-B675D1080UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008158
REPORT IS A COMBINATION OF REPORTS P984441 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D1080UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6752.0 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008158

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008158

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46			39
1	95	91	87	84	86	83	80	77	67	65	63	53	52	51	40	39	39			33
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33			27
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	32	29	28			23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24			20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21			17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18			15
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16			13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15			12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13			11
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16246	16246	16246
5°	16272	15485	15375
10°	16139	14779	14486
15°	15903	14068	13550
20°	15583	13295	12665
25°	15265	12487	11780
30°	14865	11728	10853
35°	14487	10926	9941
40°	14020	10138	9078
45°	13556	9353	8234
50°	13050	8556	7357
55°	12516	7703	6527
60°	11916	6780	5664
65°	11262	5842	4757
70°	10428	4815	3841
75°	9275	3712	2965
80°	7880	2522	1909
85°	5721	1174	811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13556 cd/sqm

TEST NUMBER: P1008158

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	1.4
10°-20°	271.8	4.0
20°-30°	399.4	5.9
30°-40°	463.9	6.9
40°-50°	463.3	6.9
50°-60°	404.0	6.0
60°-70°	298.6	4.4
70°-80°	169.0	2.5
80°-90°	47.1	0.7
90°-100°	46.6	0.7
100°-110°	173.5	2.6
110°-120°	460.2	6.8
120°-130°	763.3	11.3
130°-140°	810.8	12.0
140°-150°	753.6	11.2
150°-160°	605.8	9.0
160°-170°	390.4	5.8
170°-180°	134.4	2.0
0°-30°	767.7	11.4
0°-40°	1231.6	18.2
0°-60°	2098.9	31.1
0°-90°	2613.5	38.7
90°-120°	680.3	10.1
90°-150°	3007.9	44.5
90°-180°	4139.0	61.3
0°-180°	6752.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1026	1026	1026	1026	1026	
5°	1026	1022	1012	1019	1017	97
15°	977	971	958	962	957	275
25°	884	876	860	862	860	407
35°	763	753	737	731	726	476
45°	621	614	599	588	584	479
55°	470	464	452	440	435	420
65°	317	311	301	292	287	313
75°	166	164	159	153	155	177
85°	40	40	38	36	34	45
90°	1	12	20	26	28	6
95°	66	33	40	45	44	79
105°	310	341	62	74	78	332
115°	587	605	630	157	84	578
125°	830	844	863	870	873	741
135°	1028	1044	1053	1063	1061	794
145°	1192	1191	1208	1216	1210	746
155°	1313	1303	1316	1322	1314	605
165°	1383	1377	1380	1387	1380	391
175°	1415	1408	1410	1417	1407	135
180°	1412	1412	1412	1412	1412	

TEST NUMBER: P1008158

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1032.2	1027.3	1016.4	1026.3	1024.3
5°	1026.3	1022.3	1011.5	1019.4	1017.4
7.5°	1019.4	1013.4	1002.6	1010.5	1008.5
10°	1008.5	1001.6	989.8	997.7	994.7
12.5°	993.7	987.8	975.9	980.9	978.9
15°	976.9	971.0	958.2	962.1	957.2
17.5°	956.2	950.3	937.5	942.4	937.5
20°	933.5	927.6	913.8	916.7	912.8
22.5°	910.8	901.9	889.1	889.1	887.1
25°	884.2	876.3	859.5	861.5	859.5
27.5°	854.6	847.7	834.8	831.9	826.9
30°	825.0	817.1	802.3	799.3	795.4
32.5°	793.4	787.5	771.7	765.8	761.8
35°	762.8	752.9	737.1	731.2	726.3
37.5°	728.3	719.4	703.6	696.7	691.7
40°	692.7	684.8	669.1	660.2	656.2
42.5°	658.2	650.3	634.5	624.6	618.7
45°	620.7	613.8	599.0	588.1	584.2
47.5°	584.2	577.3	561.5	550.6	544.7
50°	545.7	540.8	527.0	513.1	508.2
52.5°	508.2	501.3	488.5	477.6	470.7
55°	469.7	463.8	452.0	440.1	435.2
57.5°	431.2	426.3	413.5	401.6	397.7
60°	392.7	388.8	375.0	364.1	361.2
62.5°	355.2	348.3	338.5	328.6	324.7
65°	316.8	310.8	301.0	292.1	287.2
67.5°	277.3	272.4	263.5	256.6	252.6
70°	240.8	236.8	228.0	221.0	217.1
72.5°	203.3	199.3	194.4	187.5	184.5
75°	165.8	163.8	158.9	153.0	154.9
77.5°	132.2	128.3	126.3	123.3	120.4
80°	98.7	97.7	95.7	92.8	90.8
82.5°	67.1	67.1	66.1	62.2	62.2
85°	40.5	39.5	38.5	35.5	34.5
87.5°	17.8	15.8	13.8	10.9	9.9
90°	1.0	12.3	20.4	25.5	27.6
92.5°	25.5	21.5	24.5	26.6	27.6
95°	66.4	32.7	39.8	44.9	43.9
97.5°	119.5	35.8	52.1	55.2	56.2
100°	180.8	40.9	58.2	66.4	68.4
102.5°	248.2	246.2	60.3	71.5	74.6
105°	310.5	341.2	62.3	73.5	77.6
107.5°	383.1	408.6	64.4	75.6	79.7
110°	452.5	474.0	178.8	76.6	80.7

TEST NUMBER: P1008158

CATALOG NUMBER: S122DIP-B675D1080UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	517.9	536.3	518.9	78.7	81.7
115°	587.3	604.7	630.2	157.3	83.8
117.5°	647.6	668.0	685.4	539.3	271.7
120°	715.0	730.3	748.7	761.0	623.1
122.5°	772.2	788.6	809.0	815.1	816.2
125°	830.5	843.7	863.1	870.3	873.4
127.5°	883.6	897.9	913.2	923.4	924.4
130°	933.6	950.0	961.2	972.4	971.4
132.5°	984.7	998.0	1009.2	1018.4	1017.4
135°	1027.6	1043.9	1053.1	1063.3	1061.3
137.5°	1072.5	1084.8	1095.0	1105.2	1102.2
140°	1116.5	1124.6	1135.9	1145.1	1140.0
142.5°	1153.2	1160.4	1173.7	1181.8	1176.7
145°	1192.1	1191.0	1208.4	1215.5	1210.4
147.5°	1225.8	1222.7	1240.1	1245.2	1241.1
150°	1258.4	1251.3	1267.6	1273.8	1268.7
152.5°	1286.0	1277.9	1293.2	1299.3	1292.2
155°	1312.6	1303.4	1315.7	1321.8	1313.6
157.5°	1334.0	1325.9	1335.1	1342.2	1334.0
160°	1352.4	1346.3	1352.4	1358.6	1351.4
162.5°	1368.8	1362.6	1367.7	1374.9	1365.7
165°	1383.1	1376.9	1380.0	1387.2	1380.0
167.5°	1394.3	1388.2	1391.2	1398.4	1389.2
170°	1403.5	1397.4	1399.4	1406.6	1397.4
172.5°	1409.6	1403.5	1405.5	1412.7	1403.5
175°	1414.7	1407.6	1409.6	1416.8	1406.6
177.5°	1416.8	1409.6	1410.6	1417.8	1408.6
180°	1411.7	1411.7	1411.7	1411.7	1411.7

(END OF REPORT)