

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001669

Luminaire Tested: SA4XXDIP-B575D810UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001669
REPORT IS A COMBINATION OF REPORTS P996291 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D810UB30-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5320.7 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001669

CATALOG NUMBER: SA4XXDIP-B575D810UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001669

CATALOG NUMBER: SA4XXDIP-B575D810UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53
1	97	93	89	85	89	85	82	79	71	69	67	59	57	55	47	46	45
2	88	81	75	70	81	75	69	65	63	59	55	51	49	46	41	39	38
3	81	71	64	58	74	66	59	54	55	50	46	45	42	39	37	34	32
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24
6	62	50	42	36	57	47	39	34	39	34	30	33	29	25	27	24	21
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	46	34	27	22	43	32	26	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7885	7885	7885
5°	7892	7659	7668
10°	7825	7446	7394
15°	7713	7193	7084
20°	7569	6920	6765
25°	7409	6631	6420
30°	7214	6318	6042
35°	7012	5999	5676
40°	6802	5655	5287
45°	6582	5309	4923
50°	6338	4974	4521
55°	6073	4585	4121
60°	5801	4156	3705
65°	5492	3714	3235
70°	5133	3182	2732
75°	4599	2565	2188
80°	3920	1854	1539
85°	3042	1033	828

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6582 cd/sqm

TEST NUMBER: P1001669

CATALOG NUMBER: SA4XXDIP-B575D810UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.1	1.7
10°-20°	256.8	4.8
20°-30°	377.9	7.1
30°-40°	439.3	8.3
40°-50°	439.3	8.3
50°-60°	384.2	7.2
60°-70°	285.2	5.4
70°-80°	161.8	3.0
80°-90°	47.8	0.9
90°-100°	288.8	5.4
100°-110°	587.3	11.0
110°-120°	523.5	9.8
120°-130°	439.8	8.3
130°-140°	367.0	6.9
140°-150°	280.3	5.3
150°-160°	197.0	3.7
160°-170°	115.9	2.2
170°-180°	37.7	0.7
0°-30°	725.8	13.6
0°-40°	1165.1	21.9
0°-60°	1988.6	37.4
0°-90°	2483.5	46.7
90°-120°	1399.6	26.3
90°-150°	2486.6	46.7
90°-180°	2837.0	53.3
0°-180°	5320.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	967	967	967	967	967	
5°	966	963	955	963	962	92
15°	920	917	905	910	907	259
25°	833	828	817	818	814	383
35°	717	711	700	695	691	448
45°	585	580	567	559	556	451
55°	442	440	429	420	415	396
65°	300	296	288	280	277	297
75°	160	156	152	149	148	169
85°	42	42	40	40	40	45
90°	1	6	14	15	16	4
95°	25	79	622	308	186	28
105°	89	129	501	1079	1075	95
115°	157	197	447	858	1032	156
125°	219	260	444	731	823	195
135°	260	310	441	648	736	201
145°	300	344	438	547	601	188
155°	341	369	426	483	503	157
165°	372	383	409	433	439	105
175°	388	389	392	397	396	37
180°	389	389	389	389	389	

TEST NUMBER: P1001669

CATALOG NUMBER: SA4XXDIP-B575D810UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	967.0	967.0	967.0	967.0	967.0
2.5°	970.1	967.8	959.3	967.0	966.2
5°	966.2	963.1	954.6	963.1	961.6
7.5°	959.3	956.2	946.9	953.8	953.1
10°	949.2	946.1	936.0	942.2	940.7
12.5°	936.0	932.9	922.1	929.0	926.7
15°	919.7	916.6	905.0	909.7	907.3
17.5°	901.1	897.3	886.4	889.5	888.0
20°	880.2	876.3	864.7	867.0	865.5
22.5°	857.7	852.3	840.7	845.4	842.3
25°	833.0	827.5	816.7	817.5	814.4
27.5°	805.1	799.6	789.6	788.0	784.1
30°	777.2	771.0	760.9	757.8	753.9
32.5°	747.7	742.3	731.5	727.6	723.7
35°	716.7	711.3	700.5	695.0	691.2
37.5°	684.2	679.5	667.9	662.5	657.1
40°	652.4	646.2	634.6	626.8	623.0
42.5°	618.3	615.2	602.1	592.8	590.4
45°	585.0	579.6	567.2	558.7	556.3
47.5°	550.1	546.3	534.6	525.3	519.1
50°	514.5	511.4	500.5	489.7	485.1
52.5°	479.6	475.8	464.1	454.8	448.6
55°	442.4	440.1	429.3	420.0	415.3
57.5°	407.6	405.2	394.4	385.1	380.4
60°	371.1	367.3	357.2	350.2	346.4
62.5°	335.5	332.4	321.6	315.4	311.5
65°	299.9	296.0	288.2	280.5	276.6
67.5°	263.4	260.3	252.6	244.8	244.1
70°	230.1	224.7	218.5	212.3	210.0
72.5°	194.5	189.1	184.4	179.8	177.4
75°	159.6	155.7	151.9	148.8	148.0
77.5°	125.5	124.0	120.1	119.3	117.0
80°	95.3	93.0	91.4	89.9	89.1
82.5°	65.9	65.1	65.1	64.3	63.5
85°	41.8	41.8	40.3	40.3	39.5
87.5°	20.1	19.4	18.6	18.6	18.6
90°	0.8	6.1	13.7	15.3	16.0
92.5°	10.7	58.8	299.4	99.0	69.5
95°	25.2	79.4	622.5	308.2	186.4
97.5°	42.0	87.8	666.0	629.4	447.6
100°	58.0	99.3	614.1	870.8	700.4
102.5°	73.3	113.0	549.2	1022.0	920.4
105°	89.4	129.4	501.0	1078.8	1074.6
107.5°	106.9	146.2	469.7	1061.6	1148.0
110°	124.5	163.1	455.2	1000.6	1149.5

TEST NUMBER: P1001669

CATALOG NUMBER: SA4XXDIP-B575D810UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.3	179.9	448.3	925.7	1104.4
115°	157.3	197.4	446.8	858.5	1031.9
117.5°	174.1	213.9	446.0	805.8	960.8
120°	190.9	229.9	446.0	770.3	902.8
122.5°	206.2	245.6	445.3	747.0	857.0
125°	219.2	260.5	444.5	730.6	823.4
127.5°	231.4	274.2	443.0	714.9	802.0
130°	241.4	287.6	442.2	696.2	783.6
132.5°	251.3	299.0	441.5	674.0	763.0
135°	260.4	310.1	440.7	648.4	736.3
137.5°	269.6	319.6	440.7	621.0	705.0
140°	279.5	328.5	439.9	594.2	670.6
142.5°	290.2	336.4	439.9	569.4	633.9
145°	300.2	343.7	438.4	546.9	601.1
147.5°	311.6	350.5	436.1	528.2	570.5
150°	322.3	357.0	433.8	511.0	545.3
152.5°	332.2	363.2	430.0	496.4	522.4
155°	341.4	368.6	426.2	482.7	503.3
157.5°	350.6	373.5	422.4	469.7	485.8
160°	359.0	377.7	417.8	456.8	469.7
162.5°	366.6	381.2	413.2	444.2	454.4
165°	372.0	383.4	408.6	432.7	439.2
167.5°	378.1	385.3	404.0	422.8	427.0
170°	381.9	386.8	399.5	412.8	415.5
172.5°	385.7	388.0	394.9	404.0	404.0
175°	388.0	388.8	391.8	397.2	395.6
177.5°	389.5	388.8	389.5	392.2	389.5
180°	388.8	388.8	388.8	388.8	388.8

(END OF REPORT)