

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008165

Luminaire Tested: S122DIP-B675D330UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008165
REPORT IS A COMBINATION OF REPORTS P984493 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D330UB2750-4F0-XX-W2A-D_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4021.0 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008165

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008165

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65
1	98	93	88	84	91	87	83	79	75	72	69	65	62	60	55	53	51
2	89	80	73	67	82	75	69	63	65	60	56	56	52	49	47	44	42
3	80	70	62	55	75	65	58	52	57	51	46	49	44	40	41	38	35
4	73	62	53	46	68	58	50	44	50	44	39	43	38	34	36	33	30
5	67	55	46	39	62	51	43	37	45	38	33	38	33	29	33	29	25
6	62	49	40	34	57	46	38	32	40	34	29	35	29	26	29	25	22
7	57	44	36	30	53	41	34	28	36	30	25	31	26	22	27	23	20
8	53	40	32	26	49	38	30	25	33	27	22	29	24	20	25	21	17
9	49	36	29	23	46	34	27	22	30	24	20	26	21	18	23	19	16
10	46	33	26	21	43	32	25	20	28	22	18	24	20	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11209	11209	11209
5°	11260	10732	10671
10°	11184	10360	10209
15°	11026	9975	9734
20°	10827	9570	9284
25°	10631	9185	8876
30°	10355	8791	8472
35°	10077	8412	8175
40°	9784	8086	7880
45°	9503	7789	7624
50°	9204	7516	7369
55°	8886	7225	7111
60°	8503	6921	6840
65°	8098	6573	6527
70°	7644	6199	6192
75°	7060	5826	5874
80°	6148	5436	5546
85°	5212	5071	5260

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9503 cd/sqm

TEST NUMBER: P1008165

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.1	1.7
10°-20°	192.5	4.8
20°-30°	291.7	7.3
30°-40°	355.2	8.8
40°-50°	382.2	9.5
50°-60°	371.2	9.2
60°-70°	324.2	8.1
70°-80°	249.5	6.2
80°-90°	167.9	4.2
90°-100°	130.1	3.2
100°-110°	139.5	3.5
110°-120°	202.2	5.0
120°-130°	274.1	6.8
130°-140°	271.3	6.7
140°-150°	242.2	6.0
150°-160°	193.0	4.8
160°-170°	124.3	3.1
170°-180°	42.8	1.1
0°-30°	551.4	13.7
0°-40°	906.6	22.5
0°-60°	1660.0	41.3
0°-90°	2401.6	59.7
90°-120°	471.7	11.7
90°-150°	1259.3	31.3
90°-180°	1619.0	40.3
0°-180°	4021.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	708	708	708	708	708	
5°	710	707	701	707	706	67
15°	677	679	679	689	688	191
25°	616	623	632	644	648	283
35°	531	548	568	590	597	332
45°	435	463	499	531	541	336
55°	334	370	424	461	474	298
65°	228	278	339	381	394	226
75°	126	184	249	294	307	134
85°	37	101	166	209	224	39
90°	11	74	142	185	198	8
95°	29	67	131	171	183	31
105°	104	144	108	148	160	112
115°	191	208	262	142	130	188
125°	267	271	310	340	350	238
135°	328	334	347	372	379	254
145°	380	379	385	393	397	238
155°	418	415	419	421	418	193
165°	440	439	440	442	440	124
175°	451	448	449	451	448	43
180°	450	450	450	450	450	

TEST NUMBER: P1008165

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	708.1	708.1	708.1	708.1	708.1
2.5°	713.3	710.2	703.0	708.1	706.1
5°	710.2	707.1	701.0	707.1	706.1
7.5°	705.1	703.0	697.9	705.1	704.0
10°	698.9	696.8	693.8	702.0	701.0
12.5°	688.6	689.7	687.6	695.8	694.8
15°	677.3	679.4	679.4	688.6	687.6
17.5°	663.0	667.1	670.2	679.4	679.4
20°	648.6	653.7	657.8	669.1	669.1
22.5°	633.2	639.4	645.5	656.8	658.9
25°	615.8	623.0	632.2	644.5	647.6
27.5°	595.2	606.5	616.8	632.2	634.2
30°	574.7	588.1	601.4	617.8	620.9
32.5°	552.1	567.5	584.0	603.5	609.6
35°	530.6	548.0	567.5	590.1	597.3
37.5°	507.0	526.5	551.1	575.7	582.9
40°	483.4	506.0	533.7	560.4	569.6
42.5°	460.8	483.4	516.2	546.0	555.2
45°	435.1	462.9	498.8	530.6	540.9
47.5°	410.5	440.3	481.3	514.2	525.5
50°	384.9	416.7	462.9	497.7	509.0
52.5°	360.2	394.1	443.4	479.3	491.6
55°	333.5	370.5	423.9	460.8	474.1
57.5°	307.9	348.9	402.3	442.3	455.7
60°	280.2	324.3	382.8	421.8	436.2
62.5°	255.5	301.7	360.2	402.3	415.6
65°	227.8	278.1	338.7	380.8	394.1
67.5°	203.2	255.5	317.1	359.2	373.6
70°	176.5	229.9	293.5	337.6	350.0
72.5°	151.9	207.3	272.0	315.1	330.5
75°	126.2	183.7	249.4	293.5	306.9
77.5°	101.6	161.1	227.8	272.0	286.3
80°	77.0	139.6	206.3	249.4	263.8
82.5°	56.4	118.0	185.8	228.9	242.2
85°	36.9	100.6	166.3	209.4	223.7
87.5°	22.6	84.2	149.8	191.9	205.3
90°	10.6	73.7	142.0	184.6	197.6
92.5°	17.3	70.4	134.0	174.8	187.4
95°	29.3	66.8	130.7	171.3	183.3
97.5°	45.3	62.7	127.4	166.4	179.0
100°	64.8	58.2	121.1	161.7	173.7
102.5°	85.3	118.4	114.6	155.2	167.5
105°	104.0	143.6	108.1	147.6	160.2
107.5°	127.1	159.9	101.6	140.1	152.7
110°	148.2	175.6	131.8	132.2	144.7



TEST NUMBER: P1008165

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	169.1	191.3	233.0	125.7	137.9
115°	191.2	208.0	262.3	142.5	130.4
117.5°	209.4	224.1	272.7	257.0	181.9
120°	230.9	239.8	286.7	319.4	286.8
122.5°	249.1	255.3	299.8	329.4	339.0
125°	266.6	270.8	309.8	339.8	350.0
127.5°	283.5	287.0	319.6	348.5	358.1
130°	299.5	303.6	328.8	356.9	364.8
132.5°	315.7	318.9	337.9	364.4	372.3
135°	328.3	333.5	346.7	371.5	379.1
137.5°	342.6	346.5	355.0	377.7	383.9
140°	356.6	358.2	363.9	383.2	387.7
142.5°	368.3	369.6	373.8	388.7	392.2
145°	379.7	379.4	384.9	393.4	396.9
147.5°	390.4	389.5	395.0	397.6	399.4
150°	400.8	398.6	403.8	405.7	404.1
152.5°	409.6	407.0	411.9	413.9	411.6
155°	418.1	415.2	419.1	421.0	418.4
157.5°	424.9	422.3	425.2	427.5	424.9
160°	430.8	428.8	430.8	432.7	430.5
162.5°	436.0	434.0	435.7	437.9	435.0
165°	440.5	438.6	439.6	441.8	439.6
167.5°	444.1	442.2	443.1	445.4	442.5
170°	447.0	445.1	445.7	448.0	445.1
172.5°	449.0	447.0	447.7	450.0	447.0
175°	450.6	448.3	449.0	451.3	448.0
177.5°	451.3	449.0	449.3	451.6	448.7
180°	449.6	449.6	449.6	449.6	449.6

(END OF REPORT)