

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008171

Luminaire Tested: S122DIP-B675D330UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008171
REPORT IS A COMBINATION OF REPORTS P984499 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D330UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4051.0 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008171

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008171

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67		
1	102	97	93	90	96	92	88	85	82	79	77	72	70	68	64	62	61	57		
2	93	85	79	73	87	80	75	70	72	67	63	64	60	57	56	54	51	48		
3	85	75	67	61	79	71	64	59	63	58	53	56	52	48	50	46	44	40		
4	77	66	58	52	73	63	55	50	56	50	46	50	45	42	44	41	38	35		
5	71	59	51	45	67	56	49	43	50	44	39	45	40	36	40	36	33	30		
6	66	53	45	39	62	51	43	37	45	39	35	41	36	32	36	32	29	26		
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26	23		
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	26	23	21		
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19		
10	49	37	29	25	47	35	28	24	32	26	22	29	24	21	26	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16967	16967	16967
5°	16995	16172	16058
10°	16856	15435	15129
15°	16609	14694	14152
20°	16276	13886	13227
25°	15944	13042	12304
30°	15524	12249	11334
35°	15131	11412	10383
40°	14643	10587	9482
45°	14159	9769	8599
50°	13628	8936	7684
55°	13073	8044	6817
60°	12447	7080	5915
65°	11760	6100	4967
70°	10892	5029	4010
75°	9683	3875	3097
80°	8231	2635	1993
85°	5975	1226	849

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14159 cd/sqm

TEST NUMBER: P1008171

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	2.5
10°-20°	283.8	7.0
20°-30°	417.1	10.3
30°-40°	484.5	12.0
40°-50°	483.9	11.9
50°-60°	421.9	10.4
60°-70°	311.9	7.7
70°-80°	176.5	4.4
80°-90°	47.4	1.2
90°-100°	14.9	0.4
100°-110°	55.5	1.4
110°-120°	147.1	3.6
120°-130°	244.0	6.0
130°-140°	259.2	6.4
140°-150°	240.9	5.9
150°-160°	193.7	4.8
160°-170°	124.8	3.1
170°-180°	43.0	1.1
0°-30°	801.8	19.8
0°-40°	1286.3	31.8
0°-60°	2192.1	54.1
0°-90°	2727.8	67.3
90°-120°	217.5	5.4
90°-150°	961.7	23.7
90°-180°	1323.0	32.7
0°-180°	4051.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1056	1065	1063	102
15°	1020	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	614	610	500
55°	491	484	472	460	454	439
65°	331	325	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	47
90°	0	4	6	8	9	4
95°	21	10	13	14	14	25
105°	99	109	20	24	25	106
115°	188	193	202	50	27	185
125°	266	270	276	278	279	237
135°	329	334	337	340	339	254
145°	381	381	386	389	387	238
155°	420	417	421	423	420	193
165°	442	440	441	444	441	125
175°	452	450	451	453	450	43
180°	451	451	451	451	451	

TEST NUMBER: P1008171

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1071.9	1071.9	1071.9	1071.9	1071.9
2.5°	1078.1	1072.9	1061.6	1071.9	1069.8
5°	1071.9	1067.7	1056.4	1064.7	1062.6
7.5°	1064.7	1058.5	1047.1	1055.4	1053.3
10°	1053.3	1046.1	1033.7	1042.0	1038.9
12.5°	1037.9	1031.7	1019.3	1024.5	1022.4
15°	1020.3	1014.2	1000.8	1004.9	999.7
17.5°	998.7	992.5	979.1	984.3	979.1
20°	975.0	968.8	954.4	957.5	953.3
22.5°	951.3	942.0	928.6	928.6	926.5
25°	923.5	915.2	897.7	899.7	897.7
27.5°	892.5	885.3	871.9	868.8	863.7
30°	861.6	853.4	837.9	834.8	830.7
32.5°	828.6	822.5	806.0	799.8	795.7
35°	796.7	786.4	769.9	763.7	758.6
37.5°	760.6	751.3	734.8	727.6	722.5
40°	723.5	715.3	698.8	689.5	685.4
42.5°	687.4	679.2	662.7	652.4	646.2
45°	648.3	641.1	625.6	614.3	610.1
47.5°	610.1	602.9	586.4	575.1	568.9
50°	569.9	564.8	550.4	535.9	530.8
52.5°	530.8	523.6	510.2	498.8	491.6
55°	490.6	484.4	472.0	459.7	454.5
57.5°	450.4	445.2	431.8	419.5	415.3
60°	410.2	406.1	391.6	380.3	377.2
62.5°	371.0	363.8	353.5	343.2	339.1
65°	330.8	324.7	314.3	305.1	299.9
67.5°	289.6	284.5	275.2	268.0	263.8
70°	251.5	247.4	238.1	230.9	226.7
72.5°	212.3	208.2	203.0	195.8	192.7
75°	173.1	171.1	165.9	159.7	161.8
77.5°	138.1	134.0	131.9	128.8	125.7
80°	103.1	102.0	100.0	96.9	94.8
82.5°	70.1	70.1	69.1	64.9	64.9
85°	42.3	41.2	40.2	37.1	36.1
87.5°	18.6	16.5	14.4	11.3	10.3
90°	0.3	3.9	6.5	8.2	8.8
92.5°	8.2	6.9	7.8	8.5	8.8
95°	21.2	10.5	12.7	14.4	14.0
97.5°	38.2	11.4	16.7	17.6	18.0
100°	57.8	13.1	18.6	21.2	21.9
102.5°	79.4	78.7	19.3	22.9	23.8
105°	99.3	109.1	19.9	23.5	24.8
107.5°	122.5	130.6	20.6	24.2	25.5
110°	144.7	151.5	57.2	24.5	25.8

TEST NUMBER: P1008171

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	165.6	171.5	165.9	25.1	26.1
115°	187.8	193.3	201.5	50.3	26.8
117.5°	207.1	213.6	219.1	172.4	86.9
120°	228.6	233.5	239.4	243.3	199.2
122.5°	246.9	252.1	258.7	260.6	260.9
125°	265.5	269.8	276.0	278.3	279.2
127.5°	282.5	287.1	292.0	295.2	295.6
130°	298.5	303.7	307.3	310.9	310.6
132.5°	314.8	319.1	322.7	325.6	325.3
135°	328.6	333.8	336.7	340.0	339.3
137.5°	342.9	346.8	350.1	353.4	352.4
140°	357.0	359.6	363.2	366.1	364.5
142.5°	368.7	371.0	375.3	377.9	376.2
145°	381.1	380.8	386.4	388.6	387.0
147.5°	391.9	390.9	396.5	398.1	396.8
150°	402.4	400.1	405.3	407.3	405.6
152.5°	411.2	408.6	413.5	415.4	413.1
155°	419.7	416.7	420.7	422.6	420.0
157.5°	426.5	423.9	426.9	429.1	426.5
160°	432.4	430.5	432.4	434.4	432.1
162.5°	437.6	435.7	437.3	439.6	436.7
165°	442.2	440.2	441.2	443.5	441.2
167.5°	445.8	443.8	444.8	447.1	444.2
170°	448.7	446.8	447.4	449.7	446.8
172.5°	450.7	448.7	449.4	451.7	448.7
175°	452.3	450.0	450.7	453.0	449.7
177.5°	453.0	450.7	451.0	453.3	450.4
180°	451.4	451.4	451.4	451.4	451.4

(END OF REPORT)