

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001729

Luminaire Tested: SA4XXDIP-B795D1035UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001729
REPORT IS A COMBINATION OF REPORTS P996351 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1035UB30-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7098.4 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001729

CATALOG NUMBER: SA4XXDIP-B795D1035UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001729

CATALOG NUMBER: SA4XXDIP-B795D1035UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25
6	63	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19
8	54	41	34	28	49	38	32	27	33	27	24	28	24	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10881	10881	10881
5°	10890	10568	10581
10°	10798	10275	10203
15°	10643	9926	9777
20°	10445	9549	9334
25°	10223	9150	8859
30°	9954	8719	8338
35°	9676	8278	7833
40°	9387	7803	7296
45°	9083	7327	6794
50°	8747	6865	6238
55°	8380	6326	5687
60°	8007	5735	5111
65°	7578	5126	4464
70°	7086	4390	3770
75°	6349	3540	3019
80°	5408	2559	2125
85°	4199	1425	1142

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9083 cd/sqm

TEST NUMBER: P1001729

CATALOG NUMBER: SA4XXDIP-B795D1035UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.8	1.8
10°-20°	354.3	5.0
20°-30°	521.5	7.3
30°-40°	606.2	8.5
40°-50°	606.2	8.5
50°-60°	530.2	7.5
60°-70°	393.6	5.5
70°-80°	223.3	3.1
80°-90°	65.9	0.9
90°-100°	373.7	5.3
100°-110°	760.0	10.7
110°-120°	677.5	9.5
120°-130°	569.1	8.0
130°-140°	474.9	6.7
140°-150°	362.7	5.1
150°-160°	254.9	3.6
160°-170°	149.9	2.1
170°-180°	48.8	0.7
0°-30°	1001.6	14.1
0°-40°	1607.8	22.7
0°-60°	2744.1	38.7
0°-90°	3427.0	48.3
90°-120°	1811.2	25.5
90°-150°	3217.8	45.3
90°-180°	3671.0	51.7
0°-180°	7098.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1334	1334	1334	1334	1334	
5°	1333	1329	1317	1329	1327	127
15°	1269	1265	1249	1255	1252	358
25°	1149	1142	1127	1128	1124	529
35°	989	982	967	959	954	618
45°	807	800	783	771	768	622
55°	610	607	592	580	573	547
65°	414	408	398	387	382	410
75°	220	215	210	205	204	234
85°	58	58	56	56	54	62
90°	1	8	18	20	21	6
95°	33	103	806	399	241	36
105°	116	168	648	1396	1391	123
115°	204	255	578	1111	1335	202
125°	284	337	575	945	1066	253
135°	337	401	570	839	953	260
145°	388	445	567	708	778	244
155°	442	477	552	625	651	204
165°	481	496	529	560	568	136
175°	502	503	507	514	512	48
180°	503	503	503	503	503	

TEST NUMBER: P1001729

CATALOG NUMBER: SA4XXDIP-B795D1035UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1334.4	1334.4	1334.4	1334.4	1334.4
2.5°	1338.7	1335.5	1323.7	1334.4	1333.3
5°	1333.3	1329.1	1317.3	1329.1	1326.9
7.5°	1323.7	1319.4	1306.6	1316.2	1315.2
10°	1309.8	1305.5	1291.6	1300.2	1298.0
12.5°	1291.6	1287.4	1272.4	1282.0	1278.8
15°	1269.2	1264.9	1248.9	1255.3	1252.1
17.5°	1243.5	1238.2	1223.2	1227.5	1225.3
20°	1214.6	1209.3	1193.3	1196.5	1194.3
22.5°	1183.6	1176.2	1160.1	1166.5	1162.3
25°	1149.4	1141.9	1127.0	1128.0	1123.8
27.5°	1110.9	1103.4	1089.5	1087.4	1082.1
30°	1072.4	1063.9	1050.0	1045.7	1040.4
32.5°	1031.8	1024.3	1009.4	1004.0	998.7
35°	989.0	981.6	966.6	959.1	953.8
37.5°	944.1	937.7	921.7	914.2	906.7
40°	900.3	891.7	875.7	865.0	859.7
42.5°	853.2	849.0	830.8	818.0	814.8
45°	807.3	799.8	782.7	770.9	767.7
47.5°	759.2	753.8	737.8	724.9	716.4
50°	710.0	705.7	690.7	675.8	669.3
52.5°	661.9	656.5	640.5	627.6	619.1
55°	610.5	607.3	592.4	579.5	573.1
57.5°	562.4	559.2	544.2	531.4	525.0
60°	512.2	506.8	492.9	483.3	477.9
62.5°	463.0	458.7	443.7	435.2	429.8
65°	413.8	408.4	397.8	387.1	381.7
67.5°	363.5	359.3	348.6	337.9	336.8
70°	317.6	310.1	301.5	293.0	289.8
72.5°	268.4	260.9	254.5	248.1	244.9
75°	220.3	214.9	209.6	205.3	204.2
77.5°	173.2	171.1	165.7	164.7	161.5
80°	131.5	128.3	126.2	124.0	123.0
82.5°	90.9	89.8	89.8	88.7	87.7
85°	57.7	57.7	55.6	55.6	54.5
87.5°	27.8	26.7	25.7	25.7	25.7
90°	1.0	7.9	17.8	19.8	20.8
92.5°	13.8	76.2	387.4	128.0	89.9
95°	32.6	102.8	805.5	398.8	241.2
97.5°	54.4	113.7	861.8	814.4	579.2
100°	75.1	128.5	794.6	1126.8	906.3
102.5°	94.9	146.3	710.6	1322.4	1191.0
105°	115.6	167.6	648.4	1396.0	1390.6
107.5°	138.4	189.2	607.8	1373.8	1485.5
110°	161.1	211.0	589.1	1294.8	1487.5

TEST NUMBER: P1001729

CATALOG NUMBER: SA4XXDIP-B795D1035UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.8	232.8	580.2	1197.9	1429.2
115°	203.6	255.4	578.2	1111.0	1335.3
117.5°	225.3	276.8	577.2	1042.7	1243.4
120°	247.1	297.5	577.2	996.8	1168.2
122.5°	266.9	317.8	576.2	966.6	1108.9
125°	283.7	337.0	575.2	945.4	1065.5
127.5°	299.5	354.8	573.2	925.1	1037.8
130°	312.3	372.1	572.3	900.9	1014.1
132.5°	325.2	387.0	571.3	872.2	987.4
135°	337.0	401.2	570.3	839.1	952.8
137.5°	348.9	413.6	570.3	803.6	912.3
140°	361.7	425.0	569.3	769.0	867.8
142.5°	375.6	435.4	569.3	736.8	820.3
145°	388.4	444.8	567.3	707.6	777.8
147.5°	403.3	453.6	564.4	683.4	738.3
150°	417.1	462.0	561.4	661.2	705.7
152.5°	429.9	470.0	556.4	642.4	676.0
155°	441.8	476.9	551.5	624.7	651.3
157.5°	453.7	483.3	546.6	607.8	628.6
160°	464.5	488.8	540.6	591.0	607.8
162.5°	474.4	493.2	534.7	574.8	588.1
165°	481.3	496.2	528.8	559.9	568.3
167.5°	489.2	498.6	522.8	547.0	552.5
170°	494.2	500.6	516.9	534.2	537.7
172.5°	499.1	502.1	511.0	522.8	522.8
175°	502.1	503.1	507.0	513.9	512.0
177.5°	504.1	503.1	504.1	507.5	504.1
180°	503.1	503.1	503.1	503.1	503.1

(END OF REPORT)