

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008184

Luminaire Tested: S122DIP-B675D530UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008184
REPORT IS A COMBINATION OF REPORTS P984557 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D530UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4794.0 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008184

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1008184

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56		
1	99	95	91	87	92	88	85	82	76	74	71	65	63	61	55	53	52	47		
2	90	83	77	71	84	77	72	67	67	63	59	57	54	51	48	46	44	40		
3	82	73	65	59	76	68	61	56	59	54	50	50	47	43	43	40	37	34		
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32	29		
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28	25		
6	64	52	43	38	59	48	41	36	42	36	32	37	32	28	31	28	25	22		
7	59	47	39	33	55	44	37	31	38	32	28	33	29	25	28	25	22	20		
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	23	20	17		
9	51	39	31	26	47	36	30	25	32	26	23	28	23	20	24	21	18	16		
10	48	36	28	23	44	34	27	22	30	24	20	26	21	18	22	19	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16749	16749	16749
5°	16776	15964	15853
10°	16640	15238	14936
15°	16396	14504	13971
20°	16067	13707	13057
25°	15738	12875	12146
30°	15326	12092	11188
35°	14937	11266	10249
40°	14455	10451	9361
45°	13978	9644	8489
50°	13454	8821	7586
55°	12905	7942	6730
60°	12287	6990	5840
65°	11610	6022	4904
70°	10749	4963	3959
75°	9560	3826	3057
80°	8119	2601	1968
85°	5890	1211	837

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13978 cd/sqm

TEST NUMBER: P1008184

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	2.1
10°-20°	280.2	5.8
20°-30°	411.8	8.6
30°-40°	478.3	10.0
40°-50°	477.7	10.0
50°-60°	416.5	8.7
60°-70°	307.9	6.4
70°-80°	174.2	3.6
80°-90°	47.2	1.0
90°-100°	23.6	0.5
100°-110°	88.1	1.8
110°-120°	233.6	4.9
120°-130°	387.5	8.1
130°-140°	411.6	8.6
140°-150°	382.5	8.0
150°-160°	307.5	6.4
160°-170°	198.2	4.1
170°-180°	68.2	1.4
0°-30°	791.6	16.5
0°-40°	1269.8	26.5
0°-60°	2164.0	45.1
0°-90°	2693.3	56.2
90°-120°	345.3	7.2
90°-150°	1526.9	31.8
90°-180°	2101.0	43.8
0°-180°	4794.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1058	1058	1058	1058	1058	
5°	1058	1054	1043	1051	1049	100
15°	1007	1001	988	992	987	284
25°	912	904	886	888	886	419
35°	786	776	760	754	749	491
45°	640	633	618	606	602	494
55°	484	478	466	454	449	433
65°	327	320	310	301	296	323
75°	171	169	164	158	160	182
85°	42	41	40	37	36	46
90°	0	6	10	13	14	4
95°	34	17	20	23	22	40
105°	158	173	32	37	39	168
115°	298	307	320	80	42	293
125°	422	428	438	442	443	376
135°	522	530	535	540	539	403
145°	605	605	613	617	614	378
155°	666	662	668	671	667	307
165°	702	699	700	704	700	198
175°	718	714	716	719	714	68
180°	717	717	717	717	717	

TEST NUMBER: P1008184

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1058.1	1058.1	1058.1	1058.1	1058.1
2.5°	1064.2	1059.1	1047.9	1058.1	1056.1
5°	1058.1	1054.0	1042.8	1051.0	1049.0
7.5°	1051.0	1044.9	1033.7	1041.8	1039.8
10°	1039.8	1032.7	1020.5	1028.6	1025.6
12.5°	1024.5	1018.4	1006.2	1011.3	1009.3
15°	1007.2	1001.1	987.9	992.0	986.9
17.5°	985.9	979.8	966.5	971.6	966.5
20°	962.5	956.4	942.1	945.2	941.1
22.5°	939.1	929.9	916.7	916.7	914.7
25°	911.6	903.5	886.2	888.2	886.2
27.5°	881.1	874.0	860.7	857.7	852.6
30°	850.6	842.4	827.2	824.1	820.0
32.5°	818.0	811.9	795.6	789.5	785.4
35°	786.5	776.3	760.0	753.9	748.8
37.5°	750.9	741.7	725.4	718.3	713.2
40°	714.2	706.1	689.8	680.6	676.6
42.5°	678.6	670.5	654.2	644.0	637.9
45°	640.0	632.8	617.6	606.4	602.3
47.5°	602.3	595.2	578.9	567.7	561.6
50°	562.6	557.5	543.3	529.1	524.0
52.5°	524.0	516.8	503.6	492.4	485.3
55°	484.3	478.2	466.0	453.8	448.7
57.5°	444.6	439.5	426.3	414.1	410.0
60°	404.9	400.9	386.6	375.4	372.4
62.5°	366.3	359.1	349.0	338.8	334.7
65°	326.6	320.5	310.3	301.2	296.1
67.5°	285.9	280.8	271.6	264.5	260.5
70°	248.2	244.2	235.0	227.9	223.8
72.5°	209.6	205.5	200.4	193.3	190.3
75°	170.9	168.9	163.8	157.7	159.7
77.5°	136.3	132.3	130.2	127.2	124.1
80°	101.7	100.7	98.7	95.6	93.6
82.5°	69.2	69.2	68.2	64.1	64.1
85°	41.7	40.7	39.7	36.6	35.6
87.5°	18.3	16.3	14.2	11.2	10.2
90°	0.5	6.2	10.4	13.0	14.0
92.5°	13.0	10.9	12.4	13.5	14.0
95°	33.7	16.6	20.2	22.8	22.3
97.5°	60.7	18.1	26.4	28.0	28.5
100°	91.8	20.7	29.6	33.7	34.7
102.5°	126.0	125.0	30.6	36.3	37.9
105°	157.6	173.2	31.6	37.3	39.4
107.5°	194.4	207.4	32.7	38.4	40.4
110°	229.7	240.6	90.7	38.9	41.0



TEST NUMBER: P1008184

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	262.9	272.2	263.4	39.9	41.5
115°	298.1	307.0	319.9	79.8	42.5
117.5°	328.7	339.1	347.9	273.8	137.9
120°	363.0	370.7	380.1	386.3	316.3
122.5°	392.0	400.3	410.7	413.8	414.3
125°	421.5	428.3	438.1	441.8	443.3
127.5°	448.5	455.8	463.5	468.7	469.2
130°	473.9	482.2	487.9	493.6	493.1
132.5°	499.8	506.6	512.3	516.9	516.4
135°	521.6	529.9	534.6	539.8	538.7
137.5°	544.4	550.7	555.8	561.0	559.5
140°	566.7	570.9	576.6	581.2	578.7
142.5°	585.4	589.0	595.8	599.9	597.3
145°	605.1	604.6	613.4	617.0	614.4
147.5°	622.2	620.6	629.5	632.1	630.0
150°	638.8	635.2	643.5	646.6	644.0
152.5°	652.8	648.6	656.4	659.5	655.9
155°	666.3	661.6	667.8	670.9	666.8
157.5°	677.2	673.0	677.7	681.3	677.2
160°	686.5	683.4	686.5	689.6	686.0
162.5°	694.8	691.7	694.3	697.9	693.2
165°	702.1	698.9	700.5	704.1	700.5
167.5°	707.8	704.6	706.2	709.8	705.2
170°	712.4	709.3	710.4	714.0	709.3
172.5°	715.5	712.4	713.5	717.1	712.4
175°	718.1	714.5	715.5	719.2	714.0
177.5°	719.2	715.5	716.1	719.7	715.0
180°	716.6	716.6	716.6	716.6	716.6

(END OF REPORT)