

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008187

Luminaire Tested: S122DIP-B675D530UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008187
REPORT IS A COMBINATION OF REPORTS P984560 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D530UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4808.0 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008187

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008187

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	99	95	91	87	92	88	85	82	76	74	71	65	63	61	55	53	52
2	90	83	77	71	84	77	72	67	67	63	59	57	54	51	48	46	44
3	82	73	65	59	76	68	61	56	59	54	50	50	47	43	43	40	37
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28
6	64	52	43	38	59	48	41	36	42	36	32	37	32	28	31	28	25
7	59	47	39	33	55	44	37	31	38	32	28	33	29	25	28	25	22
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	23	20
9	51	39	31	26	47	36	30	25	32	26	23	28	23	20	24	21	18
10	48	36	28	23	44	34	27	22	30	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16800	16800	16800
5°	16827	16012	15899
10°	16689	15283	14979
15°	16445	14547	14012
20°	16114	13747	13096
25°	15785	12913	12182
30°	15371	12127	11222
35°	14981	11300	10279
40°	14497	10483	9388
45°	14019	9672	8515
50°	13494	8847	7608
55°	12942	7966	6749
60°	12323	7011	5857
65°	11646	6040	4917
70°	10783	4978	3972
75°	9588	3838	3066
80°	8143	2609	1974
85°	5905	1214	839

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14019 cd/sqm

TEST NUMBER: P1008187

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	2.1
10°-20°	281.0	5.8
20°-30°	413.0	8.6
30°-40°	479.7	10.0
40°-50°	479.1	10.0
50°-60°	417.7	8.7
60°-70°	308.8	6.4
70°-80°	174.7	3.6
80°-90°	47.4	1.0
90°-100°	23.7	0.5
100°-110°	88.3	1.8
110°-120°	234.3	4.9
120°-130°	388.6	8.1
130°-140°	412.7	8.6
140°-150°	383.6	8.0
150°-160°	308.4	6.4
160°-170°	198.7	4.1
170°-180°	68.4	1.4
0°-30°	793.9	16.5
0°-40°	1273.6	26.5
0°-60°	2170.4	45.1
0°-90°	2701.2	56.2
90°-120°	346.3	7.2
90°-150°	1531.2	31.8
90°-180°	2107.0	43.8
0°-180°	4808.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1061	1061	1061	1061	1061	
5°	1061	1057	1046	1054	1052	101
15°	1010	1004	991	995	990	285
25°	914	906	889	891	889	421
35°	789	779	762	756	751	493
45°	642	635	619	608	604	495
55°	486	480	467	455	450	434
65°	328	321	311	302	297	324
75°	171	169	164	158	160	183
85°	42	41	40	37	36	47
90°	0	6	10	13	14	4
95°	34	17	20	23	22	40
105°	158	174	32	37	40	169
115°	299	308	321	80	43	294
125°	423	430	439	443	445	377
135°	523	531	536	541	540	404
145°	607	606	615	619	616	380
155°	668	664	670	673	669	308
165°	704	701	702	706	702	199
175°	720	716	718	721	716	69
180°	719	719	719	719	719	

TEST NUMBER: P1008187

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1067.4	1062.3	1051.0	1061.3	1059.2
5°	1061.3	1057.2	1045.9	1054.1	1052.1
7.5°	1054.1	1048.0	1036.8	1044.9	1042.9
10°	1042.9	1035.7	1023.5	1031.7	1028.6
12.5°	1027.6	1021.5	1009.2	1014.3	1012.3
15°	1010.2	1004.1	990.8	994.9	989.8
17.5°	988.8	982.7	969.4	974.5	969.4
20°	965.3	959.2	944.9	948.0	943.9
22.5°	941.9	932.7	919.4	919.4	917.4
25°	914.3	906.1	888.8	890.8	888.8
27.5°	883.7	876.6	863.3	860.2	855.1
30°	853.1	844.9	829.6	826.6	822.5
32.5°	820.4	814.3	798.0	791.9	787.8
35°	788.8	778.6	762.3	756.1	751.0
37.5°	753.1	743.9	727.6	720.4	715.3
40°	716.3	708.2	691.9	682.7	678.6
42.5°	680.6	672.5	656.1	645.9	639.8
45°	641.9	634.7	619.4	608.2	604.1
47.5°	604.1	597.0	580.6	569.4	563.3
50°	564.3	559.2	544.9	530.6	525.5
52.5°	525.5	518.4	505.1	493.9	486.7
55°	485.7	479.6	467.4	455.1	450.0
57.5°	445.9	440.8	427.6	415.3	411.2
60°	406.1	402.1	387.8	376.5	373.5
62.5°	367.4	360.2	350.0	339.8	335.7
65°	327.6	321.4	311.2	302.0	296.9
67.5°	286.7	281.6	272.5	265.3	261.2
70°	249.0	244.9	235.7	228.6	224.5
72.5°	210.2	206.1	201.0	193.9	190.8
75°	171.4	169.4	164.3	158.2	160.2
77.5°	136.7	132.7	130.6	127.6	124.5
80°	102.0	101.0	99.0	95.9	93.9
82.5°	69.4	69.4	68.4	64.3	64.3
85°	41.8	40.8	39.8	36.7	35.7
87.5°	18.4	16.3	14.3	11.2	10.2
90°	0.5	6.2	10.4	13.0	14.0
92.5°	13.0	10.9	12.5	13.5	14.0
95°	33.8	16.6	20.3	22.9	22.4
97.5°	60.8	18.2	26.5	28.1	28.6
100°	92.0	20.8	29.6	33.8	34.8
102.5°	126.4	125.3	30.7	36.4	38.0
105°	158.1	173.7	31.7	37.4	39.5
107.5°	195.0	208.0	32.8	38.5	40.6
110°	230.4	241.3	91.0	39.0	41.1

TEST NUMBER: P1008187

CATALOG NUMBER: S122DIP-B675D530UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	263.6	273.0	264.2	40.0	41.6
115°	299.0	307.8	320.8	80.1	42.6
117.5°	329.7	340.1	348.9	274.6	138.3
120°	364.0	371.8	381.1	387.4	317.2
122.5°	393.1	401.4	411.8	414.9	415.5
125°	422.7	429.5	439.4	443.0	444.6
127.5°	449.8	457.1	464.9	470.1	470.6
130°	475.3	483.6	489.3	495.0	494.5
132.5°	501.3	508.0	513.7	518.4	517.9
135°	523.1	531.4	536.1	541.3	540.3
137.5°	546.0	552.2	557.4	562.6	561.1
140°	568.3	572.5	578.2	582.9	580.3
142.5°	587.1	590.7	597.5	601.6	599.0
145°	606.8	606.3	615.1	618.8	616.2
147.5°	624.0	622.4	631.3	633.9	631.8
150°	640.6	637.0	645.3	648.4	645.8
152.5°	654.7	650.5	658.3	661.4	657.8
155°	668.2	663.5	669.7	672.9	668.7
157.5°	679.1	674.9	679.6	683.3	679.1
160°	688.5	685.3	688.5	691.6	687.9
162.5°	696.8	693.7	696.3	699.9	695.2
165°	704.1	700.9	702.5	706.1	702.5
167.5°	709.8	706.7	708.2	711.9	707.2
170°	714.5	711.3	712.4	716.0	711.3
172.5°	717.6	714.5	715.5	719.1	714.5
175°	720.2	716.5	717.6	721.2	716.0
177.5°	721.2	717.6	718.1	721.7	717.1
180°	718.6	718.6	718.6	718.6	718.6

(END OF REPORT)