

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008202

Luminaire Tested: S122DIP-B675D725UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008202
REPORT IS A COMBINATION OF REPORTS P984620 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D725UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5516.0 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008202

CATALOG NUMBER: S122DIP-B675D725UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008202

CATALOG NUMBER: S122DIP-B675D725UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55			49
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47			41
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39			35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33			29
4	74	63	55	49	68	59	52	46	50	45	40	42	38	34	34	31	29			25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25			22
6	63	51	43	37	58	47	40	35	40	35	30	34	29	26	28	25	22			19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20			17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18			15
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	22	18	16			14
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16800	16800	16800
5°	16827	16012	15899
10°	16689	15283	14979
15°	16445	14547	14012
20°	16114	13747	13096
25°	15785	12913	12182
30°	15371	12127	11222
35°	14981	11300	10279
40°	14497	10483	9388
45°	14019	9672	8515
50°	13494	8847	7608
55°	12942	7966	6749
60°	12323	7011	5857
65°	11646	6040	4917
70°	10783	4978	3972
75°	9588	3838	3066
80°	8143	2609	1974
85°	5905	1214	839

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14019 cd/sqm

TEST NUMBER: P1008202

CATALOG NUMBER: S122DIP-B675D725UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	1.8
10°-20°	281.0	5.1
20°-30°	413.0	7.5
30°-40°	479.7	8.7
40°-50°	479.1	8.7
50°-60°	417.7	7.6
60°-70°	308.8	5.6
70°-80°	174.7	3.2
80°-90°	47.8	0.9
90°-100°	31.7	0.6
100°-110°	118.0	2.1
110°-120°	313.0	5.7
120°-130°	519.1	9.4
130°-140°	551.4	10.0
140°-150°	512.4	9.3
150°-160°	412.0	7.5
160°-170°	265.5	4.8
170°-180°	91.4	1.7
0°-30°	793.9	14.4
0°-40°	1273.6	23.1
0°-60°	2170.4	39.3
0°-90°	2701.7	49.0
90°-120°	462.7	8.4
90°-150°	2045.5	37.1
90°-180°	2814.0	51.0
0°-180°	5516.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1061	1061	1061	1061	1061	
5°	1061	1057	1046	1054	1052	101
15°	1010	1004	991	995	990	285
25°	914	906	889	891	889	421
35°	789	779	762	756	751	493
45°	642	635	619	608	604	495
55°	486	480	467	455	450	434
65°	328	321	311	302	297	324
75°	171	169	164	158	160	183
85°	42	41	40	37	36	47
90°	1	8	14	17	19	5
95°	45	22	27	31	30	53
105°	211	232	42	50	53	226
115°	399	411	429	107	57	393
125°	565	574	587	592	594	504
135°	699	710	716	723	722	540
145°	811	810	822	827	823	507
155°	893	886	895	899	893	411
165°	940	936	938	943	938	266
175°	962	957	959	963	956	92
180°	960	960	960	960	960	

TEST NUMBER: P1008202

CATALOG NUMBER: S122DIP-B675D725UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1067.4	1062.3	1051.0	1061.3	1059.2
5°	1061.3	1057.2	1045.9	1054.1	1052.1
7.5°	1054.1	1048.0	1036.8	1044.9	1042.9
10°	1042.9	1035.7	1023.5	1031.7	1028.6
12.5°	1027.6	1021.5	1009.2	1014.3	1012.3
15°	1010.2	1004.1	990.8	994.9	989.8
17.5°	988.8	982.7	969.4	974.5	969.4
20°	965.3	959.2	944.9	948.0	943.9
22.5°	941.9	932.7	919.4	919.4	917.4
25°	914.3	906.1	888.8	890.8	888.8
27.5°	883.7	876.6	863.3	860.2	855.1
30°	853.1	844.9	829.6	826.6	822.5
32.5°	820.4	814.3	798.0	791.9	787.8
35°	788.8	778.6	762.3	756.1	751.0
37.5°	753.1	743.9	727.6	720.4	715.3
40°	716.3	708.2	691.9	682.7	678.6
42.5°	680.6	672.5	656.1	645.9	639.8
45°	641.9	634.7	619.4	608.2	604.1
47.5°	604.1	597.0	580.6	569.4	563.3
50°	564.3	559.2	544.9	530.6	525.5
52.5°	525.5	518.4	505.1	493.9	486.7
55°	485.7	479.6	467.4	455.1	450.0
57.5°	445.9	440.8	427.6	415.3	411.2
60°	406.1	402.1	387.8	376.5	373.5
62.5°	367.4	360.2	350.0	339.8	335.7
65°	327.6	321.4	311.2	302.0	296.9
67.5°	286.7	281.6	272.5	265.3	261.2
70°	249.0	244.9	235.7	228.6	224.5
72.5°	210.2	206.1	201.0	193.9	190.8
75°	171.4	169.4	164.3	158.2	160.2
77.5°	136.7	132.7	130.6	127.6	124.5
80°	102.0	101.0	99.0	95.9	93.9
82.5°	69.4	69.4	68.4	64.3	64.3
85°	41.8	40.8	39.8	36.7	35.7
87.5°	18.4	16.3	14.3	11.2	10.2
90°	0.7	8.3	13.9	17.4	18.8
92.5°	17.4	14.6	16.7	18.1	18.8
95°	45.2	22.2	27.1	30.6	29.9
97.5°	81.3	24.3	35.4	37.5	38.2
100°	122.9	27.8	39.6	45.2	46.5
102.5°	168.8	167.4	41.0	48.6	50.7
105°	211.2	232.0	42.4	50.0	52.8
107.5°	260.5	277.9	43.8	51.4	54.2
110°	307.7	322.3	121.6	52.1	54.9

TEST NUMBER: P1008202

CATALOG NUMBER: S122DIP-B675D725UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	352.2	364.7	352.9	53.5	55.6
115°	399.4	411.2	428.6	107.0	57.0
117.5°	440.4	454.3	466.1	366.8	184.8
120°	486.2	496.7	509.2	517.5	423.7
122.5°	525.1	536.3	550.1	554.3	555.0
125°	564.7	573.8	587.0	591.8	593.9
127.5°	600.9	610.6	621.0	627.9	628.6
130°	634.9	646.0	653.6	661.3	660.6
132.5°	669.6	678.7	686.3	692.5	691.8
135°	698.8	709.9	716.2	723.1	721.7
137.5°	729.4	737.7	744.6	751.6	749.5
140°	759.2	764.8	772.4	778.7	775.2
142.5°	784.2	789.1	798.1	803.7	800.2
145°	810.6	809.9	821.7	826.6	823.1
147.5°	833.6	831.5	843.3	846.8	844.0
150°	855.8	850.9	862.0	866.2	862.7
152.5°	874.5	869.0	879.4	883.6	878.7
155°	892.6	886.3	894.7	898.8	893.3
157.5°	907.2	901.6	907.9	912.7	907.2
160°	919.7	915.5	919.7	923.9	919.0
162.5°	930.8	926.6	930.1	935.0	928.7
165°	940.5	936.4	938.4	943.3	938.4
167.5°	948.2	944.0	946.1	950.9	944.7
170°	954.4	950.3	951.6	956.5	950.3
172.5°	958.6	954.4	955.8	960.7	954.4
175°	962.1	957.2	958.6	963.4	956.5
177.5°	963.4	958.6	959.3	964.1	957.9
180°	960.0	960.0	960.0	960.0	960.0

(END OF REPORT)