

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001789

Luminaire Tested: SA4XXDIP-B795D1205UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001789
REPORT IS A COMBINATION OF REPORTS P996411 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1205UB30-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7740.7 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001789

CATALOG NUMBER: SA4XXDIP-B795D1205UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001789

CATALOG NUMBER: SA4XXDIP-B795D1205UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44		
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	45	44	43	37		
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	38	36	31		
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26		
4	73	63	55	49	67	58	51	45	48	43	39	39	36	33	31	29	26	23		
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23	20		
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	26	23	20	17		
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15		
8	53	41	33	28	48	38	31	26	32	27	23	27	22	19	21	18	16	14		
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15	12		
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10881	10881	10881
5°	10890	10568	10581
10°	10798	10275	10203
15°	10643	9926	9777
20°	10445	9549	9334
25°	10223	9150	8859
30°	9954	8719	8338
35°	9676	8278	7833
40°	9387	7803	7296
45°	9083	7327	6794
50°	8747	6865	6238
55°	8380	6326	5687
60°	8007	5735	5111
65°	7578	5126	4464
70°	7086	4390	3770
75°	6349	3540	3019
80°	5408	2559	2125
85°	4199	1425	1142

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9083 cd/sqm

TEST NUMBER: P1001789

CATALOG NUMBER: SA4XXDIP-B795D1205UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.8	1.6
10°-20°	354.3	4.6
20°-30°	521.5	6.7
30°-40°	606.2	7.8
40°-50°	606.2	7.8
50°-60°	530.2	6.8
60°-70°	393.6	5.1
70°-80°	223.3	2.9
80°-90°	66.2	0.9
90°-100°	439.0	5.7
100°-110°	893.0	11.5
110°-120°	795.9	10.3
120°-130°	668.6	8.6
130°-140°	557.9	7.2
140°-150°	426.1	5.5
150°-160°	299.5	3.9
160°-170°	176.2	2.3
170°-180°	57.3	0.7
0°-30°	1001.6	12.9
0°-40°	1607.8	20.8
0°-60°	2744.1	35.5
0°-90°	3427.3	44.3
90°-120°	2127.9	27.5
90°-150°	3780.4	48.8
90°-180°	4313.0	55.7
0°-180°	7740.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1334	1334	1334	1334	1334	
5°	1333	1329	1317	1329	1327	127
15°	1269	1265	1249	1255	1252	358
25°	1149	1142	1127	1128	1124	529
35°	989	982	967	959	954	618
45°	807	800	783	771	768	622
55°	610	607	592	580	573	547
65°	414	408	398	387	382	410
75°	220	215	210	205	204	234
85°	58	58	56	56	54	62
90°	1	9	21	23	24	6
95°	38	121	946	469	283	42
105°	136	197	762	1640	1634	145
115°	239	300	679	1305	1569	237
125°	333	396	676	1111	1252	297
135°	396	471	670	986	1119	306
145°	456	523	666	831	914	286
155°	519	560	648	734	765	239
165°	566	583	621	658	668	160
175°	590	591	596	604	602	56
180°	591	591	591	591	591	

TEST NUMBER: P1001789

CATALOG NUMBER: SA4XXDIP-B795D1205UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1334.4	1334.4	1334.4	1334.4	1334.4
2.5°	1338.7	1335.5	1323.7	1334.4	1333.3
5°	1333.3	1329.1	1317.3	1329.1	1326.9
7.5°	1323.7	1319.4	1306.6	1316.2	1315.2
10°	1309.8	1305.5	1291.6	1300.2	1298.0
12.5°	1291.6	1287.4	1272.4	1282.0	1278.8
15°	1269.2	1264.9	1248.9	1255.3	1252.1
17.5°	1243.5	1238.2	1223.2	1227.5	1225.3
20°	1214.6	1209.3	1193.3	1196.5	1194.3
22.5°	1183.6	1176.2	1160.1	1166.5	1162.3
25°	1149.4	1141.9	1127.0	1128.0	1123.8
27.5°	1110.9	1103.4	1089.5	1087.4	1082.1
30°	1072.4	1063.9	1050.0	1045.7	1040.4
32.5°	1031.8	1024.3	1009.4	1004.0	998.7
35°	989.0	981.6	966.6	959.1	953.8
37.5°	944.1	937.7	921.7	914.2	906.7
40°	900.3	891.7	875.7	865.0	859.7
42.5°	853.2	849.0	830.8	818.0	814.8
45°	807.3	799.8	782.7	770.9	767.7
47.5°	759.2	753.8	737.8	724.9	716.4
50°	710.0	705.7	690.7	675.8	669.3
52.5°	661.9	656.5	640.5	627.6	619.1
55°	610.5	607.3	592.4	579.5	573.1
57.5°	562.4	559.2	544.2	531.4	525.0
60°	512.2	506.8	492.9	483.3	477.9
62.5°	463.0	458.7	443.7	435.2	429.8
65°	413.8	408.4	397.8	387.1	381.7
67.5°	363.5	359.3	348.6	337.9	336.8
70°	317.6	310.1	301.5	293.0	289.8
72.5°	268.4	260.9	254.5	248.1	244.9
75°	220.3	214.9	209.6	205.3	204.2
77.5°	173.2	171.1	165.7	164.7	161.5
80°	131.5	128.3	126.2	124.0	123.0
82.5°	90.9	89.8	89.8	88.7	87.7
85°	57.7	57.7	55.6	55.6	54.5
87.5°	27.8	26.7	25.7	25.7	25.7
90°	1.2	9.3	20.9	23.2	24.4
92.5°	16.3	89.4	455.2	150.4	105.7
95°	38.3	120.8	946.4	468.6	283.3
97.5°	63.9	133.5	1012.5	956.8	680.4
100°	88.2	151.0	933.6	1323.8	1064.8
102.5°	111.5	171.9	834.9	1553.6	1399.2
105°	135.9	196.8	761.7	1640.2	1633.8
107.5°	162.6	222.4	714.1	1614.0	1745.2
110°	189.3	247.9	692.1	1521.2	1747.6

TEST NUMBER: P1001789

CATALOG NUMBER: SA4XXDIP-B795D1205UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	214.8	273.5	681.6	1407.4	1679.1
115°	239.2	300.2	679.3	1305.2	1568.7
117.5°	264.7	325.2	678.1	1225.0	1460.8
120°	290.3	349.6	678.1	1171.0	1372.5
122.5°	313.5	373.3	677.0	1135.6	1302.8
125°	333.3	396.0	675.8	1110.6	1251.7
127.5°	351.8	416.8	673.5	1086.8	1219.2
130°	366.9	437.2	672.3	1058.4	1191.4
132.5°	382.0	454.6	671.2	1024.8	1160.0
135°	396.0	471.4	670.0	985.8	1119.4
137.5°	409.9	486.0	670.0	944.0	1071.8
140°	425.0	499.3	668.8	903.4	1019.5
142.5°	441.2	511.5	668.8	865.6	963.8
145°	456.3	522.6	666.5	831.4	913.8
147.5°	473.8	533.0	663.0	803.0	867.4
150°	490.0	542.8	659.5	776.8	829.1
152.5°	505.1	552.2	653.7	754.8	794.2
155°	519.0	560.3	647.9	733.8	765.2
157.5°	533.0	567.8	642.1	714.1	738.5
160°	545.8	574.2	635.2	694.4	714.1
162.5°	557.4	579.4	628.2	675.2	690.9
165°	565.5	582.9	621.2	657.8	667.7
167.5°	574.8	585.8	614.3	642.8	649.1
170°	580.6	588.2	607.3	627.6	631.7
172.5°	586.4	589.8	600.3	614.2	614.3
175°	589.9	591.0	595.7	603.8	601.5
177.5°	592.2	591.0	592.2	596.2	592.2
180°	591.0	591.0	591.0	591.0	591.0

(END OF REPORT)