

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001797

Luminaire Tested: SA4XXDIP-B795D1205UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001797
REPORT IS A COMBINATION OF REPORTS P996419 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1205UB35-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7627.0 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001797

CATALOG NUMBER: SA4XXDIP-B795D1205UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001797

CATALOG NUMBER: SA4XXDIP-B795D1205UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	45	44
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27
5	67	56	48	42	61	51	44	39	43	38	34	36	32	29	29	26	23
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16
9	49	37	30	25	45	35	28	23	29	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10929	10929	10929
5°	10938	10615	10627
10°	10845	10320	10247
15°	10690	9969	9820
20°	10491	9591	9376
25°	10268	9190	8898
30°	9998	8757	8374
35°	9719	8314	7867
40°	9427	7837	7328
45°	9122	7359	6824
50°	8785	6895	6266
55°	8417	6353	5711
60°	8041	5760	5134
65°	7611	5148	4484
70°	7117	4409	3786
75°	6374	3555	3032
80°	5433	2570	2133
85°	4221	1430	1149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9122 cd/sqm

TEST NUMBER: P1001797

CATALOG NUMBER: SA4XXDIP-B795D1205UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.7
10°-20°	355.9	4.7
20°-30°	523.8	6.9
30°-40°	608.9	8.0
40°-50°	608.8	8.0
50°-60°	532.5	7.0
60°-70°	395.3	5.2
70°-80°	224.3	2.9
80°-90°	67.5	0.9
90°-100°	98.3	1.3
100°-110°	294.4	3.9
110°-120°	500.1	6.6
120°-130°	659.6	8.6
130°-140°	740.8	9.7
140°-150°	728.1	9.5
150°-160°	612.4	8.0
160°-170°	407.5	5.3
170°-180°	142.7	1.9
0°-30°	1006.0	13.2
0°-40°	1614.9	21.2
0°-60°	2756.1	36.1
0°-90°	3443.2	45.1
90°-120°	892.8	11.7
90°-150°	3021.3	39.6
90°-180°	4184.0	54.9
0°-180°	7627.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1339	1335	1323	1335	1333	127
15°	1275	1270	1254	1261	1258	359
25°	1154	1147	1132	1133	1129	531
35°	993	986	971	963	958	621
45°	811	803	786	774	771	625
55°	613	610	595	582	576	549
65°	416	410	400	389	383	411
75°	221	216	210	206	205	235
85°	58	58	56	56	55	62
90°	4	16	26	33	35	9
95°	70	80	89	92	92	76
105°	272	273	278	281	284	288
115°	508	508	506	505	504	501
125°	740	740	739	737	735	660
135°	955	962	962	960	956	739
145°	1160	1165	1166	1165	1162	726
155°	1329	1329	1328	1333	1328	612
165°	1447	1444	1441	1448	1444	408
175°	1506	1500	1498	1507	1498	143
180°	1508	1508	1508	1508	1508	

TEST NUMBER: P1001797

CATALOG NUMBER: SA4XXDIP-B795D1205UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.2	1340.2	1340.2	1340.2	1340.2
2.5°	1344.5	1341.3	1329.5	1340.2	1339.2
5°	1339.2	1334.9	1323.1	1334.9	1332.7
7.5°	1329.5	1325.2	1312.3	1322.0	1320.9
10°	1315.5	1311.2	1297.3	1305.9	1303.7
12.5°	1297.3	1293.0	1278.0	1287.6	1284.4
15°	1274.7	1270.4	1254.3	1260.8	1257.6
17.5°	1249.0	1243.6	1228.6	1232.9	1230.7
20°	1220.0	1214.6	1198.5	1201.7	1199.6
22.5°	1188.8	1181.3	1165.2	1171.6	1167.3
25°	1154.5	1146.9	1131.9	1133.0	1128.7
27.5°	1115.8	1108.3	1094.3	1092.2	1086.8
30°	1077.1	1068.5	1054.6	1050.3	1044.9
32.5°	1036.3	1028.8	1013.8	1008.4	1003.0
35°	993.4	985.9	970.8	963.3	957.9
37.5°	948.3	941.8	925.7	918.2	910.7
40°	904.2	895.6	879.5	868.8	863.4
42.5°	857.0	852.7	834.4	821.5	818.3
45°	810.8	803.3	786.1	774.3	771.1
47.5°	762.5	757.1	741.0	728.1	719.5
50°	713.1	708.8	693.7	678.7	672.3
52.5°	664.8	659.4	643.3	630.4	621.8
55°	613.2	610.0	594.9	582.1	575.6
57.5°	564.9	561.7	546.6	533.7	527.3
60°	514.4	509.0	495.1	485.4	480.0
62.5°	465.0	460.7	445.7	437.1	431.7
65°	415.6	410.2	399.5	388.8	383.4
67.5°	365.1	360.8	350.1	339.4	338.3
70°	319.0	311.4	302.8	294.3	291.0
72.5°	269.6	262.0	255.6	249.1	245.9
75°	221.2	215.9	210.5	206.2	205.1
77.5°	174.0	171.8	166.5	165.4	162.2
80°	132.1	128.9	126.7	124.6	123.5
82.5°	91.3	90.2	90.2	89.1	88.1
85°	58.0	58.0	55.8	55.8	54.8
87.5°	27.9	26.8	25.8	25.8	25.8
90°	3.5	16.3	25.7	32.7	35.0
92.5°	30.3	45.5	51.3	54.8	56.0
95°	70.0	80.5	88.6	92.1	92.1
97.5°	112.0	121.3	130.6	135.3	135.3
100°	163.3	167.9	178.4	180.8	180.8
102.5°	216.9	218.1	227.4	230.9	232.1
105°	271.7	272.9	277.6	281.0	284.5
107.5°	328.9	330.0	331.2	335.9	334.7
110°	387.2	389.5	388.3	386.0	389.5

TEST NUMBER: P1001797

CATALOG NUMBER: SA4XXDIP-B795D1205UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	447.8	447.8	445.5	445.5	445.5
115°	508.5	508.5	506.1	505.0	503.8
117.5°	565.6	565.6	564.4	560.9	557.4
120°	622.7	627.4	623.9	618.1	620.4
122.5°	682.2	683.4	682.2	678.7	672.9
125°	740.5	740.5	739.4	737.0	734.7
127.5°	793.0	796.5	794.2	791.8	790.7
130°	849.0	852.5	852.5	850.1	845.5
132.5°	906.1	908.5	907.3	905.0	903.8
135°	955.1	962.1	962.1	959.8	956.3
137.5°	1009.9	1013.4	1015.7	1012.2	1013.4
140°	1064.7	1067.1	1067.1	1065.9	1064.7
142.5°	1114.9	1117.2	1116.0	1116.0	1116.0
145°	1160.3	1165.0	1166.2	1165.0	1161.5
147.5°	1207.0	1212.8	1211.7	1210.5	1209.3
150°	1249.0	1253.6	1253.6	1253.6	1252.5
152.5°	1288.6	1291.0	1292.1	1295.6	1292.1
155°	1329.4	1329.4	1328.3	1332.9	1328.3
157.5°	1364.4	1362.1	1362.1	1365.6	1362.1
160°	1394.7	1393.6	1392.4	1395.9	1390.1
162.5°	1422.7	1419.2	1418.1	1425.1	1419.2
165°	1447.2	1443.7	1441.4	1448.4	1443.7
167.5°	1467.1	1462.4	1462.4	1469.4	1462.4
170°	1483.4	1477.5	1478.7	1485.7	1477.5
172.5°	1495.0	1490.4	1490.4	1498.5	1490.4
175°	1505.5	1499.7	1498.5	1506.7	1498.5
177.5°	1510.2	1504.4	1504.4	1512.5	1503.2
180°	1507.9	1507.9	1507.9	1507.9	1507.9

(END OF REPORT)