

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008226

Luminaire Tested: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008226
REPORT IS A COMBINATION OF REPORTS P984734 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7812.9 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008226

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008226

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47			40
1	94	90	85	81	85	81	78	74	66	64	61	52	50	49	39	38	37			31
2	85	77	71	65	77	70	65	60	57	53	50	45	42	40	34	32	30			25
3	78	68	60	54	70	62	55	50	50	45	41	39	36	33	30	27	25			21
4	71	60	51	45	64	54	47	42	44	39	35	35	31	28	26	24	21			17
5	65	53	45	38	58	48	41	35	39	34	30	31	27	24	24	21	18			15
6	59	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16			13
7	55	42	34	29	50	39	32	27	32	26	22	25	21	18	19	16	14			11
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13			10
9	47	35	27	22	43	32	25	21	26	21	18	21	17	14	16	13	11			9
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10			8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14470	14470	14470
5°	14536	13853	13775
10°	14438	13373	13178
15°	14234	12876	12565
20°	13977	12355	11985
25°	13723	11856	11458
30°	13368	11348	10936
35°	13007	10860	10552
40°	12629	10437	10173
45°	12268	10054	9841
50°	11880	9701	9513
55°	11474	9326	9180
60°	10976	8935	8830
65°	10455	8485	8425
70°	9870	8002	7993
75°	9118	7519	7581
80°	7936	7018	7158
85°	6738	6544	6791

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12268 cd/sqm

TEST NUMBER: P1008226

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.7	1.1
10°-20°	248.5	3.2
20°-30°	376.6	4.8
30°-40°	458.6	5.9
40°-50°	493.4	6.3
50°-60°	479.2	6.1
60°-70°	418.5	5.4
70°-80°	322.1	4.1
80°-90°	218.3	2.8
90°-100°	197.4	2.5
100°-110°	289.9	3.7
110°-120°	552.4	7.1
120°-130°	837.2	10.7
130°-140°	863.6	11.1
140°-150°	789.9	10.1
150°-160°	632.7	8.1
160°-170°	407.7	5.2
170°-180°	140.3	1.8
0°-30°	711.8	9.1
0°-40°	1170.4	15.0
0°-60°	2142.9	27.4
0°-90°	3101.7	39.7
90°-120°	1039.8	13.3
90°-150°	3530.4	45.2
90°-180°	4711.0	60.3
0°-180°	7812.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	914	914	914	914	914	
5°	917	913	905	913	912	87
15°	874	877	877	889	888	246
25°	795	804	816	832	836	366
35°	685	708	733	762	771	428
45°	562	598	644	685	698	434
55°	431	478	547	595	612	385
65°	294	359	437	492	509	292
75°	163	237	322	379	396	172
85°	48	130	215	270	289	50
90°	14	103	196	255	273	13
95°	80	107	194	250	264	90
105°	331	401	179	237	256	354
115°	619	652	738	284	221	609
125°	870	884	946	990	1005	776
135°	1075	1092	1114	1153	1162	830
145°	1245	1244	1262	1278	1279	779
155°	1371	1361	1374	1380	1372	632
165°	1444	1438	1441	1449	1441	408
175°	1478	1470	1472	1480	1469	141
180°	1474	1474	1474	1474	1474	

TEST NUMBER: P1008226

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	914.1	914.1	914.1	914.1	914.1
2.5°	920.8	916.8	907.5	914.1	911.5
5°	916.8	912.8	904.9	912.8	911.5
7.5°	910.2	907.5	900.9	910.2	908.8
10°	902.2	899.6	895.6	906.2	904.9
12.5°	889.0	890.3	887.6	898.2	896.9
15°	874.4	877.0	877.0	889.0	887.6
17.5°	855.8	861.1	865.1	877.0	877.0
20°	837.3	843.9	849.2	863.8	863.8
22.5°	817.4	825.4	833.3	847.9	850.5
25°	794.9	804.2	816.1	832.0	836.0
27.5°	768.4	783.0	796.2	816.1	818.7
30°	741.9	759.1	776.3	797.5	801.5
32.5°	712.8	732.6	753.8	779.0	786.9
35°	684.9	707.5	732.6	761.8	771.0
37.5°	654.5	679.6	711.4	743.2	752.5
40°	624.0	653.1	688.9	723.4	735.3
42.5°	594.8	624.0	666.4	704.8	716.7
45°	561.7	597.5	643.9	684.9	698.2
47.5°	529.9	568.4	621.3	663.7	678.3
50°	496.8	537.9	597.5	642.5	657.1
52.5°	465.0	508.7	572.3	618.7	634.6
55°	430.6	478.3	547.2	594.8	612.1
57.5°	397.4	450.4	519.3	571.0	588.2
60°	361.7	418.6	494.2	544.5	563.1
62.5°	329.9	389.5	465.0	519.3	536.6
65°	294.1	359.0	437.2	491.5	508.7
67.5°	262.3	329.9	409.4	463.7	482.2
70°	227.9	296.8	378.9	435.9	451.8
72.5°	196.1	267.6	351.1	406.7	426.6
75°	163.0	237.1	321.9	378.9	396.1
77.5°	131.2	208.0	294.1	351.1	369.6
80°	99.4	180.2	266.3	321.9	340.5
82.5°	72.9	152.4	239.8	295.4	312.7
85°	47.7	129.8	214.6	270.3	288.8
87.5°	29.1	108.6	193.4	247.7	265.0
90°	14.3	102.9	196.2	254.6	272.6
92.5°	38.6	104.5	188.6	242.3	259.3
95°	79.9	107.0	194.0	249.6	264.5
97.5°	134.1	103.5	197.5	249.7	266.7
100°	198.1	101.0	193.3	250.8	267.6
102.5°	267.1	308.8	186.1	245.6	263.4
105°	330.9	401.3	179.0	237.1	256.0
107.5°	406.7	465.1	171.9	228.6	247.5
110°	477.9	526.8	283.4	219.1	238.0

TEST NUMBER: P1008226

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	546.2	586.6	629.4	211.9	229.7
115°	618.7	651.5	737.7	283.5	221.3
117.5°	680.4	712.3	786.1	673.3	407.0
120°	750.8	772.1	844.3	894.2	764.7
122.5°	810.5	828.9	899.2	941.5	954.4
125°	870.0	883.8	946.5	989.8	1004.9
127.5°	925.4	939.1	990.9	1034.6	1047.6
130°	977.7	993.5	1033.0	1076.5	1086.1
132.5°	1031.0	1043.6	1075.3	1115.4	1124.9
135°	1074.6	1091.6	1114.5	1153.0	1161.5
137.5°	1121.5	1134.3	1151.6	1187.4	1193.5
140°	1167.4	1174.6	1188.9	1219.7	1222.4
142.5°	1205.8	1211.9	1225.8	1250.3	1251.5
145°	1245.0	1244.0	1262.1	1277.5	1278.8
147.5°	1280.2	1277.0	1295.2	1301.8	1301.5
150°	1314.4	1306.9	1324.0	1330.4	1325.0
152.5°	1343.2	1334.6	1350.6	1357.0	1349.6
155°	1370.9	1361.3	1374.1	1380.5	1372.0
157.5°	1393.3	1384.8	1394.4	1401.8	1393.3
160°	1412.5	1406.1	1412.5	1418.9	1411.4
162.5°	1429.6	1423.2	1428.5	1436.0	1426.4
165°	1444.5	1438.1	1441.3	1448.8	1441.3
167.5°	1456.3	1449.9	1453.1	1460.5	1450.9
170°	1465.9	1459.5	1461.6	1469.1	1459.5
172.5°	1472.3	1465.9	1468.0	1475.5	1465.9
175°	1477.6	1470.1	1472.3	1479.7	1469.1
177.5°	1479.7	1472.3	1473.3	1480.8	1471.2
180°	1474.4	1474.4	1474.4	1474.4	1474.4

(END OF REPORT)