

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001803

Luminaire Tested: SA4XXDIP-B795D1205UB40-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001803
REPORT IS A COMBINATION OF REPORTS P996425 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1205UB40-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7382.0 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001803

CATALOG NUMBER: SA4XXDIP-B795D1205UB40-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001803

CATALOG NUMBER: SA4XXDIP-B795D1205UB40-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	47	47	41
1	95	90	86	82	86	82	79	75	67	65	62	53	52	50	41	39	38	38	38	32
2	86	78	72	67	78	71	66	61	58	54	51	46	44	41	35	33	32	32	32	27
3	78	68	61	55	71	62	56	51	51	46	42	41	37	34	31	29	27	27	27	22
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	27	25	23	23	23	19
5	65	54	45	39	59	49	42	36	40	35	31	32	28	25	25	22	20	20	20	16
6	60	48	40	34	54	44	37	31	36	31	27	29	25	22	22	19	17	17	17	14
7	55	43	35	29	50	40	32	27	33	27	23	26	22	19	20	17	15	15	15	12
8	51	39	31	26	47	36	29	24	30	24	20	24	20	17	19	16	13	13	13	11
9	48	36	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12	12	12	10
10	45	32	25	20	40	30	23	19	25	20	16	20	16	14	16	13	11	11	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7742	7742	7742
5°	7763	7541	7554
10°	7713	7392	7371
15°	7641	7225	7164
20°	7534	7044	6964
25°	7413	6845	6747
30°	7283	6648	6527
35°	7136	6446	6330
40°	7017	6253	6127
45°	6842	6071	5947
50°	6693	5865	5757
55°	6538	5665	5539
60°	6300	5418	5333
65°	6036	5152	5085
70°	5716	4846	4799
75°	5271	4507	4527
80°	4767	4162	4242
85°	4097	3813	4012

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6842 cd/sqm

TEST NUMBER: P1001803

CATALOG NUMBER: SA4XXDIP-B795D1205UB40-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	1.2
10°-20°	257.7	3.5
20°-30°	389.7	5.3
30°-40°	471.5	6.4
40°-50°	498.4	6.8
50°-60°	469.1	6.4
60°-70°	389.3	5.3
70°-80°	273.2	3.7
80°-90°	157.2	2.1
90°-100°	189.0	2.6
100°-110°	359.3	4.9
110°-120°	540.7	7.3
120°-130°	678.6	9.2
130°-140°	744.5	10.1
140°-150°	723.0	9.8
150°-160°	606.3	8.2
160°-170°	403.4	5.5
170°-180°	141.2	1.9
0°-30°	737.4	10.0
0°-40°	1208.9	16.4
0°-60°	2176.5	29.5
0°-90°	2996.1	40.6
90°-120°	1089.0	14.8
90°-150°	3235.0	43.8
90°-180°	4386.0	59.4
0°-180°	7382.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	949	949	949	949	949	
5°	950	947	940	948	947	90
15°	911	912	909	919	918	257
25°	834	840	843	855	856	384
35°	729	742	753	768	771	457
45°	608	628	648	667	672	470
55°	476	499	530	552	558	424
65°	330	364	400	426	435	327
75°	183	222	267	297	306	194
85°	56	101	149	181	191	59
90°	20	76	131	168	179	17
95°	83	129	180	212	222	86
105°	279	301	345	375	387	296
115°	510	519	551	573	580	503
125°	737	736	762	780	784	658
135°	948	954	962	977	980	733
145°	1150	1153	1154	1160	1160	720
155°	1316	1316	1315	1320	1315	606
165°	1433	1429	1427	1434	1429	404
175°	1490	1485	1484	1492	1484	142
180°	1493	1493	1493	1493	1493	

TEST NUMBER: P1001803

CATALOG NUMBER: SA4XXDIP-B795D1205UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	949.4	949.4	949.4	949.4	949.4
2.5°	953.7	950.5	942.0	949.4	948.4
5°	950.5	947.3	939.9	948.4	947.3
7.5°	944.1	942.0	935.6	945.2	944.1
10°	935.6	934.5	929.2	938.8	937.7
12.5°	923.9	923.9	920.7	929.2	929.2
15°	911.2	912.2	909.0	918.6	917.5
17.5°	894.1	897.3	896.3	905.8	904.8
20°	876.1	879.3	880.3	891.0	891.0
22.5°	855.9	860.1	862.2	872.9	875.0
25°	833.5	839.9	843.1	854.8	855.9
27.5°	809.1	818.7	822.9	833.5	834.6
30°	784.6	793.1	800.6	812.3	814.4
32.5°	758.1	768.7	777.2	791.0	793.1
35°	729.4	742.1	752.7	767.6	770.8
37.5°	700.6	715.5	728.3	743.2	746.4
40°	673.0	686.8	701.7	717.7	721.9
42.5°	641.1	657.1	675.1	693.2	696.4
45°	608.1	628.3	648.5	666.6	671.9
47.5°	577.3	597.5	620.9	639.0	645.4
50°	543.3	566.7	590.1	611.3	617.7
52.5°	509.3	532.7	560.3	581.6	587.9
55°	476.3	498.6	530.5	551.8	558.2
57.5°	439.1	466.7	497.6	523.1	528.4
60°	403.0	430.6	465.7	490.1	498.6
62.5°	367.9	398.7	433.8	458.2	466.7
65°	329.6	363.6	399.8	426.3	434.8
67.5°	293.4	329.6	367.9	394.4	403.0
70°	256.2	292.4	332.8	361.5	368.9
72.5°	220.1	257.3	300.9	328.5	337.0
75°	182.9	222.2	266.9	296.6	306.2
77.5°	147.8	189.2	236.0	265.8	276.4
80°	115.9	158.4	205.2	237.1	245.6
82.5°	84.0	128.6	175.4	208.4	218.0
85°	56.3	101.0	148.8	180.7	191.4
87.5°	35.1	78.7	125.5	156.3	165.9
90°	20.5	75.7	130.7	168.4	179.2
92.5°	45.9	98.2	149.7	182.9	192.6
95°	83.1	128.6	180.2	212.4	222.0
97.5°	123.6	163.7	216.5	248.7	258.3
100°	173.3	205.5	257.4	288.4	295.9
102.5°	226.4	251.0	300.6	331.7	341.3
105°	278.6	300.9	345.0	375.0	387.0
107.5°	335.2	354.3	392.8	423.9	430.2
110°	391.8	409.0	445.0	467.2	479.2

TEST NUMBER: P1001803

CATALOG NUMBER: SA4XXDIP-B795D1205UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	450.7	463.5	496.3	519.7	528.2
115°	509.8	519.3	551.0	573.3	579.5
117.5°	566.3	572.7	603.5	622.3	627.3
120°	621.8	629.6	656.9	672.5	683.3
122.5°	680.7	681.8	709.4	727.2	728.8
125°	737.4	736.3	761.7	779.6	783.6
127.5°	789.3	791.7	810.7	827.5	833.7
130°	843.7	846.0	863.0	879.9	881.7
132.5°	900.2	901.4	913.1	928.9	934.0
135°	947.6	954.5	962.0	976.7	979.7
137.5°	1001.9	1004.3	1010.9	1023.4	1029.8
140°	1056.1	1057.4	1058.4	1071.1	1075.3
142.5°	1104.8	1107.1	1104.8	1116.5	1120.7
145°	1149.8	1153.3	1154.5	1159.7	1160.5
147.5°	1196.0	1200.7	1199.5	1199.4	1202.5
150°	1237.5	1241.1	1241.1	1241.1	1239.9
152.5°	1275.7	1278.0	1279.2	1282.6	1279.2
155°	1316.1	1316.1	1315.0	1319.6	1315.0
157.5°	1350.7	1348.4	1348.4	1351.9	1348.4
160°	1380.8	1379.6	1378.4	1381.9	1376.1
162.5°	1408.5	1405.0	1403.8	1410.8	1405.0
165°	1432.7	1429.2	1426.9	1433.9	1429.2
167.5°	1452.3	1447.7	1447.7	1454.6	1447.7
170°	1468.5	1462.7	1463.9	1470.8	1462.7
172.5°	1480.0	1475.4	1475.4	1483.5	1475.4
175°	1490.4	1484.7	1483.5	1491.6	1483.5
177.5°	1495.1	1489.3	1489.3	1497.4	1488.1
180°	1492.7	1492.7	1492.7	1492.7	1492.7

(END OF REPORT)