

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008239

Luminaire Tested: S122DIP-B865D330UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008239
REPORT IS A COMBINATION OF REPORTS P984792 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D330UB2750-4F0-XX-W2A-D_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4750.0 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008239

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1008239

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64		
1	99	94	89	85	93	88	84	80	77	74	71	67	65	63	58	56	55	50		
2	89	81	74	68	83	76	70	64	67	62	57	58	54	51	50	47	45	41		
3	81	70	62	56	76	66	59	53	58	52	47	51	46	42	44	40	37	33		
4	74	62	53	47	69	58	50	44	51	45	40	45	40	36	39	35	32	28		
5	68	55	46	40	63	52	44	38	46	39	34	40	35	31	35	31	27	24		
6	62	49	41	34	58	46	38	33	41	35	30	36	31	27	31	27	24	21		
7	58	44	36	30	54	42	34	29	37	31	26	33	27	23	29	24	21	18		
8	54	40	32	26	50	38	31	25	34	28	23	30	25	21	26	22	19	16		
9	50	37	29	23	47	35	28	23	31	25	21	28	22	19	24	20	17	15		
10	47	34	26	21	44	32	25	20	29	23	19	25	20	17	22	18	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14283	14283	14283
5°	14349	13674	13596
10°	14252	13200	13008
15°	14050	12710	12404
20°	13797	12196	11829
25°	13546	11704	11310
30°	13195	11202	10795
35°	12840	10720	10417
40°	12465	10303	10041
45°	12110	9925	9714
50°	11727	9576	9390
55°	11325	9205	9062
60°	10833	8819	8716
65°	10320	8376	8318
70°	9740	7899	7888
75°	9001	7423	7484
80°	7832	6928	7066
85°	6653	6461	6704

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12110 cd/sqm

TEST NUMBER: P1008239

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.5	1.8
10°-20°	245.3	5.2
20°-30°	371.7	7.8
30°-40°	452.7	9.5
40°-50°	487.0	10.3
50°-60°	473.0	10.0
60°-70°	413.1	8.7
70°-80°	317.9	6.7
80°-90°	213.7	4.5
90°-100°	161.6	3.4
100°-110°	162.0	3.4
110°-120°	216.1	4.5
120°-130°	280.4	5.9
130°-140°	272.5	5.7
140°-150°	240.6	5.1
150°-160°	191.2	4.0
160°-170°	123.2	2.6
170°-180°	42.4	0.9
0°-30°	702.6	14.8
0°-40°	1155.3	24.3
0°-60°	2115.3	44.5
0°-90°	3059.9	64.4
90°-120°	539.7	11.4
90°-150°	1333.2	28.1
90°-180°	1690.0	35.6
0°-180°	4750.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	902	902	902	902	902	
5°	905	901	893	901	900	86
15°	863	866	866	878	876	243
25°	785	794	806	821	825	361
35°	676	698	723	752	761	423
45°	554	590	636	676	689	428
55°	425	472	540	587	604	380
65°	290	354	432	485	502	288
75°	161	234	318	374	391	170
85°	47	128	212	267	285	50
90°	13	93	179	233	249	10
95°	32	82	163	214	230	33
105°	104	152	132	181	197	112
115°	191	210	277	167	158	187
125°	265	269	317	354	367	237
135°	326	331	347	377	387	252
145°	376	376	381	392	396	236
155°	414	411	415	417	415	191
165°	436	435	436	438	436	123
175°	446	444	445	447	444	42
180°	446	446	446	446	446	

TEST NUMBER: P1008239

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	902.3	902.3	902.3	902.3	902.3
2.5°	908.9	905.0	895.8	902.3	899.7
5°	905.0	901.0	893.2	901.0	899.7
7.5°	898.4	895.8	889.3	898.4	897.1
10°	890.6	888.0	884.0	894.5	893.2
12.5°	877.5	878.8	876.2	886.6	885.3
15°	863.1	865.7	865.7	877.5	876.2
17.5°	844.8	850.0	854.0	865.7	865.7
20°	826.5	833.0	838.3	852.6	852.6
22.5°	806.9	814.7	822.6	836.9	839.6
25°	784.6	793.8	805.6	821.3	825.2
27.5°	758.5	772.9	785.9	805.6	808.2
30°	732.3	749.3	766.3	787.3	791.2
32.5°	703.6	723.2	744.1	768.9	776.8
35°	676.1	698.3	723.2	751.9	761.1
37.5°	646.0	670.9	702.3	733.6	742.8
40°	615.9	644.7	680.0	714.0	725.8
42.5°	587.2	615.9	657.8	695.7	707.5
45°	554.5	589.8	635.6	676.1	689.2
47.5°	523.1	561.0	613.3	655.2	669.6
50°	490.4	530.9	589.8	634.3	648.6
52.5°	459.0	502.2	564.9	610.7	626.4
55°	425.0	472.1	540.1	587.2	604.2
57.5°	392.3	444.6	512.6	563.6	580.6
60°	357.0	413.2	487.8	537.5	555.8
62.5°	325.6	384.5	459.0	512.6	529.6
65°	290.3	354.4	431.6	485.2	502.2
67.5°	258.9	325.6	404.1	457.7	476.0
70°	224.9	292.9	374.0	430.2	445.9
72.5°	193.5	264.2	346.5	401.5	421.1
75°	160.9	234.1	317.8	374.0	391.0
77.5°	129.5	205.3	290.3	346.5	364.9
80°	98.1	177.9	262.9	317.8	336.1
82.5°	71.9	150.4	236.7	291.6	308.6
85°	47.1	128.2	211.9	266.8	285.1
87.5°	28.8	107.2	190.9	244.5	261.5
90°	13.4	92.8	179.0	233.0	249.3
92.5°	19.9	87.9	168.6	220.3	236.2
95°	31.5	82.2	163.0	214.3	229.7
97.5°	46.9	76.7	157.6	207.0	223.0
100°	66.3	70.4	149.2	200.2	215.1
102.5°	86.1	128.7	140.6	191.3	206.6
105°	104.5	152.2	132.2	181.4	197.1
107.5°	127.4	166.9	123.6	171.7	187.3
110°	148.0	181.0	151.9	161.5	177.2



TEST NUMBER: P1008239

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	168.7	195.5	250.1	153.0	168.3
115°	190.6	210.5	277.4	167.3	158.5
117.5°	208.3	225.2	285.6	278.7	207.4
120°	229.6	239.7	297.8	338.3	309.2
122.5°	247.6	254.1	308.9	346.2	358.3
125°	264.7	268.9	316.9	354.5	367.2
127.5°	281.5	284.7	324.8	360.7	372.9
130°	297.3	301.1	332.2	367.1	377.2
132.5°	313.4	316.3	339.4	372.4	382.6
135°	325.6	330.8	346.8	377.4	387.3
137.5°	339.8	343.7	353.4	381.5	389.7
140°	353.7	355.0	361.1	384.9	391.2
142.5°	365.3	366.2	370.4	388.7	393.6
145°	376.2	375.9	381.4	391.5	396.4
147.5°	386.9	385.9	391.4	394.3	396.9
150°	397.2	394.9	400.1	402.0	400.4
152.5°	405.9	403.3	408.2	410.1	407.8
155°	414.3	411.4	415.3	417.2	414.6
157.5°	421.1	418.5	421.4	423.6	421.1
160°	426.9	424.9	426.9	428.8	426.5
162.5°	432.0	430.1	431.7	434.0	431.0
165°	436.5	434.6	435.6	437.8	435.6
167.5°	440.1	438.1	439.1	441.4	438.5
170°	443.0	441.0	441.7	443.9	441.0
172.5°	444.9	443.0	443.6	445.9	443.0
175°	446.5	444.3	444.9	447.2	443.9
177.5°	447.2	444.9	445.2	447.5	444.6
180°	445.6	445.6	445.6	445.6	445.6

(END OF REPORT)