

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008245

Luminaire Tested: S122DIP-B865D330UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008245
REPORT IS A COMBINATION OF REPORTS P984798 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D330UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4809.0 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008245

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008245

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	73
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	66	65	65	65	61
2	94	86	80	74	89	82	76	71	74	69	65	67	63	60	60	57	55	55	55	51
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	47	47	43
4	78	67	59	53	74	64	56	51	58	52	47	53	48	44	47	44	40	40	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	35	35	32
6	66	54	45	39	63	52	44	38	47	41	36	43	37	33	39	34	31	31	31	28
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	28	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25	25	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	22	22	20
10	50	38	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20	20	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21715	21715	21715
5°	21750	20698	20551
10°	21572	19755	19363
15°	21257	18804	18112
20°	20830	17770	16928
25°	20403	16691	15747
30°	19868	15677	14505
35°	19364	14605	13287
40°	18739	13549	12135
45°	18121	12501	11007
50°	17443	11436	9834
55°	16728	10296	8724
60°	15931	9062	7571
65°	15052	7808	6357
70°	13936	6435	5134
75°	12396	4961	3964
80°	10531	3370	2550
85°	7642	1567	1086

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18121 cd/sqm

TEST NUMBER: P1008245

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	2.7
10°-20°	363.3	7.6
20°-30°	533.8	11.1
30°-40°	620.0	12.9
40°-50°	619.2	12.9
50°-60°	540.0	11.2
60°-70°	399.1	8.3
70°-80°	225.8	4.7
80°-90°	60.4	1.3
90°-100°	14.8	0.3
100°-110°	55.3	1.1
110°-120°	146.6	3.0
120°-130°	243.1	5.1
130°-140°	258.3	5.4
140°-150°	240.0	5.0
150°-160°	193.0	4.0
160°-170°	124.3	2.6
170°-180°	42.8	0.9
0°-30°	1026.2	21.3
0°-40°	1646.2	34.2
0°-60°	2805.4	58.3
0°-90°	3490.8	72.6
90°-120°	216.7	4.5
90°-150°	958.1	19.9
90°-180°	1318.0	27.4
0°-180°	4809.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1279	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	985	977	971	637
45°	830	820	801	786	781	640
55°	628	620	604	588	582	561
65°	423	416	402	390	384	419
75°	222	219	212	204	207	236
85°	54	53	51	48	46	60
90°	0	4	6	8	9	4
95°	21	10	13	14	14	25
105°	99	109	20	23	25	106
115°	187	193	201	50	27	184
125°	264	269	275	277	278	236
135°	327	332	335	339	338	253
145°	380	379	385	387	386	237
155°	418	415	419	421	418	193
165°	440	439	440	442	440	124
175°	451	448	449	451	448	43
180°	450	450	450	450	450	

TEST NUMBER: P1008245

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1371.8	1371.8	1371.8	1371.8	1371.8
2.5°	1379.7	1373.1	1358.6	1371.8	1369.1
5°	1371.8	1366.5	1352.0	1362.5	1359.9
7.5°	1362.5	1354.6	1340.1	1350.7	1348.0
10°	1348.0	1338.8	1323.0	1333.5	1329.6
12.5°	1328.2	1320.3	1304.5	1311.1	1308.5
15°	1305.8	1297.9	1280.8	1286.0	1279.4
17.5°	1278.1	1270.2	1253.1	1259.7	1253.1
20°	1247.8	1239.9	1221.4	1225.4	1220.1
22.5°	1217.4	1205.6	1188.4	1188.4	1185.8
25°	1181.8	1171.3	1148.9	1151.5	1148.9
27.5°	1142.3	1133.0	1115.9	1111.9	1105.3
30°	1102.7	1092.1	1072.4	1068.4	1063.1
32.5°	1060.5	1052.6	1031.5	1023.6	1018.3
35°	1019.6	1006.4	985.3	977.4	970.8
37.5°	973.4	961.6	940.5	931.2	924.6
40°	925.9	915.4	894.3	882.4	877.1
42.5°	879.8	869.2	848.1	834.9	827.0
45°	829.7	820.4	800.6	786.1	780.9
47.5°	780.9	771.6	750.5	736.0	728.1
50°	729.4	722.8	704.4	685.9	679.3
52.5°	679.3	670.1	652.9	638.4	629.2
55°	627.8	619.9	604.1	588.3	581.7
57.5°	576.4	569.8	552.7	536.8	531.6
60°	525.0	519.7	501.2	486.7	482.8
62.5°	474.8	465.6	452.4	439.2	434.0
65°	423.4	415.5	402.3	390.4	383.8
67.5°	370.6	364.0	352.2	342.9	337.7
70°	321.8	316.6	304.7	295.5	290.2
72.5°	271.7	266.4	259.8	250.6	246.7
75°	221.6	219.0	212.4	204.4	207.1
77.5°	176.7	171.5	168.8	164.9	160.9
80°	131.9	130.6	127.9	124.0	121.3
82.5°	89.7	89.7	88.4	83.1	83.1
85°	54.1	52.8	51.4	47.5	46.2
87.5°	23.7	21.1	18.5	14.5	13.2
90°	0.3	3.9	6.5	8.1	8.8
92.5°	8.1	6.8	7.8	8.5	8.8
95°	21.1	10.4	12.7	14.3	14.0
97.5°	38.1	11.4	16.6	17.6	17.9
100°	57.6	13.0	18.5	21.1	21.8
102.5°	79.1	78.4	19.2	22.8	23.8
105°	98.9	108.7	19.8	23.4	24.7
107.5°	122.0	130.1	20.5	24.1	25.4
110°	144.1	151.0	56.9	24.4	25.7



TEST NUMBER: P1008245

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	165.0	170.8	165.3	25.1	26.0
115°	187.1	192.6	200.7	50.1	26.7
117.5°	206.3	212.8	218.3	171.8	86.5
120°	227.8	232.6	238.5	242.4	198.5
122.5°	246.0	251.2	257.7	259.6	260.0
125°	264.5	268.7	274.9	277.2	278.2
127.5°	281.4	286.0	290.9	294.1	294.5
130°	297.4	302.6	306.2	309.7	309.4
132.5°	313.6	317.9	321.5	324.4	324.1
135°	327.3	332.5	335.4	338.7	338.0
137.5°	341.6	345.5	348.8	352.0	351.1
140°	355.6	358.2	361.8	364.7	363.1
142.5°	367.3	369.6	373.8	376.4	374.8
145°	379.7	379.4	384.9	387.2	385.6
147.5°	390.4	389.5	395.0	396.6	395.3
150°	400.8	398.6	403.8	405.7	404.1
152.5°	409.6	407.0	411.9	413.9	411.6
155°	418.1	415.2	419.1	421.0	418.4
157.5°	424.9	422.3	425.2	427.5	424.9
160°	430.8	428.8	430.8	432.7	430.5
162.5°	436.0	434.0	435.7	437.9	435.0
165°	440.5	438.6	439.6	441.8	439.6
167.5°	444.1	442.2	443.1	445.4	442.5
170°	447.0	445.1	445.7	448.0	445.1
172.5°	449.0	447.0	447.7	450.0	447.0
175°	450.6	448.3	449.0	451.3	448.0
177.5°	451.3	449.0	449.3	451.6	448.7
180°	449.6	449.6	449.6	449.6	449.6

(END OF REPORT)