

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001821

Luminaire Tested: SA4XXDIP-B795D365UB27-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001821
REPORT IS A COMBINATION OF REPORTS P996443 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB27-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4493.0 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001821

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001821

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71
1	100	95	91	87	94	90	86	82	79	76	73	70	67	65	61	59	58
2	91	82	75	70	85	78	71	66	69	64	60	60	57	53	53	50	47
3	82	72	64	57	77	68	61	55	60	54	50	53	48	45	46	43	40
4	75	63	55	48	70	60	52	46	53	47	42	47	42	38	41	37	34
5	69	56	48	41	64	53	45	39	47	41	36	42	37	33	37	33	29
6	63	51	42	36	59	48	40	34	43	36	31	38	32	28	33	29	26
7	59	46	37	31	55	43	35	30	39	32	27	34	29	25	30	26	23
8	54	41	33	28	51	39	32	26	35	29	24	31	26	22	28	23	20
9	51	38	30	25	48	36	29	24	32	26	22	29	24	20	26	21	18
10	47	35	27	22	45	33	26	21	30	24	20	27	22	18	24	20	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7721	7721	7721
5°	7742	7519	7533
10°	7692	7371	7350
15°	7619	7205	7144
20°	7513	7025	6944
25°	7393	6827	6729
30°	7263	6630	6508
35°	7116	6428	6313
40°	6997	6236	6110
45°	6824	6054	5931
50°	6674	5848	5741
55°	6520	5650	5523
60°	6281	5403	5319
65°	6020	5136	5071
70°	5700	4833	4786
75°	5256	4494	4514
80°	4754	4149	4230
85°	4090	3803	3999

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6824 cd/sqm

TEST NUMBER: P1001821

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.7	2.0
10°-20°	257.0	5.7
20°-30°	388.6	8.6
30°-40°	470.2	10.5
40°-50°	497.1	11.1
50°-60°	467.8	10.4
60°-70°	388.2	8.6
70°-80°	272.4	6.1
80°-90°	154.5	3.4
90°-100°	121.1	2.7
100°-110°	156.7	3.5
110°-120°	196.5	4.4
120°-130°	224.9	5.0
130°-140°	234.9	5.2
140°-150°	222.2	4.9
150°-160°	185.0	4.1
160°-170°	123.1	2.7
170°-180°	43.1	1.0
0°-30°	735.4	16.4
0°-40°	1205.6	26.8
0°-60°	2170.4	48.3
0°-90°	2985.6	66.4
90°-120°	474.3	10.6
90°-150°	1156.2	25.7
90°-180°	1507.0	33.5
0°-180°	4493.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	948	945	937	946	945	90
15°	909	910	906	916	915	256
25°	831	838	841	852	854	383
35°	727	740	751	766	769	455
45°	606	627	647	665	670	469
55°	475	497	529	550	557	423
65°	329	363	399	425	434	326
75°	182	222	266	296	305	194
85°	56	101	148	180	191	59
90°	18	64	113	146	155	13
95°	35	73	119	149	158	34
105°	92	113	154	181	191	98
115°	160	170	203	226	233	158
125°	228	227	253	272	278	203
135°	291	293	300	316	322	225
145°	352	352	352	358	362	220
155°	402	402	401	403	401	185
165°	437	436	436	438	436	123
175°	455	453	453	455	453	43
180°	456	456	456	456	456	

TEST NUMBER: P1001821

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	946.8	946.8	946.8	946.8	946.8
2.5°	951.0	947.9	939.4	946.8	945.7
5°	947.9	944.7	937.2	945.7	944.7
7.5°	941.5	939.4	933.0	942.6	941.5
10°	933.0	931.9	926.6	936.2	935.1
12.5°	921.3	921.3	918.2	926.6	926.6
15°	908.6	909.7	906.5	916.0	915.0
17.5°	891.7	894.8	893.8	903.3	902.3
20°	873.6	876.8	877.9	888.5	888.5
22.5°	853.5	857.7	859.9	870.5	872.6
25°	831.2	837.6	840.8	852.4	853.5
27.5°	806.8	816.4	820.6	831.2	832.3
30°	782.5	790.9	798.4	810.0	812.1
32.5°	755.9	766.6	775.0	788.8	790.9
35°	727.3	740.0	750.6	765.5	768.7
37.5°	698.7	713.5	726.3	741.1	744.3
40°	671.1	684.9	699.8	715.7	719.9
42.5°	639.3	655.2	673.3	691.3	694.5
45°	606.5	626.6	646.7	664.8	670.1
47.5°	575.7	595.9	619.2	637.2	643.6
50°	541.8	565.1	588.4	609.6	616.0
52.5°	507.9	531.2	558.7	579.9	586.3
55°	475.0	497.3	529.1	550.3	556.6
57.5°	437.9	465.4	496.2	521.6	526.9
60°	401.8	429.4	464.4	488.8	497.3
62.5°	366.8	397.6	432.6	457.0	465.4
65°	328.7	362.6	398.6	425.2	433.6
67.5°	292.6	328.7	366.8	393.3	401.8
70°	255.5	291.6	331.9	360.5	367.9
72.5°	219.5	256.6	300.0	327.6	336.1
75°	182.4	221.6	266.1	295.8	305.3
77.5°	147.4	188.7	235.4	265.1	275.7
80°	115.6	158.0	204.6	236.4	244.9
82.5°	83.8	128.3	174.9	207.8	217.3
85°	56.2	100.7	148.4	180.2	190.8
87.5°	35.0	78.5	125.1	155.9	165.4
90°	18.1	64.3	112.8	145.6	154.8
92.5°	25.1	66.7	114.1	144.9	153.7
95°	34.9	73.1	119.0	148.7	158.2
97.5°	46.5	80.1	126.4	155.4	164.9
100°	61.0	89.9	134.5	163.8	171.2
102.5°	77.2	100.9	144.0	172.6	181.4
105°	91.6	113.1	153.9	181.4	191.0
107.5°	108.9	127.3	164.8	192.7	199.7
110°	125.5	141.0	177.7	201.4	211.0



TEST NUMBER: P1001821

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	142.7	155.4	189.7	213.1	221.5
115°	160.0	169.5	202.7	225.8	232.8
117.5°	177.3	183.6	215.0	236.3	243.7
120°	193.4	198.1	227.7	247.1	256.3
122.5°	211.4	211.8	240.0	260.2	265.9
125°	227.9	226.9	253.1	272.5	278.2
127.5°	243.8	243.8	264.3	282.7	289.8
130°	259.7	259.7	276.7	295.1	299.9
132.5°	277.0	276.6	288.9	306.3	312.3
135°	290.7	292.8	300.2	316.5	321.8
137.5°	307.2	307.3	312.2	327.0	332.7
140°	323.8	323.5	324.5	337.9	342.9
142.5°	337.9	338.6	337.2	348.9	353.1
145°	351.7	352.0	352.3	358.4	361.5
147.5°	365.8	366.4	366.1	366.8	370.7
150°	378.4	378.8	378.8	378.8	378.4
152.5°	389.3	390.0	390.4	391.4	390.4
155°	401.7	401.7	401.3	402.7	401.3
157.5°	412.2	411.5	411.5	412.6	411.5
160°	421.4	421.0	420.7	421.7	420.0
162.5°	429.8	428.8	428.4	430.5	428.8
165°	437.2	436.2	435.5	437.6	436.2
167.5°	443.2	441.8	441.8	443.9	441.8
170°	448.2	446.4	446.8	448.9	446.4
172.5°	451.7	450.3	450.3	452.7	450.3
175°	454.9	453.1	452.7	455.2	452.7
177.5°	456.3	454.5	454.5	457.0	454.2
180°	455.6	455.6	455.6	455.6	455.6

(END OF REPORT)