

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001822

Luminaire Tested: SA4XXDIP-B795D365UB27-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001822
REPORT IS A COMBINATION OF REPORTS P996444 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB27-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4538.6 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001822

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001822

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	100	95	90	86	94	89	85	82	79	76	73	69	67	65	60	59	57
2	91	82	75	70	85	77	71	66	68	64	59	60	56	53	52	49	47
3	82	72	64	57	77	68	60	55	60	54	49	53	48	44	46	42	39
4	75	63	55	48	70	60	52	46	53	47	42	47	42	38	41	37	34
5	69	56	48	41	64	53	45	39	47	41	36	42	36	32	37	32	29
6	63	50	42	36	59	48	40	34	42	36	31	38	32	28	33	29	25
7	59	46	37	31	55	43	35	30	38	32	27	34	29	25	30	26	22
8	54	41	33	27	51	39	32	26	35	29	24	31	26	22	28	23	20
9	51	38	30	25	48	36	29	24	32	26	22	29	24	20	25	21	18
10	47	35	27	22	44	33	26	21	30	24	20	27	22	18	24	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7721	7721	7721
5°	7742	7519	7533
10°	7692	7371	7350
15°	7619	7205	7144
20°	7513	7025	6944
25°	7393	6827	6729
30°	7263	6630	6508
35°	7116	6428	6313
40°	6997	6236	6110
45°	6824	6054	5931
50°	6674	5848	5741
55°	6520	5650	5523
60°	6281	5403	5319
65°	6020	5136	5071
70°	5700	4833	4786
75°	5256	4494	4514
80°	4754	4149	4230
85°	4090	3803	3999

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6824 cd/sqm

TEST NUMBER: P1001822

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.7	2.0
10°-20°	257.0	5.7
20°-30°	388.6	8.6
30°-40°	470.2	10.4
40°-50°	497.1	11.0
50°-60°	467.8	10.3
60°-70°	388.2	8.6
70°-80°	272.4	6.0
80°-90°	154.3	3.4
90°-100°	224.8	5.0
100°-110°	338.9	7.5
110°-120°	287.1	6.3
120°-130°	228.6	5.0
130°-140°	180.5	4.0
140°-150°	131.6	2.9
150°-160°	91.0	2.0
160°-170°	53.5	1.2
170°-180°	17.4	0.4
0°-30°	735.4	16.2
0°-40°	1205.6	26.6
0°-60°	2170.4	47.8
0°-90°	2985.3	65.8
90°-120°	850.8	18.7
90°-150°	1391.5	30.7
90°-180°	1553.0	34.2
0°-180°	4538.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	948	945	937	946	945	90
15°	909	910	906	916	915	256
25°	831	838	841	852	854	383
35°	727	740	751	766	769	455
45°	606	627	647	665	670	469
55°	475	497	529	550	557	423
65°	329	363	399	425	434	326
75°	182	222	266	296	305	194
85°	56	101	148	180	191	59
90°	17	62	111	143	152	12
95°	25	86	380	263	216	24
105°	51	90	301	595	601	55
115°	79	107	256	470	557	79
125°	105	123	235	387	436	94
135°	122	145	213	326	373	95
145°	140	159	202	259	288	88
155°	158	170	197	223	232	73
165°	172	177	189	200	203	49
175°	179	180	181	183	183	17
180°	180	180	180	180	180	

TEST NUMBER: P1001822

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	946.8	946.8	946.8	946.8	946.8
2.5°	951.0	947.9	939.4	946.8	945.7
5°	947.9	944.7	937.2	945.7	944.7
7.5°	941.5	939.4	933.0	942.6	941.5
10°	933.0	931.9	926.6	936.2	935.1
12.5°	921.3	921.3	918.2	926.6	926.6
15°	908.6	909.7	906.5	916.0	915.0
17.5°	891.7	894.8	893.8	903.3	902.3
20°	873.6	876.8	877.9	888.5	888.5
22.5°	853.5	857.7	859.9	870.5	872.6
25°	831.2	837.6	840.8	852.4	853.5
27.5°	806.8	816.4	820.6	831.2	832.3
30°	782.5	790.9	798.4	810.0	812.1
32.5°	755.9	766.6	775.0	788.8	790.9
35°	727.3	740.0	750.6	765.5	768.7
37.5°	698.7	713.5	726.3	741.1	744.3
40°	671.1	684.9	699.8	715.7	719.9
42.5°	639.3	655.2	673.3	691.3	694.5
45°	606.5	626.6	646.7	664.8	670.1
47.5°	575.7	595.9	619.2	637.2	643.6
50°	541.8	565.1	588.4	609.6	616.0
52.5°	507.9	531.2	558.7	579.9	586.3
55°	475.0	497.3	529.1	550.3	556.6
57.5°	437.9	465.4	496.2	521.6	526.9
60°	401.8	429.4	464.4	488.8	497.3
62.5°	366.8	397.6	432.6	457.0	465.4
65°	328.7	362.6	398.6	425.2	433.6
67.5°	292.6	328.7	366.8	393.3	401.8
70°	255.5	291.6	331.9	360.5	367.9
72.5°	219.5	256.6	300.0	327.6	336.1
75°	182.4	221.6	266.1	295.8	305.3
77.5°	147.4	188.7	235.4	265.1	275.7
80°	115.6	158.0	204.6	236.4	244.9
82.5°	83.8	128.3	174.9	207.8	217.3
85°	56.2	100.7	148.4	180.2	190.8
87.5°	35.0	78.5	125.1	155.9	165.4
90°	17.4	62.2	111.3	142.8	151.6
92.5°	20.8	80.2	236.8	174.0	168.9
95°	25.4	85.5	379.6	263.2	216.4
97.5°	32.1	84.0	394.4	405.0	330.6
100°	38.5	85.1	364.1	511.2	440.0
102.5°	45.6	87.2	328.8	574.6	536.2
105°	50.8	90.5	301.3	594.6	601.2
107.5°	58.9	95.1	281.6	581.4	628.6
110°	66.0	98.6	270.6	546.8	624.0



TEST NUMBER: P1001822

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	72.6	103.2	262.1	505.9	596.8
115°	79.0	107.0	256.1	469.6	557.0
117.5°	86.8	111.4	250.4	438.8	518.9
120°	93.5	114.6	245.1	416.0	485.7
122.5°	100.5	118.6	239.5	400.0	458.3
125°	105.4	123.4	234.9	387.1	436.3
127.5°	111.0	129.8	228.9	373.5	421.2
130°	114.6	134.9	223.3	359.7	406.3
132.5°	119.2	140.2	218.6	344.1	391.5
135°	122.3	145.3	213.0	325.9	372.8
137.5°	126.6	148.7	208.8	307.9	352.0
140°	131.2	152.8	205.2	290.2	330.8
142.5°	135.1	156.5	203.1	274.6	308.6
145°	139.7	158.7	202.4	258.9	288.1
147.5°	145.0	161.9	201.4	245.0	268.7
150°	149.9	164.8	200.3	235.9	251.8
152.5°	153.4	167.7	198.5	229.2	241.2
155°	157.6	170.2	196.8	222.9	232.4
157.5°	161.9	172.4	195.0	216.8	224.3
160°	165.7	174.4	192.9	210.9	216.9
162.5°	169.3	176.0	190.8	205.0	209.8
165°	171.7	177.0	188.7	199.8	202.8
167.5°	174.6	177.9	186.5	195.2	197.1
170°	176.3	178.6	184.4	190.6	191.8
172.5°	178.1	179.2	182.3	186.6	186.5
175°	179.1	179.5	180.9	183.4	182.7
177.5°	179.8	179.5	179.8	181.1	179.8
180°	179.5	179.5	179.5	179.5	179.5

(END OF REPORT)