

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001824

Luminaire Tested: SA4XXDIP-B795D365UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001824
REPORT IS A COMBINATION OF REPORTS P996446 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB27-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4661.0 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001824

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001824

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	67	65
2	94	86	80	74	89	82	76	71	74	69	65	67	63	60	60	57	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35
6	66	54	45	39	63	51	44	38	47	41	36	43	37	33	39	34	31
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10789	10789	10789
5°	10798	10479	10492
10°	10706	10188	10117
15°	10553	9842	9694
20°	10357	9468	9255
25°	10136	9072	8784
30°	9870	8645	8267
35°	9595	8208	7766
40°	9307	7737	7234
45°	9005	7265	6737
50°	8673	6807	6186
55°	8310	6272	5639
60°	7938	5686	5069
65°	7514	5082	4427
70°	7025	4354	3738
75°	6294	3509	2994
80°	5363	2537	2106
85°	4162	1412	1134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9005 cd/sqm

TEST NUMBER: P1001824

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	2.7
10°-20°	351.3	7.5
20°-30°	517.1	11.1
30°-40°	601.1	12.9
40°-50°	601.0	12.9
50°-60°	525.7	11.3
60°-70°	390.3	8.4
70°-80°	221.4	4.8
80°-90°	64.4	1.4
90°-100°	29.7	0.6
100°-110°	88.9	1.9
110°-120°	151.1	3.2
120°-130°	199.3	4.3
130°-140°	223.8	4.8
140°-150°	220.0	4.7
150°-160°	185.0	4.0
160°-170°	123.1	2.6
170°-180°	43.1	0.9
0°-30°	993.1	21.3
0°-40°	1594.2	34.2
0°-60°	2720.9	58.4
0°-90°	3397.0	72.9
90°-120°	269.7	5.8
90°-150°	912.8	19.6
90°-180°	1264.0	27.1
0°-180°	4661.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1323	1323	1323	1323	1323	
5°	1322	1318	1306	1318	1316	125
15°	1258	1254	1238	1245	1242	355
25°	1140	1132	1117	1118	1114	524
35°	981	973	958	951	946	613
45°	800	793	776	764	761	617
55°	605	602	587	575	568	542
65°	410	405	394	384	378	406
75°	218	213	208	204	202	232
85°	57	57	55	55	54	62
90°	1	5	8	10	11	5
95°	21	24	27	28	28	23
105°	82	82	84	85	86	87
115°	154	154	153	153	152	152
125°	224	224	223	223	222	199
135°	289	291	291	290	289	223
145°	351	352	352	352	351	219
155°	402	402	401	403	401	185
165°	437	436	436	438	436	123
175°	455	453	453	455	453	43
180°	456	456	456	456	456	

TEST NUMBER: P1001824

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1323.1	1323.1	1323.1	1323.1	1323.1
2.5°	1327.3	1324.2	1312.5	1323.1	1322.0
5°	1322.0	1317.8	1306.1	1317.8	1315.7
7.5°	1312.5	1308.3	1295.5	1305.1	1304.0
10°	1298.7	1294.5	1280.7	1289.2	1287.1
12.5°	1280.7	1276.5	1261.6	1271.2	1268.0
15°	1258.4	1254.2	1238.3	1244.6	1241.5
17.5°	1233.0	1227.7	1212.8	1217.1	1215.0
20°	1204.4	1199.1	1183.2	1186.3	1184.2
22.5°	1173.6	1166.2	1150.3	1156.7	1152.4
25°	1139.7	1132.3	1117.4	1118.5	1114.2
27.5°	1101.5	1094.1	1080.3	1078.2	1072.9
30°	1063.4	1054.9	1041.1	1036.9	1031.6
32.5°	1023.1	1015.7	1000.8	995.5	990.2
35°	980.7	973.2	958.4	951.0	945.7
37.5°	936.1	929.8	913.9	906.5	899.0
40°	892.7	884.2	868.3	857.7	852.4
42.5°	846.0	841.8	823.8	811.0	807.9
45°	800.4	793.0	776.1	764.4	761.2
47.5°	752.7	747.4	731.5	718.8	710.3
50°	704.0	699.7	684.9	670.0	663.7
52.5°	656.3	650.9	635.0	622.3	613.8
55°	605.4	602.2	587.3	574.6	568.3
57.5°	557.7	554.5	539.6	526.9	520.5
60°	507.8	502.5	488.7	479.2	473.9
62.5°	459.1	454.8	440.0	431.5	426.2
65°	410.3	405.0	394.4	383.8	378.5
67.5°	360.5	356.2	345.6	335.0	334.0
70°	314.9	307.5	299.0	290.5	287.3
72.5°	266.1	258.7	252.3	246.0	242.8
75°	218.4	213.1	207.8	203.6	202.5
77.5°	171.7	169.6	164.3	163.3	160.1
80°	130.4	127.2	125.1	123.0	121.9
82.5°	90.1	89.1	89.1	88.0	86.9
85°	57.2	57.2	55.1	55.1	54.1
87.5°	27.6	26.5	25.4	25.4	25.4
90°	1.1	4.9	7.8	9.9	10.6
92.5°	9.2	13.7	15.5	16.6	16.9
95°	21.1	24.3	26.8	27.8	27.8
97.5°	33.8	36.6	39.5	40.9	40.9
100°	49.3	50.7	53.9	54.6	54.6
102.5°	65.5	65.9	68.7	69.8	70.1
105°	82.1	82.4	83.9	84.9	86.0
107.5°	99.4	99.7	100.1	101.5	101.1
110°	117.0	117.7	117.3	116.6	117.7

TEST NUMBER: P1001824

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.3	135.3	134.6	134.6	134.6
115°	153.6	153.6	152.9	152.6	152.2
117.5°	170.9	170.9	170.5	169.5	168.4
120°	188.1	189.6	188.5	186.7	187.4
122.5°	206.1	206.5	206.1	205.1	203.3
125°	223.7	223.7	223.4	222.7	222.0
127.5°	239.6	240.6	239.9	239.2	238.9
130°	256.5	257.6	257.6	256.9	255.4
132.5°	273.8	274.5	274.1	273.4	273.1
135°	288.6	290.7	290.7	290.0	288.9
137.5°	305.1	306.2	306.9	305.8	306.2
140°	321.7	322.4	322.4	322.0	321.7
142.5°	336.8	337.5	337.2	337.2	337.2
145°	350.6	352.0	352.3	352.0	350.9
147.5°	364.7	366.4	366.1	365.7	365.4
150°	377.3	378.8	378.8	378.8	378.4
152.5°	389.3	390.0	390.4	391.4	390.4
155°	401.7	401.7	401.3	402.7	401.3
157.5°	412.2	411.5	411.5	412.6	411.5
160°	421.4	421.0	420.7	421.7	420.0
162.5°	429.8	428.8	428.4	430.5	428.8
165°	437.2	436.2	435.5	437.6	436.2
167.5°	443.2	441.8	441.8	443.9	441.8
170°	448.2	446.4	446.8	448.9	446.4
172.5°	451.7	450.3	450.3	452.7	450.3
175°	454.9	453.1	452.7	455.2	452.7
177.5°	456.3	454.5	454.5	457.0	454.2
180°	455.6	455.6	455.6	455.6	455.6

(END OF REPORT)