

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001825

Luminaire Tested: SA4XXDIP-B795D365UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001825
REPORT IS A COMBINATION OF REPORTS P996447 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB27-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4706.6 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001825

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001825

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76
1	103	98	94	91	97	93	90	86	84	81	79	75	73	71	68	66	65
2	94	86	79	74	88	82	76	71	74	69	65	66	63	60	59	57	54
3	85	75	68	62	81	72	65	59	65	59	55	59	54	50	53	49	46
4	78	67	59	52	74	64	56	50	58	52	47	52	47	43	47	43	40
5	72	60	51	45	68	57	49	44	52	45	41	47	42	38	42	38	35
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31
7	61	49	40	35	58	47	39	34	43	36	31	39	33	29	35	31	27
8	57	44	36	31	54	42	35	30	39	33	28	36	30	26	32	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	27	24	30	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	22	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10789	10789	10789
5°	10798	10479	10492
10°	10706	10188	10117
15°	10553	9842	9694
20°	10357	9468	9255
25°	10136	9072	8784
30°	9870	8645	8267
35°	9595	8208	7766
40°	9307	7737	7234
45°	9005	7265	6737
50°	8673	6807	6186
55°	8310	6272	5639
60°	7938	5686	5069
65°	7514	5082	4427
70°	7025	4354	3738
75°	6294	3509	2994
80°	5363	2537	2106
85°	4162	1412	1134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9005 cd/sqm

TEST NUMBER: P1001825

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	2.6
10°-20°	351.3	7.5
20°-30°	517.1	11.0
30°-40°	601.1	12.8
40°-50°	601.0	12.8
50°-60°	525.7	11.2
60°-70°	390.3	8.3
70°-80°	221.4	4.7
80°-90°	64.1	1.4
90°-100°	133.3	2.8
100°-110°	271.2	5.8
110°-120°	241.7	5.1
120°-130°	203.0	4.3
130°-140°	169.4	3.6
140°-150°	129.4	2.7
150°-160°	91.0	1.9
160°-170°	53.5	1.1
170°-180°	17.4	0.4
0°-30°	993.1	21.1
0°-40°	1594.2	33.9
0°-60°	2720.9	57.8
0°-90°	3396.7	72.2
90°-120°	646.2	13.7
90°-150°	1148.1	24.4
90°-180°	1310.0	27.8
0°-180°	4706.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1323	1323	1323	1323	1323	
5°	1322	1318	1306	1318	1316	125
15°	1258	1254	1238	1245	1242	355
25°	1140	1132	1117	1118	1114	524
35°	981	973	958	951	946	613
45°	800	793	776	764	761	617
55°	605	602	587	575	568	542
65°	410	405	394	384	378	406
75°	218	213	208	204	202	232
85°	57	57	55	55	54	62
90°	0	3	6	7	7	5
95°	12	37	287	142	86	13
105°	41	60	231	498	496	44
115°	73	91	206	396	476	72
125°	101	120	205	337	380	90
135°	120	143	204	299	340	93
145°	139	159	202	252	278	87
155°	158	170	197	223	232	73
165°	172	177	189	200	203	49
175°	179	180	181	183	183	17
180°	180	180	180	180	180	

TEST NUMBER: P1001825

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1323.1	1323.1	1323.1	1323.1	1323.1
2.5°	1327.3	1324.2	1312.5	1323.1	1322.0
5°	1322.0	1317.8	1306.1	1317.8	1315.7
7.5°	1312.5	1308.3	1295.5	1305.1	1304.0
10°	1298.7	1294.5	1280.7	1289.2	1287.1
12.5°	1280.7	1276.5	1261.6	1271.2	1268.0
15°	1258.4	1254.2	1238.3	1244.6	1241.5
17.5°	1233.0	1227.7	1212.8	1217.1	1215.0
20°	1204.4	1199.1	1183.2	1186.3	1184.2
22.5°	1173.6	1166.2	1150.3	1156.7	1152.4
25°	1139.7	1132.3	1117.4	1118.5	1114.2
27.5°	1101.5	1094.1	1080.3	1078.2	1072.9
30°	1063.4	1054.9	1041.1	1036.9	1031.6
32.5°	1023.1	1015.7	1000.8	995.5	990.2
35°	980.7	973.2	958.4	951.0	945.7
37.5°	936.1	929.8	913.9	906.5	899.0
40°	892.7	884.2	868.3	857.7	852.4
42.5°	846.0	841.8	823.8	811.0	807.9
45°	800.4	793.0	776.1	764.4	761.2
47.5°	752.7	747.4	731.5	718.8	710.3
50°	704.0	699.7	684.9	670.0	663.7
52.5°	656.3	650.9	635.0	622.3	613.8
55°	605.4	602.2	587.3	574.6	568.3
57.5°	557.7	554.5	539.6	526.9	520.5
60°	507.8	502.5	488.7	479.2	473.9
62.5°	459.1	454.8	440.0	431.5	426.2
65°	410.3	405.0	394.4	383.8	378.5
67.5°	360.5	356.2	345.6	335.0	334.0
70°	314.9	307.5	299.0	290.5	287.3
72.5°	266.1	258.7	252.3	246.0	242.8
75°	218.4	213.1	207.8	203.6	202.5
77.5°	171.7	169.6	164.3	163.3	160.1
80°	130.4	127.2	125.1	123.0	121.9
82.5°	90.1	89.1	89.1	88.0	86.9
85°	57.2	57.2	55.1	55.1	54.1
87.5°	27.6	26.5	25.4	25.4	25.4
90°	0.4	2.8	6.3	7.1	7.4
92.5°	4.9	27.2	138.2	45.7	32.1
95°	11.6	36.7	287.4	142.3	86.0
97.5°	19.4	40.6	307.5	290.6	206.6
100°	26.8	45.8	283.5	402.0	323.4
102.5°	33.9	52.2	253.5	471.8	424.9
105°	41.3	59.8	231.3	498.1	496.2
107.5°	49.4	67.5	216.9	490.2	530.0
110°	57.5	75.2	210.2	462.0	530.7

TEST NUMBER: P1001825

CATALOG NUMBER: SA4XXDIP-B795D365UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.2	83.0	207.0	427.4	509.9
115°	72.6	91.2	206.3	396.4	476.4
117.5°	80.4	98.8	205.9	372.0	443.6
120°	88.2	106.2	205.9	355.6	416.8
122.5°	95.2	113.4	205.6	344.9	395.7
125°	101.2	120.2	205.2	337.3	380.1
127.5°	106.8	126.6	204.5	330.0	370.3
130°	111.4	132.8	204.2	321.5	361.8
132.5°	116.0	138.0	203.8	311.2	352.3
135°	120.2	143.2	203.5	299.4	339.9
137.5°	124.5	147.6	203.5	286.7	325.5
140°	129.1	151.6	203.1	274.4	309.6
142.5°	134.0	155.4	203.1	262.9	292.7
145°	138.6	158.7	202.4	252.5	277.5
147.5°	143.9	161.9	201.4	243.8	263.4
150°	148.8	164.8	200.3	235.9	251.8
152.5°	153.4	167.7	198.5	229.2	241.2
155°	157.6	170.2	196.8	222.9	232.4
157.5°	161.9	172.4	195.0	216.8	224.3
160°	165.7	174.4	192.9	210.9	216.9
162.5°	169.3	176.0	190.8	205.0	209.8
165°	171.7	177.0	188.7	199.8	202.8
167.5°	174.6	177.9	186.5	195.2	197.1
170°	176.3	178.6	184.4	190.6	191.8
172.5°	178.1	179.2	182.3	186.6	186.5
175°	179.1	179.5	180.9	183.4	182.7
177.5°	179.8	179.5	179.8	181.1	179.8
180°	179.5	179.5	179.5	179.5	179.5

(END OF REPORT)