

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008271

Luminaire Tested: S122DIP-B865D725UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008271
REPORT IS A COMBINATION OF REPORTS P984914 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D725UB2750-4F0-XX-W2A-D_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6331.9 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008271

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008271

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49		
1	96	91	87	83	88	84	80	77	70	68	65	58	56	54	46	45	44	38		
2	87	79	72	66	80	73	67	62	61	56	53	50	47	44	40	38	36	31		
3	79	69	61	55	72	63	56	51	53	48	44	44	40	36	35	32	30	25		
4	72	60	52	46	66	56	48	43	47	41	37	39	34	31	31	28	25	21		
5	66	54	45	39	60	50	42	36	42	36	31	35	30	26	28	24	22	18		
6	61	48	40	33	55	44	37	31	37	32	27	31	26	23	25	22	19	16		
7	56	43	35	29	51	40	33	27	34	28	24	28	24	20	23	19	17	14		
8	52	39	31	26	47	36	29	24	31	25	21	26	21	18	21	17	15	12		
9	48	36	28	23	44	33	26	21	28	23	19	24	19	16	19	16	13	11		
10	45	33	25	20	41	30	24	19	26	20	17	22	17	14	18	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14470	14470	14470
5°	14536	13853	13775
10°	14438	13373	13178
15°	14234	12876	12565
20°	13977	12355	11985
25°	13723	11856	11458
30°	13368	11348	10936
35°	13007	10860	10552
40°	12629	10437	10173
45°	12268	10054	9841
50°	11880	9701	9513
55°	11474	9326	9180
60°	10976	8935	8830
65°	10455	8485	8425
70°	9870	8002	7993
75°	9118	7519	7581
80°	7936	7018	7158
85°	6738	6544	6791

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12268 cd/sqm

TEST NUMBER: P1008271

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.7	1.4
10°-20°	248.5	3.9
20°-30°	376.6	5.9
30°-40°	458.6	7.2
40°-50°	493.4	7.8
50°-60°	479.2	7.6
60°-70°	418.5	6.6
70°-80°	322.1	5.1
80°-90°	217.4	3.4
90°-100°	180.8	2.9
100°-110°	227.9	3.6
110°-120°	387.8	6.1
120°-130°	564.2	8.9
130°-140°	573.6	9.1
140°-150°	520.4	8.2
150°-160°	416.1	6.6
160°-170°	268.1	4.2
170°-180°	92.3	1.5
0°-30°	711.8	11.2
0°-40°	1170.4	18.5
0°-60°	2142.9	33.8
0°-90°	3100.8	49.0
90°-120°	796.5	12.6
90°-150°	2454.6	38.8
90°-180°	3231.0	51.0
0°-180°	6331.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	914	914	914	914	914	
5°	917	913	905	913	912	87
15°	874	877	877	889	888	246
25°	795	804	816	832	836	366
35°	685	708	733	762	771	428
45°	562	598	644	685	698	434
55°	431	478	547	595	612	385
65°	294	359	437	492	509	292
75°	163	237	322	379	396	172
85°	48	130	215	270	289	50
90°	14	98	189	245	263	12
95°	56	95	180	234	249	62
105°	220	279	157	211	228	235
115°	409	435	512	227	191	402
125°	573	582	638	678	692	511
135°	707	718	738	773	782	547
145°	819	818	830	843	846	512
155°	902	895	904	908	902	415
165°	950	946	948	953	948	268
175°	972	967	968	973	966	92
180°	970	970	970	970	970	

TEST NUMBER: P1008271

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	914.1	914.1	914.1	914.1	914.1
2.5°	920.8	916.8	907.5	914.1	911.5
5°	916.8	912.8	904.9	912.8	911.5
7.5°	910.2	907.5	900.9	910.2	908.8
10°	902.2	899.6	895.6	906.2	904.9
12.5°	889.0	890.3	887.6	898.2	896.9
15°	874.4	877.0	877.0	889.0	887.6
17.5°	855.8	861.1	865.1	877.0	877.0
20°	837.3	843.9	849.2	863.8	863.8
22.5°	817.4	825.4	833.3	847.9	850.5
25°	794.9	804.2	816.1	832.0	836.0
27.5°	768.4	783.0	796.2	816.1	818.7
30°	741.9	759.1	776.3	797.5	801.5
32.5°	712.8	732.6	753.8	779.0	786.9
35°	684.9	707.5	732.6	761.8	771.0
37.5°	654.5	679.6	711.4	743.2	752.5
40°	624.0	653.1	688.9	723.4	735.3
42.5°	594.8	624.0	666.4	704.8	716.7
45°	561.7	597.5	643.9	684.9	698.2
47.5°	529.9	568.4	621.3	663.7	678.3
50°	496.8	537.9	597.5	642.5	657.1
52.5°	465.0	508.7	572.3	618.7	634.6
55°	430.6	478.3	547.2	594.8	612.1
57.5°	397.4	450.4	519.3	571.0	588.2
60°	361.7	418.6	494.2	544.5	563.1
62.5°	329.9	389.5	465.0	519.3	536.6
65°	294.1	359.0	437.2	491.5	508.7
67.5°	262.3	329.9	409.4	463.7	482.2
70°	227.9	296.8	378.9	435.9	451.8
72.5°	196.1	267.6	351.1	406.7	426.6
75°	163.0	237.1	321.9	378.9	396.1
77.5°	131.2	208.0	294.1	351.1	369.6
80°	99.4	180.2	266.3	321.9	340.5
82.5°	72.9	152.4	239.8	295.4	312.7
85°	47.7	129.8	214.6	270.3	288.8
87.5°	29.1	108.6	193.4	247.7	265.0
90°	13.9	98.5	188.9	245.4	262.7
92.5°	29.4	96.8	179.8	232.8	249.4
95°	56.2	95.3	179.8	233.6	248.8
97.5°	91.4	90.8	178.9	230.0	246.6
100°	133.5	86.4	172.5	227.1	243.1
102.5°	178.4	220.8	164.6	220.0	236.7
105°	219.9	279.3	156.7	210.8	228.2
107.5°	269.7	319.0	148.9	201.6	219.0
110°	316.1	357.3	219.5	191.7	209.1

TEST NUMBER: P1008271

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	361.0	394.8	443.8	183.8	200.5
115°	408.7	435.2	512.3	227.2	191.3
117.5°	448.8	473.4	540.9	480.4	309.8
120°	495.1	510.9	576.5	622.0	541.8
122.5°	534.4	546.9	609.9	649.9	662.5
125°	572.9	582.1	637.8	678.5	692.5
127.5°	609.4	617.9	664.3	704.4	717.0
130°	643.8	653.7	689.2	728.8	738.7
132.5°	678.9	686.7	714.3	751.1	761.0
135°	707.0	718.3	737.9	772.7	781.9
137.5°	737.9	746.3	759.9	792.2	799.4
140°	768.1	772.4	782.7	810.2	814.7
142.5°	793.3	796.9	806.1	827.6	830.7
145°	818.7	818.0	829.9	842.7	845.9
147.5°	841.8	839.7	851.7	856.5	857.7
150°	864.3	859.4	870.6	874.8	871.3
152.5°	883.2	877.6	888.1	892.4	887.4
155°	901.5	895.2	903.6	907.8	902.2
157.5°	916.2	910.6	916.9	921.8	916.2
160°	928.8	924.6	928.8	933.0	928.1
162.5°	940.1	935.8	939.4	944.3	938.0
165°	949.9	945.7	947.8	952.7	947.8
167.5°	957.6	953.4	955.5	960.4	954.1
170°	963.9	959.7	961.1	966.0	959.7
172.5°	968.1	963.9	965.3	970.2	963.9
175°	971.6	966.7	968.1	973.0	966.0
177.5°	973.0	968.1	968.8	973.7	967.4
180°	969.5	969.5	969.5	969.5	969.5

(END OF REPORT)