

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001842

Luminaire Tested: SA4XXDIP-B795D365UB30-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001842
REPORT IS A COMBINATION OF REPORTS P996467 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB30-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4532.0 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001842

CATALOG NUMBER: SA4XXDIP-B795D365UB30-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001842

CATALOG NUMBER: SA4XXDIP-B795D365UB30-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71
1	100	95	91	87	94	90	86	82	79	76	73	70	67	65	61	59	58
2	91	82	75	70	85	78	71	66	69	64	60	60	57	53	53	50	47
3	82	72	64	57	77	68	61	55	60	54	50	53	48	45	46	43	40
4	75	63	55	48	70	60	52	46	53	47	42	47	42	38	41	37	34
5	69	56	48	41	64	53	45	39	47	41	36	42	37	33	37	33	29
6	63	51	42	36	59	48	40	34	43	36	31	38	32	28	33	29	26
7	59	46	37	31	55	43	35	30	39	32	27	34	29	25	30	26	23
8	54	41	33	28	51	39	32	26	35	29	24	31	26	22	28	23	20
9	51	38	30	25	48	36	29	24	32	26	22	29	24	20	26	21	18
10	47	35	27	22	45	33	26	21	30	24	20	27	22	18	24	20	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7788	7788	7788
5°	7809	7585	7599
10°	7758	7435	7414
15°	7686	7268	7206
20°	7578	7086	7005
25°	7457	6886	6787
30°	7325	6687	6565
35°	7177	6485	6367
40°	7059	6289	6162
45°	6882	6107	5982
50°	6732	5899	5791
55°	6577	5698	5572
60°	6336	5450	5365
65°	6071	5181	5115
70°	5749	4874	4828
75°	5300	4533	4554
80°	4796	4186	4267
85°	4126	3836	4035

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6882 cd/sqm

TEST NUMBER: P1001842

CATALOG NUMBER: SA4XXDIP-B795D365UB30-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.5	2.0
10°-20°	259.3	5.7
20°-30°	392.0	8.6
30°-40°	474.3	10.5
40°-50°	501.4	11.1
50°-60°	471.9	10.4
60°-70°	391.5	8.6
70°-80°	274.8	6.1
80°-90°	155.9	3.4
90°-100°	122.2	2.7
100°-110°	158.0	3.5
110°-120°	198.2	4.4
120°-130°	226.8	5.0
130°-140°	236.9	5.2
140°-150°	224.1	4.9
150°-160°	186.6	4.1
160°-170°	124.2	2.7
170°-180°	43.5	1.0
0°-30°	741.8	16.4
0°-40°	1216.0	26.8
0°-60°	2189.2	48.3
0°-90°	3011.4	66.4
90°-120°	478.5	10.6
90°-150°	1166.3	25.7
90°-180°	1521.0	33.6
0°-180°	4532.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	955	955	955	955	955	
5°	956	953	945	954	953	91
15°	916	918	914	924	923	258
25°	838	845	848	860	861	386
35°	734	746	757	772	775	459
45°	612	632	652	670	676	473
55°	479	502	534	555	562	427
65°	332	366	402	429	437	329
75°	184	224	268	298	308	195
85°	57	102	150	182	192	59
90°	18	65	114	147	156	13
95°	35	74	120	150	160	34
105°	92	114	155	183	193	99
115°	161	171	204	228	235	160
125°	230	229	255	275	281	205
135°	293	295	303	319	325	227
145°	355	355	355	361	365	222
155°	405	405	405	406	405	187
165°	441	440	439	441	440	124
175°	459	457	457	459	457	44
180°	460	460	460	460	460	

TEST NUMBER: P1001842

CATALOG NUMBER: SA4XXDIP-B795D365UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	955.0	955.0	955.0	955.0	955.0
2.5°	959.3	956.1	947.5	955.0	953.9
5°	956.1	952.9	945.4	953.9	952.9
7.5°	949.7	947.5	941.1	950.7	949.7
10°	941.1	940.0	934.7	944.3	943.2
12.5°	929.3	929.3	926.1	934.7	934.7
15°	916.5	917.6	914.4	924.0	922.9
17.5°	899.4	902.6	901.5	911.2	910.1
20°	881.2	884.4	885.5	896.2	896.2
22.5°	860.9	865.2	867.3	878.0	880.1
25°	838.4	844.9	848.1	859.8	860.9
27.5°	813.8	823.5	827.7	838.4	839.5
30°	789.2	797.8	805.3	817.0	819.2
32.5°	762.5	773.2	781.8	795.7	797.8
35°	733.6	746.5	757.2	772.1	775.3
37.5°	704.8	719.7	732.6	747.5	750.7
40°	677.0	690.9	705.8	721.9	726.1
42.5°	644.9	660.9	679.1	697.3	700.5
45°	611.7	632.0	652.4	670.5	675.9
47.5°	580.7	601.0	624.5	642.7	649.1
50°	546.5	570.0	593.5	614.9	621.3
52.5°	512.3	535.8	563.6	585.0	591.4
55°	479.1	501.6	533.6	555.0	561.5
57.5°	441.7	469.5	500.5	526.2	531.5
60°	405.3	433.1	468.4	493.0	501.6
62.5°	370.0	401.0	436.3	460.9	469.5
65°	331.5	365.7	402.1	428.8	437.4
67.5°	295.2	331.5	370.0	396.8	405.3
70°	257.7	294.1	334.7	363.6	371.1
72.5°	221.4	258.8	302.6	330.5	339.0
75°	183.9	223.5	268.4	298.4	308.0
77.5°	148.7	190.4	237.4	267.4	278.1
80°	116.6	159.3	206.4	238.5	247.0
82.5°	84.5	129.4	176.5	209.6	219.2
85°	56.7	101.6	149.7	181.8	192.5
87.5°	35.3	79.1	126.2	157.2	166.8
90°	18.2	64.9	113.7	146.9	156.1
92.5°	25.2	67.4	115.1	146.1	155.1
95°	35.2	73.7	120.0	150.0	159.6
97.5°	46.9	80.8	127.5	156.7	166.3
100°	61.6	90.8	135.7	165.3	172.7
102.5°	77.9	101.8	145.2	174.1	183.0
105°	92.4	114.2	155.2	183.0	192.6
107.5°	109.8	128.4	166.1	194.4	201.5
110°	126.6	142.2	179.3	203.2	212.8

TEST NUMBER: P1001842

CATALOG NUMBER: SA4XXDIP-B795D365UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	144.0	156.8	191.4	214.9	223.5
115°	161.4	171.0	204.5	227.7	234.8
117.5°	178.8	185.2	216.9	238.3	245.8
120°	195.1	199.8	229.7	249.4	258.6
122.5°	213.2	213.6	242.1	262.4	268.2
125°	230.0	228.9	255.2	274.9	280.6
127.5°	246.0	245.9	266.6	285.1	292.3
130°	261.9	261.9	279.0	297.6	302.6
132.5°	279.3	279.0	291.5	309.0	315.0
135°	293.2	295.3	302.8	319.2	324.6
137.5°	309.9	309.9	314.8	329.9	335.5
140°	326.6	326.3	327.3	340.8	345.9
142.5°	340.9	341.6	340.1	351.9	356.1
145°	354.7	355.0	355.4	361.4	364.7
147.5°	368.9	369.6	369.3	370.0	373.8
150°	381.7	382.1	382.1	382.1	381.7
152.5°	392.7	393.4	393.8	394.8	393.8
155°	405.2	405.2	404.8	406.2	404.8
157.5°	415.8	415.1	415.1	416.2	415.1
160°	425.1	424.7	424.3	425.4	423.6
162.5°	433.6	432.5	432.2	434.3	432.5
165°	441.0	440.0	439.3	441.4	440.0
167.5°	447.1	445.7	445.7	447.8	445.7
170°	452.1	450.3	450.6	452.8	450.3
172.5°	455.6	454.2	454.2	456.7	454.2
175°	458.8	457.0	456.7	459.2	456.7
177.5°	460.2	458.5	458.5	460.9	458.1
180°	459.5	459.5	459.5	459.5	459.5

(END OF REPORT)