

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008273

Luminaire Tested: S122DIP-B865D725UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008273
REPORT IS A COMBINATION OF REPORTS P984916 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D725UB2750-4F0-XX-W2A-D_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6062.0 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008273

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008273

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	96	91	87	83	88	84	80	77	70	68	65	58	56	54	46	45	44
2	87	79	72	66	80	73	67	62	61	56	53	50	47	44	40	38	36
3	79	69	61	55	72	63	56	51	53	48	44	44	40	36	35	32	30
4	72	60	52	46	66	56	48	43	47	41	37	39	34	31	31	28	25
5	66	54	45	39	60	50	42	36	42	36	31	35	30	26	28	24	22
6	61	48	40	33	55	44	37	31	37	32	27	31	26	23	25	22	19
7	56	43	35	29	51	40	33	27	34	28	24	28	24	20	23	19	17
8	52	39	31	26	47	36	29	24	31	25	21	26	21	18	21	17	15
9	48	36	28	23	44	33	26	21	28	23	19	24	19	16	19	16	13
10	45	33	25	20	41	30	24	19	26	20	17	22	17	14	18	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13852	13852	13852
5°	13914	13261	13185
10°	13822	12801	12614
15°	13625	12327	12029
20°	13380	11827	11473
25°	13136	11349	10969
30°	12796	10864	10469
35°	12453	10396	10102
40°	12089	9992	9738
45°	11743	9625	9421
50°	11373	9287	9106
55°	10984	8927	8787
60°	10505	8554	8452
65°	10007	8122	8066
70°	9445	7660	7651
75°	8727	7199	7258
80°	7593	6717	6851
85°	6455	6266	6502

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11743 cd/sqm

TEST NUMBER: P1008273

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.0	1.4
10°-20°	237.9	3.9
20°-30°	360.5	5.9
30°-40°	439.0	7.2
40°-50°	472.3	7.8
50°-60°	458.7	7.6
60°-70°	400.6	6.6
70°-80°	308.3	5.1
80°-90°	208.1	3.4
90°-100°	173.1	2.9
100°-110°	218.1	3.6
110°-120°	371.3	6.1
120°-130°	540.2	8.9
130°-140°	549.2	9.1
140°-150°	498.2	8.2
150°-160°	398.4	6.6
160°-170°	256.7	4.2
170°-180°	88.4	1.5
0°-30°	681.4	11.2
0°-40°	1120.4	18.5
0°-60°	2051.4	33.8
0°-90°	2968.4	49.0
90°-120°	762.5	12.6
90°-150°	2350.2	38.8
90°-180°	3094.0	51.0
0°-180°	6062.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	875	875	875	875	875	
5°	878	874	866	874	872	83
15°	837	840	840	851	850	236
25°	761	770	781	796	800	350
35°	656	677	701	729	738	410
45°	538	572	616	656	668	415
55°	412	458	524	569	586	369
65°	282	344	418	470	487	280
75°	156	227	308	363	379	165
85°	46	124	206	259	276	48
90°	13	94	181	235	252	11
95°	54	91	172	224	238	60
105°	210	267	150	202	218	225
115°	391	417	490	218	183	385
125°	549	557	611	650	663	490
135°	677	688	706	740	749	523
145°	784	783	795	807	810	491
155°	863	857	865	869	864	398
165°	910	905	907	912	907	257
175°	930	926	927	932	925	89
180°	928	928	928	928	928	

TEST NUMBER: P1008273

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	875.1	875.1	875.1	875.1	875.1
2.5°	881.4	877.6	868.7	875.1	872.5
5°	877.6	873.8	866.2	873.8	872.5
7.5°	871.3	868.7	862.4	871.3	870.0
10°	863.7	861.1	857.3	867.5	866.2
12.5°	851.0	852.3	849.7	859.9	858.6
15°	837.0	839.6	839.6	851.0	849.7
17.5°	819.3	824.4	828.2	839.6	839.6
20°	801.5	807.9	812.9	826.9	826.9
22.5°	782.5	790.1	797.7	811.7	814.2
25°	760.9	769.8	781.2	796.5	800.3
27.5°	735.6	749.5	762.2	781.2	783.8
30°	710.2	726.7	743.2	763.5	767.3
32.5°	682.3	701.3	721.6	745.7	753.3
35°	655.7	677.2	701.3	729.2	738.1
37.5°	626.5	650.6	681.0	711.5	720.4
40°	597.3	625.2	659.5	692.5	703.9
42.5°	569.4	597.3	637.9	674.7	686.1
45°	537.7	572.0	616.4	655.7	668.4
47.5°	507.3	544.1	594.8	635.4	649.3
50°	475.6	514.9	572.0	615.1	629.0
52.5°	445.1	487.0	547.9	592.3	607.5
55°	412.2	457.8	523.8	569.4	585.9
57.5°	380.5	431.2	497.1	546.6	563.1
60°	346.2	400.8	473.1	521.2	539.0
62.5°	315.8	372.9	445.1	497.1	513.6
65°	281.5	343.7	418.5	470.5	487.0
67.5°	251.1	315.8	391.9	443.9	461.6
70°	218.1	284.1	362.7	417.2	432.5
72.5°	187.7	256.2	336.1	389.3	408.4
75°	156.0	227.0	308.2	362.7	379.2
77.5°	125.6	199.1	281.5	336.1	353.8
80°	95.1	172.5	254.9	308.2	325.9
82.5°	69.8	145.8	229.6	282.8	299.3
85°	45.7	124.3	205.5	258.7	276.5
87.5°	27.9	104.0	185.2	237.2	253.6
90°	13.4	94.3	180.8	234.9	251.5
92.5°	28.2	92.7	172.1	223.0	238.8
95°	53.8	91.3	172.0	223.6	238.2
97.5°	87.5	86.9	171.3	220.2	236.0
100°	127.8	82.7	165.1	217.4	232.7
102.5°	170.8	211.4	157.5	210.6	226.6
105°	210.5	267.4	150.1	201.9	218.4
107.5°	258.2	305.5	142.5	193.0	209.7
110°	302.7	342.1	210.1	183.6	200.2

TEST NUMBER: P1008273

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	345.6	378.0	424.9	176.0	191.9
115°	391.3	416.6	490.5	217.5	183.2
117.5°	429.6	453.3	517.9	460.0	296.6
120°	474.0	489.2	551.9	595.5	518.8
122.5°	511.6	523.6	584.0	622.2	634.4
125°	548.6	557.3	610.7	649.7	663.1
127.5°	583.5	591.7	636.0	674.4	686.5
130°	616.4	626.0	660.0	697.7	707.3
132.5°	650.0	657.5	683.9	719.2	728.6
135°	677.0	687.8	706.5	739.8	748.6
137.5°	706.6	714.6	727.6	758.5	765.4
140°	735.5	739.5	749.4	775.8	780.0
142.5°	759.6	763.0	771.8	792.3	795.4
145°	783.9	783.2	794.6	806.9	809.9
147.5°	806.0	804.0	815.4	820.1	821.2
150°	827.5	822.8	833.6	837.6	834.2
152.5°	845.7	840.3	850.4	854.4	849.7
155°	863.1	857.1	865.1	869.2	863.8
157.5°	877.2	871.8	877.9	882.6	877.2
160°	889.3	885.3	889.3	893.3	888.6
162.5°	900.1	896.0	899.4	904.1	898.0
165°	909.5	905.4	907.4	912.2	907.4
167.5°	916.9	912.8	914.8	919.5	913.5
170°	922.9	918.9	920.2	924.9	918.9
172.5°	926.9	922.9	924.2	928.9	922.9
175°	930.3	925.6	926.9	931.6	924.9
177.5°	931.6	926.9	927.6	932.3	926.3
180°	928.3	928.3	928.3	928.3	928.3

(END OF REPORT)