

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008275

Luminaire Tested: S122DIP-B865D725UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008275
REPORT IS A COMBINATION OF REPORTS P984918 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D725UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6322.0 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008275

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008275

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	51
2	90	83	76	71	83	77	72	67	66	62	59	56	53	51	47	45	43
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	47	52	46	42	45	40	37	38	34	32
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	30	28
6	64	51	43	37	59	48	41	36	42	36	32	36	32	28	31	27	24
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21715	21715	21715
5°	21750	20698	20551
10°	21572	19755	19363
15°	21257	18804	18112
20°	20830	17770	16928
25°	20403	16691	15747
30°	19868	15677	14505
35°	19364	14605	13287
40°	18739	13549	12135
45°	18121	12501	11007
50°	17443	11436	9834
55°	16728	10296	8724
60°	15931	9062	7571
65°	15052	7808	6357
70°	13936	6435	5134
75°	12396	4961	3964
80°	10531	3370	2550
85°	7642	1567	1086

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18121 cd/sqm

TEST NUMBER: P1008275

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	2.0
10°-20°	363.3	5.7
20°-30°	533.8	8.4
30°-40°	620.0	9.8
40°-50°	619.2	9.8
50°-60°	540.0	8.5
60°-70°	399.1	6.3
70°-80°	225.8	3.6
80°-90°	61.3	1.0
90°-100°	31.8	0.5
100°-110°	118.7	1.9
110°-120°	314.7	5.0
120°-130°	522.0	8.3
130°-140°	554.5	8.8
140°-150°	515.4	8.2
150°-160°	414.3	6.6
160°-170°	267.0	4.2
170°-180°	91.9	1.5
0°-30°	1026.2	16.2
0°-40°	1646.2	26.0
0°-60°	2805.4	44.4
0°-90°	3491.7	55.2
90°-120°	465.3	7.4
90°-150°	2057.1	32.5
90°-180°	2830.0	44.8
0°-180°	6322.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1279	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	985	977	971	637
45°	830	820	801	786	781	640
55°	628	620	604	588	582	561
65°	423	416	402	390	384	419
75°	222	219	212	204	207	236
85°	54	53	51	48	46	60
90°	1	8	14	18	19	6
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	395
125°	568	577	590	595	597	507
135°	703	714	720	727	726	543
145°	815	814	826	831	828	510
155°	898	891	900	904	898	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	965	965	965	965	965	

TEST NUMBER: P1008275

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1371.8	1371.8	1371.8	1371.8	1371.8
2.5°	1379.7	1373.1	1358.6	1371.8	1369.1
5°	1371.8	1366.5	1352.0	1362.5	1359.9
7.5°	1362.5	1354.6	1340.1	1350.7	1348.0
10°	1348.0	1338.8	1323.0	1333.5	1329.6
12.5°	1328.2	1320.3	1304.5	1311.1	1308.5
15°	1305.8	1297.9	1280.8	1286.0	1279.4
17.5°	1278.1	1270.2	1253.1	1259.7	1253.1
20°	1247.8	1239.9	1221.4	1225.4	1220.1
22.5°	1217.4	1205.6	1188.4	1188.4	1185.8
25°	1181.8	1171.3	1148.9	1151.5	1148.9
27.5°	1142.3	1133.0	1115.9	1111.9	1105.3
30°	1102.7	1092.1	1072.4	1068.4	1063.1
32.5°	1060.5	1052.6	1031.5	1023.6	1018.3
35°	1019.6	1006.4	985.3	977.4	970.8
37.5°	973.4	961.6	940.5	931.2	924.6
40°	925.9	915.4	894.3	882.4	877.1
42.5°	879.8	869.2	848.1	834.9	827.0
45°	829.7	820.4	800.6	786.1	780.9
47.5°	780.9	771.6	750.5	736.0	728.1
50°	729.4	722.8	704.4	685.9	679.3
52.5°	679.3	670.1	652.9	638.4	629.2
55°	627.8	619.9	604.1	588.3	581.7
57.5°	576.4	569.8	552.7	536.8	531.6
60°	525.0	519.7	501.2	486.7	482.8
62.5°	474.8	465.6	452.4	439.2	434.0
65°	423.4	415.5	402.3	390.4	383.8
67.5°	370.6	364.0	352.2	342.9	337.7
70°	321.8	316.6	304.7	295.5	290.2
72.5°	271.7	266.4	259.8	250.6	246.7
75°	221.6	219.0	212.4	204.4	207.1
77.5°	176.7	171.5	168.8	164.9	160.9
80°	131.9	130.6	127.9	124.0	121.3
82.5°	89.7	89.7	88.4	83.1	83.1
85°	54.1	52.8	51.4	47.5	46.2
87.5°	23.7	21.1	18.5	14.5	13.2
90°	0.7	8.4	14.0	17.5	18.9
92.5°	17.5	14.7	16.8	18.2	18.9
95°	45.4	22.4	27.2	30.7	30.0
97.5°	81.7	24.5	35.6	37.7	38.4
100°	123.6	27.9	39.8	45.4	46.8
102.5°	169.8	168.4	41.2	48.9	51.0
105°	212.4	233.3	42.6	50.3	53.1
107.5°	262.0	279.4	44.0	51.7	54.5
110°	309.5	324.1	122.3	52.4	55.2

TEST NUMBER: P1008275

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.2	366.8	354.9	53.8	55.9
115°	401.7	413.6	431.0	107.6	57.3
117.5°	442.9	456.9	468.7	368.8	185.8
120°	489.0	499.5	512.1	520.4	426.1
122.5°	528.1	539.3	553.3	557.5	558.2
125°	567.9	577.0	590.3	595.2	597.3
127.5°	604.3	614.0	624.5	631.5	632.2
130°	638.5	649.7	657.4	665.0	664.3
132.5°	673.4	682.5	690.2	696.5	695.8
135°	702.8	713.9	720.2	727.2	725.8
137.5°	733.5	741.9	748.9	755.9	753.8
140°	763.5	769.1	776.8	783.1	779.6
142.5°	788.7	793.6	802.7	808.3	804.8
145°	815.2	814.5	826.4	831.3	827.8
147.5°	838.3	836.2	848.1	851.6	848.8
150°	860.6	855.8	866.9	871.1	867.6
152.5°	879.5	873.9	884.4	888.6	883.7
155°	897.7	891.4	899.8	904.0	898.4
157.5°	912.3	906.7	913.0	917.9	912.3
160°	924.9	920.7	924.9	929.1	924.2
162.5°	936.1	931.9	935.4	940.3	934.0
165°	945.9	941.7	943.8	948.7	943.8
167.5°	953.6	949.4	951.5	956.3	950.1
170°	959.8	955.6	957.0	961.9	955.6
172.5°	964.0	959.8	961.2	966.1	959.8
175°	967.5	962.6	964.0	968.9	961.9
177.5°	968.9	964.0	964.7	969.6	963.3
180°	965.4	965.4	965.4	965.4	965.4

(END OF REPORT)