

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001852

Luminaire Tested: SA4XXDIP-B795D365UB35-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001852
REPORT IS A COMBINATION OF REPORTS P996477 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB35-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4597.6 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001852

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001852

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	100	95	90	86	94	89	85	82	79	76	73	69	67	65	60	59	57
2	91	82	75	70	85	77	71	66	68	64	59	60	56	53	52	49	47
3	82	72	64	57	77	68	60	55	60	54	49	53	48	44	46	42	39
4	75	63	55	48	70	60	52	46	53	47	42	47	42	38	41	37	34
5	69	56	48	41	64	53	45	39	47	41	36	42	36	32	37	32	29
6	63	50	42	36	59	48	40	34	42	36	31	38	32	28	33	29	25
7	59	46	37	31	55	43	35	30	38	32	27	34	29	25	30	26	22
8	54	41	33	27	51	39	32	26	35	29	24	31	26	22	28	23	20
9	51	38	30	25	48	36	29	24	32	26	22	29	24	20	25	21	18
10	47	35	27	22	44	33	26	21	30	24	20	27	22	18	24	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7821	7821	7821
5°	7843	7617	7631
10°	7791	7467	7446
15°	7718	7299	7237
20°	7611	7116	7034
25°	7489	6915	6816
30°	7357	6715	6593
35°	7208	6512	6395
40°	7089	6317	6190
45°	6911	6133	6008
50°	6761	5924	5816
55°	6605	5723	5595
60°	6364	5473	5387
65°	6097	5203	5138
70°	5774	4896	4849
75°	5323	4553	4573
80°	4816	4204	4286
85°	4141	3854	4052

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6911 cd/sqm

TEST NUMBER: P1001852

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	2.0
10°-20°	260.4	5.7
20°-30°	393.7	8.6
30°-40°	476.3	10.4
40°-50°	503.5	11.0
50°-60°	473.9	10.3
60°-70°	393.2	8.6
70°-80°	276.0	6.0
80°-90°	156.3	3.4
90°-100°	227.7	5.0
100°-110°	343.3	7.5
110°-120°	290.9	6.3
120°-130°	231.6	5.0
130°-140°	182.8	4.0
140°-150°	133.3	2.9
150°-160°	92.1	2.0
160°-170°	54.2	1.2
170°-180°	17.6	0.4
0°-30°	744.9	16.2
0°-40°	1221.2	26.6
0°-60°	2198.6	47.8
0°-90°	3024.1	65.8
90°-120°	861.8	18.7
90°-150°	1409.5	30.7
90°-180°	1573.0	34.2
0°-180°	4597.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	959	959	959	959	959	
5°	960	957	949	958	957	91
15°	920	922	918	928	927	259
25°	842	848	852	864	865	388
35°	737	750	760	776	779	461
45°	614	635	655	673	679	475
55°	481	504	536	557	564	429
65°	333	367	404	431	439	330
75°	185	224	270	300	309	196
85°	57	102	150	183	193	59
90°	18	63	113	145	154	13
95°	26	87	384	267	219	24
105°	52	92	305	602	609	55
115°	80	108	260	476	564	80
125°	107	125	238	392	442	95
135°	124	147	216	330	378	96
145°	142	161	205	262	292	89
155°	160	172	199	226	235	74
165°	174	179	191	202	205	49
175°	182	182	183	186	185	17
180°	182	182	182	182	182	

TEST NUMBER: P1001852

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	959.1	959.1	959.1	959.1	959.1
2.5°	963.4	960.2	951.6	959.1	958.0
5°	960.2	957.0	949.4	958.0	957.0
7.5°	953.7	951.6	945.1	954.8	953.7
10°	945.1	944.1	938.7	948.4	947.3
12.5°	933.3	933.3	930.1	938.7	938.7
15°	920.4	921.5	918.3	928.0	926.9
17.5°	903.3	906.5	905.4	915.1	914.0
20°	885.0	888.2	889.3	900.0	900.0
22.5°	864.6	868.9	871.0	881.8	883.9
25°	842.0	848.5	851.7	863.5	864.6
27.5°	817.3	827.0	831.3	842.0	843.1
30°	792.6	801.2	808.7	820.6	822.7
32.5°	765.8	776.5	785.1	799.1	801.2
35°	736.8	749.7	760.4	775.5	778.7
37.5°	707.8	722.8	735.7	750.7	754.0
40°	679.9	693.8	708.9	725.0	729.3
42.5°	647.6	663.8	682.0	700.3	703.5
45°	614.3	634.8	655.2	673.4	678.8
47.5°	583.2	603.6	627.2	645.5	651.9
50°	548.8	572.5	596.1	617.6	624.0
52.5°	514.5	538.1	566.0	587.5	593.9
55°	481.2	503.7	535.9	557.4	563.9
57.5°	443.6	471.5	502.6	528.4	533.8
60°	407.1	435.0	470.4	495.1	503.7
62.5°	371.6	402.8	438.2	462.9	471.5
65°	332.9	367.3	403.8	430.7	439.3
67.5°	296.4	332.9	371.6	398.5	407.1
70°	258.8	295.4	336.2	365.2	372.7
72.5°	222.3	259.9	304.0	331.9	340.5
75°	184.7	224.5	269.6	299.7	309.3
77.5°	149.3	191.2	238.4	268.5	279.2
80°	117.1	160.0	207.3	239.5	248.1
82.5°	84.8	130.0	177.2	210.5	220.2
85°	56.9	102.0	150.4	182.6	193.3
87.5°	35.4	79.5	126.7	157.9	167.5
90°	17.6	63.0	112.7	144.6	153.6
92.5°	21.1	81.2	239.9	176.2	171.1
95°	25.8	86.6	384.5	266.6	219.3
97.5°	32.5	85.1	399.6	410.4	335.0
100°	38.9	86.2	368.8	517.8	445.7
102.5°	46.1	88.2	333.1	582.2	543.3
105°	51.5	91.6	305.2	602.3	608.9
107.5°	59.7	96.3	285.2	588.9	636.8
110°	66.8	99.8	274.1	553.8	632.1



TEST NUMBER: P1001852

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	73.6	104.5	265.5	512.4	604.6
115°	80.0	108.4	259.5	475.6	564.2
117.5°	87.8	112.9	253.7	444.6	525.7
120°	94.7	116.1	248.3	421.4	492.0
122.5°	101.8	120.2	242.7	405.2	464.2
125°	106.8	125.0	238.0	392.2	442.0
127.5°	112.5	131.4	231.9	378.4	426.7
130°	116.1	136.6	226.1	364.3	411.6
132.5°	120.7	142.0	221.5	348.6	396.6
135°	123.9	147.2	215.8	330.2	377.7
137.5°	128.2	150.6	211.5	311.9	356.6
140°	132.8	154.7	207.9	294.0	335.1
142.5°	136.8	158.4	205.8	278.2	312.6
145°	141.5	160.8	205.0	262.2	291.8
147.5°	146.8	164.0	204.0	248.1	272.2
150°	151.8	167.0	202.9	239.0	255.1
152.5°	155.4	169.9	201.1	232.2	244.3
155°	159.7	172.4	199.3	225.8	235.4
157.5°	164.0	174.6	197.5	219.7	227.2
160°	167.9	176.6	195.4	213.6	219.7
162.5°	171.5	178.2	193.3	207.8	212.5
165°	174.0	179.4	191.1	202.4	205.4
167.5°	176.8	180.2	189.0	197.8	199.7
170°	178.6	181.0	186.8	193.0	194.3
172.5°	180.4	181.4	184.7	189.0	189.0
175°	181.5	181.8	183.3	185.8	185.0
177.5°	182.2	181.8	182.2	183.4	182.2
180°	181.8	181.8	181.8	181.8	181.8

(END OF REPORT)