

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001854

Luminaire Tested: SA4XXDIP-B795D365UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001854
REPORT IS A COMBINATION OF REPORTS P996479 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB35-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4722.0 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001854

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001854

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	67	65
2	94	86	80	74	89	82	76	71	74	69	65	67	63	60	60	57	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35
6	66	54	45	39	63	51	44	38	47	41	36	43	37	33	39	34	31
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10929	10929	10929
5°	10938	10615	10627
10°	10845	10320	10247
15°	10690	9969	9820
20°	10491	9591	9376
25°	10268	9190	8898
30°	9998	8757	8374
35°	9719	8314	7867
40°	9427	7837	7328
45°	9122	7359	6824
50°	8785	6895	6266
55°	8417	6353	5711
60°	8041	5760	5134
65°	7611	5148	4484
70°	7117	4409	3786
75°	6374	3555	3032
80°	5433	2570	2133
85°	4221	1430	1149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9122 cd/sqm

TEST NUMBER: P1001854

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.7
10°-20°	355.9	7.5
20°-30°	523.8	11.1
30°-40°	608.9	12.9
40°-50°	608.8	12.9
50°-60°	532.5	11.3
60°-70°	395.3	8.4
70°-80°	224.3	4.8
80°-90°	65.2	1.4
90°-100°	30.1	0.6
100°-110°	90.1	1.9
110°-120°	153.1	3.2
120°-130°	201.9	4.3
130°-140°	226.8	4.8
140°-150°	222.9	4.7
150°-160°	187.5	4.0
160°-170°	124.8	2.6
170°-180°	43.7	0.9
0°-30°	1006.0	21.3
0°-40°	1614.9	34.2
0°-60°	2756.1	58.4
0°-90°	3441.0	72.9
90°-120°	273.3	5.8
90°-150°	925.1	19.6
90°-180°	1281.0	27.1
0°-180°	4722.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1339	1335	1323	1335	1333	127
15°	1275	1270	1254	1261	1258	359
25°	1154	1147	1132	1133	1129	531
35°	993	986	971	963	958	621
45°	811	803	786	774	771	625
55°	613	610	595	582	576	549
65°	416	410	400	389	383	411
75°	221	216	210	206	205	235
85°	58	58	56	56	55	62
90°	1	5	8	10	11	5
95°	21	25	27	28	28	23
105°	83	84	85	86	87	88
115°	156	156	155	155	154	154
125°	227	227	226	226	225	202
135°	292	295	295	294	293	226
145°	355	357	357	357	356	222
155°	407	407	407	408	407	187
165°	443	442	441	444	442	125
175°	461	459	459	461	459	44
180°	462	462	462	462	462	

TEST NUMBER: P1001854

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.2	1340.2	1340.2	1340.2	1340.2
2.5°	1344.5	1341.3	1329.5	1340.2	1339.2
5°	1339.2	1334.9	1323.1	1334.9	1332.7
7.5°	1329.5	1325.2	1312.3	1322.0	1320.9
10°	1315.5	1311.2	1297.3	1305.9	1303.7
12.5°	1297.3	1293.0	1278.0	1287.6	1284.4
15°	1274.7	1270.4	1254.3	1260.8	1257.6
17.5°	1249.0	1243.6	1228.6	1232.9	1230.7
20°	1220.0	1214.6	1198.5	1201.7	1199.6
22.5°	1188.8	1181.3	1165.2	1171.6	1167.3
25°	1154.5	1146.9	1131.9	1133.0	1128.7
27.5°	1115.8	1108.3	1094.3	1092.2	1086.8
30°	1077.1	1068.5	1054.6	1050.3	1044.9
32.5°	1036.3	1028.8	1013.8	1008.4	1003.0
35°	993.4	985.9	970.8	963.3	957.9
37.5°	948.3	941.8	925.7	918.2	910.7
40°	904.2	895.6	879.5	868.8	863.4
42.5°	857.0	852.7	834.4	821.5	818.3
45°	810.8	803.3	786.1	774.3	771.1
47.5°	762.5	757.1	741.0	728.1	719.5
50°	713.1	708.8	693.7	678.7	672.3
52.5°	664.8	659.4	643.3	630.4	621.8
55°	613.2	610.0	594.9	582.1	575.6
57.5°	564.9	561.7	546.6	533.7	527.3
60°	514.4	509.0	495.1	485.4	480.0
62.5°	465.0	460.7	445.7	437.1	431.7
65°	415.6	410.2	399.5	388.8	383.4
67.5°	365.1	360.8	350.1	339.4	338.3
70°	319.0	311.4	302.8	294.3	291.0
72.5°	269.6	262.0	255.6	249.1	245.9
75°	221.2	215.9	210.5	206.2	205.1
77.5°	174.0	171.8	166.5	165.4	162.2
80°	132.1	128.9	126.7	124.6	123.5
82.5°	91.3	90.2	90.2	89.1	88.1
85°	58.0	58.0	55.8	55.8	54.8
87.5°	27.9	26.8	25.8	25.8	25.8
90°	1.1	5.0	7.9	10.0	10.7
92.5°	9.3	13.9	15.7	16.8	17.1
95°	21.4	24.6	27.1	28.2	28.2
97.5°	34.3	37.1	40.0	41.4	41.4
100°	50.0	51.4	54.6	55.3	55.3
102.5°	66.4	66.8	69.6	70.7	71.1
105°	83.2	83.6	85.0	86.1	87.1
107.5°	100.7	101.0	101.4	102.8	102.5
110°	118.5	119.3	118.9	118.2	119.3



TEST NUMBER: P1001854

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	137.1	137.1	136.4	136.4	136.4
115°	155.7	155.7	155.0	154.6	154.3
117.5°	173.2	173.2	172.8	171.7	170.7
120°	190.7	192.1	191.0	189.2	190.0
122.5°	208.9	209.2	208.9	207.8	206.0
125°	226.7	226.7	226.4	225.7	225.0
127.5°	242.8	243.9	243.2	242.4	242.1
130°	259.9	261.0	261.0	260.3	258.9
132.5°	277.4	278.2	277.8	277.1	276.7
135°	292.4	294.6	294.6	293.9	292.8
137.5°	309.2	310.3	311.0	309.9	310.3
140°	326.0	326.7	326.7	326.4	326.0
142.5°	341.4	342.1	341.7	341.7	341.7
145°	355.3	356.7	357.1	356.7	355.6
147.5°	369.6	371.3	371.0	370.6	370.3
150°	382.4	383.8	383.8	383.8	383.5
152.5°	394.6	395.3	395.6	396.7	395.6
155°	407.1	407.1	406.7	408.1	406.7
157.5°	417.8	417.1	417.1	418.1	417.1
160°	427.1	426.7	426.3	427.4	425.6
162.5°	435.6	434.6	434.2	436.3	434.6
165°	443.1	442.0	441.3	443.5	442.0
167.5°	449.2	447.8	447.8	449.9	447.8
170°	454.2	452.4	452.8	454.9	452.4
172.5°	457.8	456.3	456.3	458.8	456.3
175°	461.0	459.2	458.8	461.3	458.8
177.5°	462.4	460.6	460.6	463.1	460.3
180°	461.7	461.7	461.7	461.7	461.7

(END OF REPORT)