

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001860

Luminaire Tested: SA4XXDIP-B795D365UB40-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001860
REPORT IS A COMBINATION OF REPORTS P996485 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB40-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4506.0 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001860

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001860

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66		
1	100	95	91	87	94	90	86	82	79	76	73	70	67	65	61	59	58	53		
2	91	82	75	70	85	78	71	66	69	64	60	60	57	53	53	50	47	43		
3	82	72	64	57	77	68	61	55	60	54	50	53	48	45	46	43	40	36		
4	75	63	55	48	70	60	52	46	53	47	42	47	42	38	41	37	34	31		
5	69	56	48	41	64	53	45	39	47	41	36	42	37	33	37	33	29	26		
6	63	51	42	36	59	48	40	34	43	36	31	38	32	28	33	29	26	23		
7	59	46	37	31	55	43	35	30	39	32	27	34	29	25	30	26	23	20		
8	54	41	33	28	51	39	32	26	35	29	24	31	26	22	28	23	20	18		
9	51	38	30	25	48	36	29	24	32	26	22	29	24	20	26	21	18	16		
10	47	35	27	22	45	33	26	21	30	24	20	27	22	18	24	20	16	15		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7742	7742	7742
5°	7763	7541	7554
10°	7713	7392	7371
15°	7641	7225	7164
20°	7534	7044	6964
25°	7413	6845	6747
30°	7283	6648	6527
35°	7136	6446	6330
40°	7017	6253	6127
45°	6842	6071	5947
50°	6693	5865	5757
55°	6538	5665	5539
60°	6300	5418	5333
65°	6036	5152	5085
70°	5716	4846	4799
75°	5271	4507	4527
80°	4767	4162	4242
85°	4097	3813	4012

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6842 cd/sqm

TEST NUMBER: P1001860

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	2.0
10°-20°	257.7	5.7
20°-30°	389.7	8.6
30°-40°	471.5	10.5
40°-50°	498.4	11.1
50°-60°	469.1	10.4
60°-70°	389.3	8.6
70°-80°	273.2	6.1
80°-90°	155.0	3.4
90°-100°	121.5	2.7
100°-110°	157.1	3.5
110°-120°	197.1	4.4
120°-130°	225.6	5.0
130°-140°	235.6	5.2
140°-150°	222.9	4.9
150°-160°	185.6	4.1
160°-170°	123.5	2.7
170°-180°	43.2	1.0
0°-30°	737.4	16.4
0°-40°	1208.9	26.8
0°-60°	2176.5	48.3
0°-90°	2993.9	66.4
90°-120°	475.8	10.6
90°-150°	1159.8	25.7
90°-180°	1512.0	33.6
0°-180°	4506.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	949	949	949	949	949	
5°	950	947	940	948	947	90
15°	911	912	909	919	918	257
25°	834	840	843	855	856	384
35°	729	742	753	768	771	457
45°	608	628	648	667	672	470
55°	476	499	530	552	558	424
65°	330	364	400	426	435	327
75°	183	222	267	297	306	194
85°	56	101	149	181	191	59
90°	18	64	113	146	155	13
95°	35	73	119	149	159	34
105°	92	114	154	182	192	98
115°	160	170	203	226	234	159
125°	229	228	254	273	279	204
135°	292	294	301	318	323	226
145°	353	353	353	360	363	221
155°	403	403	403	404	403	185
165°	439	438	437	439	438	124
175°	456	454	454	457	454	43
180°	457	457	457	457	457	

TEST NUMBER: P1001860

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	949.4	949.4	949.4	949.4	949.4
2.5°	953.7	950.5	942.0	949.4	948.4
5°	950.5	947.3	939.9	948.4	947.3
7.5°	944.1	942.0	935.6	945.2	944.1
10°	935.6	934.5	929.2	938.8	937.7
12.5°	923.9	923.9	920.7	929.2	929.2
15°	911.2	912.2	909.0	918.6	917.5
17.5°	894.1	897.3	896.3	905.8	904.8
20°	876.1	879.3	880.3	891.0	891.0
22.5°	855.9	860.1	862.2	872.9	875.0
25°	833.5	839.9	843.1	854.8	855.9
27.5°	809.1	818.7	822.9	833.5	834.6
30°	784.6	793.1	800.6	812.3	814.4
32.5°	758.1	768.7	777.2	791.0	793.1
35°	729.4	742.1	752.7	767.6	770.8
37.5°	700.6	715.5	728.3	743.2	746.4
40°	673.0	686.8	701.7	717.7	721.9
42.5°	641.1	657.1	675.1	693.2	696.4
45°	608.1	628.3	648.5	666.6	671.9
47.5°	577.3	597.5	620.9	639.0	645.4
50°	543.3	566.7	590.1	611.3	617.7
52.5°	509.3	532.7	560.3	581.6	587.9
55°	476.3	498.6	530.5	551.8	558.2
57.5°	439.1	466.7	497.6	523.1	528.4
60°	403.0	430.6	465.7	490.1	498.6
62.5°	367.9	398.7	433.8	458.2	466.7
65°	329.6	363.6	399.8	426.3	434.8
67.5°	293.4	329.6	367.9	394.4	403.0
70°	256.2	292.4	332.8	361.5	368.9
72.5°	220.1	257.3	300.9	328.5	337.0
75°	182.9	222.2	266.9	296.6	306.2
77.5°	147.8	189.2	236.0	265.8	276.4
80°	115.9	158.4	205.2	237.1	245.6
82.5°	84.0	128.6	175.4	208.4	218.0
85°	56.3	101.0	148.8	180.7	191.4
87.5°	35.1	78.7	125.5	156.3	165.9
90°	18.1	64.4	113.1	146.0	155.2
92.5°	25.1	67.0	114.5	145.2	154.2
95°	35.0	73.3	119.4	149.1	158.7
97.5°	46.7	80.4	126.8	155.8	165.4
100°	61.2	90.2	134.9	164.3	171.8
102.5°	77.4	101.2	144.4	173.1	181.9
105°	92.0	113.5	154.3	182.0	191.5
107.5°	109.3	127.6	165.3	193.2	200.3
110°	125.8	141.5	178.3	202.1	211.7



TEST NUMBER: P1001860

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	143.1	155.9	190.3	213.7	222.2
115°	160.5	170.0	203.4	226.4	233.5
117.5°	177.8	184.2	215.8	237.0	244.4
120°	194.0	198.7	228.4	247.9	257.1
122.5°	212.1	212.4	240.8	261.0	266.6
125°	228.7	227.6	253.9	273.4	279.0
127.5°	244.6	244.6	265.2	283.6	290.6
130°	260.5	260.5	277.5	296.0	300.9
132.5°	277.8	277.4	289.9	307.3	313.2
135°	291.6	293.7	301.2	317.5	322.8
137.5°	308.2	308.2	313.2	328.1	333.7
140°	324.8	324.5	325.5	338.9	344.0
142.5°	339.0	339.7	338.2	349.9	354.1
145°	352.8	353.1	353.4	359.5	362.6
147.5°	366.9	367.6	367.2	368.0	371.8
150°	379.6	380.0	380.0	380.0	379.6
152.5°	390.6	391.3	391.6	392.7	391.6
155°	402.9	402.9	402.6	404.0	402.6
157.5°	413.5	412.8	412.8	413.9	412.8
160°	422.7	422.4	422.0	423.1	421.3
162.5°	431.2	430.1	429.8	431.9	430.1
165°	438.6	437.6	436.9	439.0	437.6
167.5°	444.6	443.2	443.2	445.3	443.2
170°	449.6	447.8	448.2	450.3	447.8
172.5°	453.1	451.7	451.7	454.2	451.7
175°	456.3	454.5	454.2	456.7	454.2
177.5°	457.7	455.9	455.9	458.4	455.6
180°	457.0	457.0	457.0	457.0	457.0

(END OF REPORT)