

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001864

Luminaire Tested: SA4XXDIP-B795D365UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001864
REPORT IS A COMBINATION OF REPORTS P996489 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB40-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4719.6 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001864

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001864

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76
1	103	98	94	91	97	93	90	86	84	81	79	75	73	71	68	66	65
2	94	86	79	74	88	82	76	71	74	69	65	66	63	60	59	57	54
3	85	75	68	62	81	72	65	59	65	59	55	59	54	50	53	49	46
4	78	67	59	52	74	64	56	50	58	52	47	52	47	43	47	43	40
5	72	60	51	45	68	57	49	44	52	45	41	47	42	38	42	38	35
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31
7	61	49	40	35	58	47	39	34	43	36	31	39	33	29	35	31	27
8	57	44	36	31	54	42	35	30	39	33	28	36	30	26	32	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	27	24	30	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	22	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10821	10821	10821
5°	10830	10510	10523
10°	10738	10218	10146
15°	10584	9871	9722
20°	10387	9495	9283
25°	10166	9099	8810
30°	9899	8671	8291
35°	9623	8232	7789
40°	9335	7759	7255
45°	9032	7286	6756
50°	8697	6827	6204
55°	8334	6291	5655
60°	7961	5703	5084
65°	7536	5096	4439
70°	7045	4367	3750
75°	6311	3519	3003
80°	5380	2545	2113
85°	4177	1417	1136

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9032 cd/sqm

TEST NUMBER: P1001864

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	2.7
10°-20°	352.4	7.5
20°-30°	518.6	11.0
30°-40°	602.8	12.8
40°-50°	602.8	12.8
50°-60°	527.2	11.2
60°-70°	391.4	8.3
70°-80°	222.1	4.7
80°-90°	64.3	1.4
90°-100°	133.6	2.8
100°-110°	271.8	5.8
110°-120°	242.3	5.1
120°-130°	203.5	4.3
130°-140°	169.8	3.6
140°-150°	129.7	2.7
150°-160°	91.2	1.9
160°-170°	53.6	1.1
170°-180°	17.4	0.4
0°-30°	996.1	21.1
0°-40°	1598.9	33.9
0°-60°	2728.9	57.8
0°-90°	3406.7	72.2
90°-120°	647.7	13.7
90°-150°	1150.7	24.4
90°-180°	1313.0	27.8
0°-180°	4719.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1327	1327	1327	1327	1327	
5°	1326	1322	1310	1322	1320	126
15°	1262	1258	1242	1248	1245	356
25°	1143	1136	1121	1122	1118	526
35°	984	976	961	954	948	615
45°	803	795	778	767	763	619
55°	607	604	589	576	570	544
65°	412	406	396	385	380	407
75°	219	214	208	204	203	232
85°	57	57	55	55	54	62
90°	0	3	6	7	7	5
95°	12	37	288	143	86	13
105°	41	60	232	499	497	44
115°	73	91	207	397	478	72
125°	101	121	206	338	381	90
135°	120	144	204	300	341	93
145°	139	159	203	253	278	87
155°	158	171	197	223	233	73
165°	172	177	189	200	203	49
175°	180	180	181	184	183	17
180°	180	180	180	180	180	

TEST NUMBER: P1001864

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1327.0	1327.0	1327.0	1327.0	1327.0
2.5°	1331.3	1328.1	1316.4	1327.0	1325.9
5°	1325.9	1321.7	1310.0	1321.7	1319.6
7.5°	1316.4	1312.1	1299.4	1308.9	1307.9
10°	1302.5	1298.3	1284.5	1293.0	1290.8
12.5°	1284.5	1280.2	1265.3	1274.9	1271.7
15°	1262.1	1257.9	1241.9	1248.3	1245.1
17.5°	1236.6	1231.3	1216.4	1220.7	1218.5
20°	1207.9	1202.6	1186.6	1189.8	1187.7
22.5°	1177.1	1169.6	1153.7	1160.1	1155.8
25°	1143.0	1135.6	1120.7	1121.8	1117.5
27.5°	1104.8	1097.3	1083.5	1081.4	1076.1
30°	1066.5	1058.0	1044.2	1039.9	1034.6
32.5°	1026.1	1018.6	1003.8	998.4	993.1
35°	983.6	976.1	961.2	953.8	948.5
37.5°	938.9	932.5	916.6	909.1	901.7
40°	895.3	886.8	870.8	860.2	854.9
42.5°	848.5	844.3	826.2	813.4	810.2
45°	802.8	795.3	778.3	766.6	763.4
47.5°	754.9	749.6	733.7	720.9	712.4
50°	706.0	701.8	686.9	672.0	665.6
52.5°	658.2	652.9	636.9	624.2	615.7
55°	607.1	604.0	589.1	576.3	569.9
57.5°	559.3	556.1	541.2	528.5	522.1
60°	509.3	504.0	490.2	480.6	475.3
62.5°	460.4	456.2	441.3	432.8	427.4
65°	411.5	406.2	395.5	384.9	379.6
67.5°	361.5	357.3	346.6	336.0	334.9
70°	315.8	308.4	299.9	291.3	288.2
72.5°	266.9	259.4	253.1	246.7	243.5
75°	219.0	213.7	208.4	204.2	203.1
77.5°	172.3	170.1	164.8	163.7	160.6
80°	130.8	127.6	125.5	123.3	122.3
82.5°	90.4	89.3	89.3	88.3	87.2
85°	57.4	57.4	55.3	55.3	54.2
87.5°	27.6	26.6	25.5	25.5	25.5
90°	0.4	2.8	6.4	7.1	7.4
92.5°	4.9	27.2	138.6	45.8	32.2
95°	11.7	36.8	288.1	142.6	86.2
97.5°	19.4	40.6	308.2	291.2	207.1
100°	26.9	46.0	284.2	403.0	324.1
102.5°	33.9	52.3	254.1	472.9	425.9
105°	41.4	59.9	231.9	499.2	497.3
107.5°	49.5	67.7	217.4	491.2	531.2
110°	57.6	75.4	210.7	463.0	531.9



TEST NUMBER: P1001864

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.4	83.2	207.5	428.4	511.1
115°	72.8	91.4	206.8	397.2	477.5
117.5°	80.6	99.0	206.4	372.8	444.6
120°	88.4	106.4	206.4	356.4	417.8
122.5°	95.4	113.6	206.1	345.7	396.6
125°	101.4	120.6	205.7	338.1	381.0
127.5°	107.1	126.8	205.0	330.8	371.1
130°	111.7	133.0	204.6	322.2	362.6
132.5°	116.3	138.4	204.3	312.0	353.1
135°	120.5	143.5	203.9	300.0	340.7
137.5°	124.8	147.9	203.9	287.4	326.2
140°	129.4	152.0	203.6	275.0	310.3
142.5°	134.3	155.7	203.6	263.5	293.4
145°	138.9	159.0	202.9	253.0	278.2
147.5°	144.2	162.2	201.8	244.4	264.0
150°	149.2	165.2	200.8	236.4	252.4
152.5°	153.7	168.1	199.0	229.8	241.8
155°	158.0	170.6	197.2	223.4	232.9
157.5°	162.2	172.8	195.5	217.4	224.8
160°	166.1	174.8	193.3	211.4	217.4
162.5°	169.7	176.4	191.2	205.6	210.3
165°	172.1	177.4	189.1	200.2	203.2
167.5°	175.0	178.3	187.0	195.6	197.6
170°	176.7	179.0	184.9	191.0	192.3
172.5°	178.5	179.6	182.7	187.0	187.0
175°	179.6	179.9	181.3	183.8	183.1
177.5°	180.3	179.9	180.3	181.5	180.3
180°	179.9	179.9	179.9	179.9	179.9

(END OF REPORT)