

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008285

Luminaire Tested: S122DIP-B865D925UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008285
REPORT IS A COMBINATION OF REPORTS P984973 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D925UB2750-4F0-XX-W2A-D_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7138.0 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008285

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008285

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50
1	95	90	86	82	86	82	79	75	68	65	63	54	52	51	42	41	40
2	86	78	71	66	78	71	66	61	59	54	51	47	44	41	36	34	32
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	32	29	27
4	71	60	52	45	65	55	48	42	45	40	35	36	32	29	28	25	23
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	20	17
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	21	18	15
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14408	14408	14408
5°	14473	13793	13716
10°	14375	13315	13121
15°	14172	12822	12511
20°	13917	12303	11934
25°	13665	11806	11409
30°	13310	11300	10889
35°	12952	10814	10507
40°	12575	10392	10129
45°	12215	10011	9799
50°	11830	9659	9472
55°	11423	9285	9140
60°	10927	8895	8791
65°	10409	8448	8389
70°	9826	7969	7957
75°	9079	7486	7549
80°	7896	6986	7127
85°	6710	6516	6763

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12215 cd/sqm

TEST NUMBER: P1008285

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.3	1.2
10°-20°	247.5	3.5
20°-30°	375.0	5.3
30°-40°	456.6	6.4
40°-50°	491.3	6.9
50°-60°	477.1	6.7
60°-70°	416.7	5.8
70°-80°	320.7	4.5
80°-90°	217.0	3.0
90°-100°	189.4	2.7
100°-110°	261.8	3.7
110°-120°	478.8	6.7
120°-130°	715.4	10.0
130°-140°	734.3	10.3
140°-150°	669.8	9.4
150°-160°	536.2	7.5
160°-170°	345.5	4.8
170°-180°	118.9	1.7
0°-30°	708.7	9.9
0°-40°	1165.3	16.3
0°-60°	2133.7	29.9
0°-90°	3088.0	43.3
90°-120°	929.9	13.0
90°-150°	3049.4	42.7
90°-180°	4050.0	56.7
0°-180°	7138.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	910	910	910	910	910	
5°	913	909	901	909	908	87
15°	871	873	873	885	884	245
25°	792	801	813	828	832	364
35°	682	704	730	758	768	426
45°	559	595	641	682	695	432
55°	429	476	545	592	609	383
65°	293	358	435	489	506	291
75°	162	236	320	377	394	172
85°	48	129	214	269	288	50
90°	14	100	192	250	267	13
95°	69	102	187	242	257	78
105°	281	347	168	225	243	301
115°	525	555	637	258	207	517
125°	738	749	809	851	865	658
135°	911	925	947	983	992	704
145°	1055	1054	1070	1084	1086	660
155°	1162	1154	1164	1170	1163	535
165°	1224	1219	1221	1228	1221	346
175°	1252	1246	1248	1254	1245	119
180°	1249	1249	1249	1249	1249	

TEST NUMBER: P1008285

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	910.2	910.2	910.2	910.2	910.2
2.5°	916.8	912.8	903.6	910.2	907.6
5°	912.8	908.9	901.0	908.9	907.6
7.5°	906.2	903.6	897.0	906.2	904.9
10°	898.3	895.7	891.7	902.3	901.0
12.5°	885.1	886.5	883.8	894.4	893.1
15°	870.6	873.3	873.3	885.1	883.8
17.5°	852.2	857.4	861.4	873.3	873.3
20°	833.7	840.3	845.6	860.1	860.1
22.5°	813.9	821.8	829.7	844.2	846.9
25°	791.5	800.7	812.6	828.4	832.4
27.5°	765.1	779.6	792.8	812.6	815.2
30°	738.7	755.9	773.0	794.1	798.1
32.5°	709.7	729.5	750.6	775.6	783.6
35°	682.0	704.4	729.5	758.5	767.7
37.5°	651.6	676.7	708.4	740.0	749.3
40°	621.3	650.3	685.9	720.2	732.1
42.5°	592.3	621.3	663.5	701.8	713.6
45°	559.3	594.9	641.1	682.0	695.2
47.5°	527.7	565.9	618.7	660.9	675.4
50°	494.7	535.6	594.9	639.8	654.3
52.5°	463.0	506.5	569.9	616.0	631.9
55°	428.7	476.2	544.8	592.3	609.4
57.5°	395.7	448.5	517.1	568.5	585.7
60°	360.1	416.8	492.0	542.2	560.6
62.5°	328.5	387.8	463.0	517.1	534.2
65°	292.8	357.5	435.3	489.4	506.5
67.5°	261.2	328.5	407.6	461.7	480.2
70°	226.9	295.5	377.3	434.0	449.8
72.5°	195.2	266.5	349.6	405.0	424.8
75°	162.3	236.1	320.5	377.3	394.4
77.5°	130.6	207.1	292.8	349.6	368.0
80°	98.9	179.4	265.1	320.5	339.0
82.5°	72.6	151.7	238.8	294.2	311.3
85°	47.5	129.3	213.7	269.1	287.6
87.5°	29.0	108.2	192.6	246.7	263.8
90°	14.1	100.5	192.2	249.5	267.1
92.5°	34.5	100.8	184.0	237.2	253.9
95°	69.4	101.5	187.0	241.6	256.6
97.5°	115.0	97.6	188.6	240.1	256.8
100°	169.2	94.2	183.4	239.5	255.8
102.5°	227.6	269.3	176.0	233.5	250.7
105°	281.4	346.9	168.5	224.7	242.8
107.5°	345.6	399.9	161.2	216.0	234.1
110°	405.8	451.2	254.5	206.3	224.4

TEST NUMBER: P1008285

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	463.7	501.0	546.4	198.9	216.1
115°	525.1	555.0	636.9	257.9	207.3
117.5°	577.2	605.7	676.5	586.8	363.2
120°	636.8	655.6	724.7	772.4	664.9
122.5°	687.5	703.2	770.1	811.1	823.9
125°	737.6	749.3	808.8	850.8	865.3
127.5°	784.6	796.0	845.1	887.2	900.0
130°	828.9	842.1	879.7	921.4	931.0
132.5°	874.1	884.6	914.3	952.7	962.4
135°	910.8	925.2	946.6	983.3	992.1
137.5°	950.6	961.4	977.0	1011.2	1017.7
140°	989.4	995.4	1007.9	1037.1	1040.6
142.5°	1022.0	1027.0	1038.8	1061.8	1063.9
145°	1055.0	1054.1	1069.5	1083.7	1085.8
147.5°	1084.9	1082.2	1097.5	1103.3	1103.7
150°	1113.8	1107.5	1121.9	1127.4	1122.8
152.5°	1138.2	1131.0	1144.5	1150.0	1143.6
155°	1161.7	1153.6	1164.4	1169.8	1162.6
157.5°	1180.7	1173.5	1181.6	1187.9	1180.7
160°	1197.0	1191.5	1197.0	1202.4	1196.1
162.5°	1211.4	1206.0	1210.5	1216.9	1208.7
165°	1224.1	1218.7	1221.4	1227.7	1221.4
167.5°	1234.0	1228.6	1231.3	1237.6	1229.5
170°	1242.2	1236.7	1238.6	1244.9	1236.7
172.5°	1247.6	1242.2	1244.0	1250.3	1242.2
175°	1252.1	1245.8	1247.6	1253.9	1244.9
177.5°	1253.9	1247.6	1248.5	1254.8	1246.7
180°	1249.4	1249.4	1249.4	1249.4	1249.4

(END OF REPORT)